

**EE CORE**



TYPE	FIG.	Dimensions(mm)					
		A	B	C	D	E	F
EE23/18/8	1	23.0±0.4	9.0±0.15	8.2±0.2	7.2±0.2	16.6min	5.4±0.15
EE25/20/6	1	25.4±0.5	10.0±0.3	6.4±0.3	6.0±0.3	18.5min	7.0±0.3
EE25/14/14	1	25.00±0.4	7.25±0.15	13.8±0.30	7.2±0.25	17.6min	2.05±0.15
EE25/18/11	1	25.05±0.75	9.0±0.25	10.75±0.3	7.25±0.25	17.8min	5.4±0.25
EE25/25/9	1	25.05±0.75	12.55min	8.85±0.25	7.25±0.25	17.5min	9.0min
EE25/26/7	1	25.05±0.75	12.55±0.25	7.2±0.3	7.25±0.25	17.5min	8.95±0.25
EE25/26/11	1	25.05±0.5	12.55±0.15	10.75±0.3	7.25±0.25	17.5min	8.95±0.15
EE25/32/6	1	25.4±0.5	16.3±0.4	6.3±0.3	6.3±0.3	18.6min	13.3±0.4
EE26/22/11	1	26.7±0.5	10.8±0.3	11.0±0.3	7.2±0.3	19.0min	6.8±0.3
EE28/21/11	1	28.40±0.5	10.30±0.2	10.70±0.3	7.20±0.3	20.0min	6.30±0.2
EE28/34/11	1	28.2±0.5	17.1±0.3	10.4±0.3	7.1±0.3	18.9min	12.8±0.4
EE30/26/11	1	30.0±0.5	13.2±0.2	10.7±0.3	10.7±0.3	19.8min	8.1±0.2
EE30/30/7	1	30.0±0.7	15.0±0.2	7.05±0.25	6.95±0.25	19.6min	10.0±0.2
EE32/33/9	1	32.1±0.6	16.7±0.15	9.15±0.3	9.2±0.3	22.7min	11.5±0.15
EE32/32/11	1	32.1±0.6	16.1±0.15	10.45±0.3	9.2±0.3	23.2±0.6	11.75±0.15
EE33/28/13	1	33.0±0.6	14.0±0.3	13.0±0/-0.6	9.7±0.3	22.8min	9.6±0.3
EE33/48/13	1	33±0.65	23.7±0.15	12.7±0.35	9.7±0.3	23.8min	19.2±0.15
EE35/29/10	1	35.0±0.5	14.5±0.25	10.0±0.4	9.5±0.3	25.0min	10.0±0.3
EE35/35/10	1	35.0±0.6	17.5±0.3	10.0±0.3	10.0±0.3	24.5min	12.5±0.3
EE40/35/12	1	40.0±0.7	17.5±0.4	11.7±0.4	11.5±0.4	27.2min	10.6±0.4
EE41/34/13	1	40.6±0.6	16.5±0.3	12.5±0.3	12.5±0.3	28.6min	10.5±0.3
EE42/42/15	1	42.1±0.9	21.2±0.4	14.9±0.3	12.0±0.3	29.5min	15.4±0.3
EE42/42/20	1	42.1±0.9	21.2±0.4	19.9±0.3	12.0±0.3	29.5min	15.4±0.3
EE51/54/12	1	50.5±1.0	26.8±0.2	12.0±0.3	16.0±0.25	33.9min	18.8±0.2
EE55/55/17	1	55.0±1.0	27.5±0.3	17.0±0.7	16.7±0.3	37.0min	18.8±0.3
EE55/55/21	1	55.0±1.0	27.7±0.3	20.9±0.5	16.9±0.3	37.5min	18.8±0.3
EE56/55/25	1	56.5±1.0	27.8±0.3	24.8±0.3	16.85±0.3	37.5min	19.0±0.3
EE65/65/20	1	65.4±1.6	32.6±0.6	19.8±0.7	19.8±0.7	44.2min	22.6±0.6
EE65/65/27	1	65.4±1.6	32.6±0.6	27.0±0.6	19.8±0.7	44.2min	22.6±0.6
EE70/66/32	1	70.0±1.5	33.0±0.3	31.75±0.8	21.5±0.6	48.0min	22.5±0.3
EE80/76/20	1	80.5±1.5	38.0±0.4	20.0±0.5	20.0±0.4	60.0min	28.0±0.3

**EE CORE**




FIG.1

Cl	Ae	Le	Ve	AL±25%(nH/N <sup>2</sup> )						Weight g/PRS
				FW40	FW44	FW95	FW5K	FW7K	FW10K	
0.72	59.00	42.60	2548.0	2500						13.50
1.28	38.40	49.50	2131.0	1900	1650	2070	4100	5100	6000	10.70
0.29	99.36	29.40	4414.0	4800						22.00
0.56	77.30	43.60	3371.0	3200						20.30
0.93	62.69	58.51	3667.9	2350	2430	3100				19.00
1.06	54.00	57.60	3267.0	1900	1980	2500				13.50
0.75	76.99	57.81	4451.0	3000	3100	3950				22.40
1.90	40.40	76.70	3097.0	1300	1300		2800	3600	4300	15.50
0.62	79.20	49.80	4578.0	3600	3600					22.00
0.63	77.00	48.80	4534.0	3500	3690	4630				24.00
0.99	73.84	73.65	6888.0	2400	2500	3230				35.00
0.53	110.00	57.80	6358.0	4100	4230	5370				35.00
1.28	48.90	63.00	4561.0	2300	1750	2240	4600			23.60
0.88	85.44	75.08	6414.5	2700	2800	3600	5050	6100	7600min	32.60
0.80	93.47	74.91	7001.8	2950	3100	3950				35.20
0.56	118.83	66.50	7901.8	3900	4040	5170				40.60
0.92	114.88	105.47	12115.9	2750	2850	3700				60.60
0.70	98.60	69.20	6820.0	2593	2684	3430	5550	6700	8400min	33.20
0.81	99.69	84.77	8047.5	2950	3050	3950				40.80
0.55	141.80	78.68	11161.0	4300	4390	5660				59.00
0.52	149.22	77.41	11551.4	4400	4560	5870	8890	10800	13300min	59.30
0.60	180.00	97.80	17600.0	3800	4560	5940				88.00
0.40	242.00	97.80	24698.0	5000	6070	7900				120.00
0.62	192.00	118.80	22866.0	4700	4500					120.00
0.428	283.00	121.00	37810.0	5500	3700					178.00
0.35	354.00	123.00	43542.0	6500	7350	9660				223.00
0.29	417.00	122.00	58446.0	7770						308.00
0.40	378.90	147.00	58655.0	5400	5900	7840				285.00
0.274	540.00	147.00	79000.0	7900	9700	12800				410.00
0.208	700.00	145.50	101900.0	12800	12200	16100				530.00
0.446	399.00	183.50	73150.0	4500	5880	7840				368.00