


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	P	F	REVISIONS				
G	14			ZONE	LTR	DESCRIPTION	DATE	APPD
					L	REV / 0720-0949-96	24MAY96	ME KF

AMP WIRE RANGE	UL Listed	SR LR7189 Certified
22-14 AWG SOLID OR STRANDED	22-14 AWG SOLID OR STRANDED	22-14 AWG SOLID OR STRANDED



STAMPING DETAIL

- 1 WIRE INSULATION OPENING 4.75mm [.187] MIN DIA
- △ SUPERSEDED BY 36964



100	LOOSE PC, BOX	8-36964-1
20000	BOX	2-36964-5 △
2500	TAPE MOUNTED	2-36964-2
-	LOOSE PIECE	36964

QTY	DESCRIPTION	PART NO
AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME SPLICE, WIRE, CLOSED END		
SIZE	CAGE CODE	DRAWING NO
B	00779	C-36964
SCALE	SHEET	
4:1	1 OF 1	

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 90°C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20 [.008] 3 PLC DEC ± - ANGLES ± -
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: 300V MAX	MATERIAL BODY, COPPER INSULATION, PVC COLOR, PURPLE
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: 0.26-2.62mm ² [509-5180]	FINISH SPLICE, TIN PLATED MIL-T-10727
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			