

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 25_BMA-50-2-2/119_N



Description

Straight panel cable jack, flange mount

Interface Standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz

Mechanical Data

Centre contact plugged
Outer contact soldered
Weight 0.0055 kg

Environmental Data

Operating Temperature -65 °C to 125 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Copper Beryllium Alloy
Body	Copper Beryllium Alloy
Other body part	Stainless Steel
Insulator	PFA / PTFE

Surface Plating

Centre contact	Gold Plating (Nickel underplated)
Outer contact	Gold Plating (without Nickel underplating)
Body	Gold Plating (Nickel underplated)

Related Documents

Catalogue drawing	DCA-00008815
Assembly instruction	DOC-0000180997
Mounting hole	DOU-00008816

Ordering Information

Single package	25_BMA-50-2-2/119_NE
Bulk 100 pcs package	25_BMA-50-2-2/119_NH

Additional Information

Suitable cable	EZ_86_TP_M17
----------------	--------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[25_BMA-50-2-2/119_NE](#)