



# TR30RDM SERIES 30 WATT AC-DC MEDICAL INTERCHANGEABLE PLUG ADAPTER

## Features

- Universal Input Range 80~264Vac
- High Efficiency up to 88%
- Interchangeable AC Plugs
- Leakage Current < 50uA
- Class II
- No Load Power Consumption < 75mW
- Approval IEC/EN/UL 60601-1 2 MOPP
- Approval EN60601-1-11  
for Home Healthcare Applications
- Approval EN 55011, FCC 47 CFR Part 18 Class B
- Approval IP22
- Meets IEC/EN 60335-1
- Operating Altitude 5000m
- Over Voltage Protection
- Continuous Short Circuit Protection
- Meets CoC Tier 2 & DoE Level VI



AC Plug Sold Separately



MODEL NUMBER	OUTPUT VOLTAGE	OUTPUT CURRENT	VOLTAGE ACCURACY NOTE1	RIPPLE & NOISE NOTE2	LINE REGULATION NOTE3	LOAD REGULATION NOTE4	%EFF. (Typ.) NOTE5
TR30RDM050	5 V	5 A	±2%	100 mV	±1%	±6%	84%
TR30RDM090	9 V	3.3 A	±2%	100 mV	±1%	±3%	88%
TR30RDM120	12 V	2.5 A	±2%	120 mV	±1%	±2%	88%
TR30RDM150	15 V	2.0 A	±2%	120 mV	±1%	±2%	88%
TR30RDM180	18 V	1.67 A	±2%	120 mV	±1%	±2%	88%
TR30RDM240	24 V	1.25 A	±2%	120 mV	±1%	±2%	88%

Note:

1. Voltage accuracy is set at 60% full load.
2. Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for ripple & noise measuring @20MHz BW.
3. Line regulation is measured from 100V<sub>ac</sub> to 240V<sub>ac</sub> with 100% full load.
4. Load regulation is measured from 60% to 100% full load and from 60% to 20% full load (60%±40% full load).
5. Typical efficiency at 230 V<sub>ac</sub> and 75% full load at 25°C.

## PART NUMBER

Series	Output Voltage	AC Plug Type	DC Plug Type	Cable Type	Cable Length	Case Color
TR30RDM	XXX	-XXXX	-XX	X	XX	-XX-BK
30W Medical Adapter	050 : 5V 090 : 9V 120 : 12V 150 : 15V 180 : 18V 240 : 24V	Blank: Sold Separately ASUE: Include 4 Type AC Plug	<a href="#">See Page 6</a>	G : UL1571 with OVP	01 : 720mm 02 : 1220mm 03 : 1800mm 11 : 720mm with Ferrite Core 12 : 1220mm with Ferrite Core 13 : 1800mm with Ferrite Core <a href="#">See page 6 for restrictions</a>	BK-BK : Black-Black BE-BK : Blue-Black

Part Number Example:

**TR30RDM120-11G13-BK-BK**, 12V<sub>ac</sub> Output, DC Jack Type, Cable Length 1800mm with Ferrite Core, Case Color Black-Black

**TR30RDM120-ASUE-11G03-BE-BK**, 12V<sub>ac</sub> Output, Include 4 Type AC Plug, DC Jack Type, Cable Length 1800mm, Case Color Blue-Black



# TR30RDM Series

## TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25°C unless otherwise noted.)

### ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	See Derating Curve	All	80		264	V <sub>ac</sub>
Operating Case Temperature	See Derating Curve	All	-25		70	°C
Storage Temperature		All	-25		85	°C
Operating Altitude		All			5000	m

### INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Voltage Range		All	100		240	V <sub>ac</sub>
Input Frequency Range		All	47		63	Hz
Maximum Input Current	100% Full load, V <sub>in</sub> =100V <sub>ac</sub>	All			0.8	A
Leakage Current		All			50	uA
Inrush Current	V <sub>in</sub> =240V <sub>ac</sub> , Cold start at 25°C	All		85		A

### OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Set Point	V <sub>in</sub> =115V <sub>ac</sub> and 230V <sub>ac</sub> , I <sub>o</sub> =60% Full load T <sub>c</sub> =25°C	TR30RDM050	4.90	5	5.10	V <sub>dc</sub>
		TR30RDM090	8.82	9	9.18	
		TR30RDM120	11.76	12	12.24	
		TR30RDM150	14.70	15	15.30	
		TR30RDM180	17.64	18	18.36	
		TR30RDM240	23.52	24	24.48	
Operating Output Current Range	V <sub>in</sub> =115V <sub>ac</sub> and 230V <sub>ac</sub> , T <sub>c</sub> =25°C	TR30RDM050			5	A
		TR30RDM090			3.3	
		TR30RDM120			2.5	
		TR30RDM150			2.0	
		TR30RDM180			1.67	
		TR30RDM240			1.25	
Holdup Time	V <sub>in</sub> =115V <sub>ac</sub>	All		10		ms
Output Voltage Regulation						
Load Regulation	60%±40% Full load change	TR30RDM050			±6.0	%
		TR30RDM090			±3.0	
		TR30RDM120			±2.0	
		TR30RDM150			±2.0	
		TR30RDM180			±2.0	
		TR30RDM240			±2.0	
Line Regulation	V <sub>in</sub> =100V <sub>ac</sub> to 240V <sub>ac</sub>	All			±1.0	%
Over Voltage Protection	Latch Off	TR30RDM050		7.44		V <sub>dc</sub>
		TR30RDM090		12.60		
		TR30RDM120		15.50		
		TR30RDM150		19.50		
		TR30RDM180		23.50		
		TR30RDM240		31.50		
Over Current Protection	Auto recovery	All	110		160	%
Short Circuit Protection	Auto recovery	All				



# TR30RDM Series

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Ripple and Noise	1. Add a 0.1uF ceramic capacitor and a 10uF aluminum electrolytic capacitor to output 2. Oscilloscope is 20MHz band width 3. Ambient temperature=25°C	TR30RDM050			100	mV
		TR30RDM090			100	
		TR30RDM120			120	
		TR30RDM150			120	
		TR30RDM180			120	
		TR30RDM240			120	
Load Capacitance	1. $V_{in}=115V_{ac}$ and $230V_{ac}$ 2. Output is max. load 3. Ambient temperature=25°C	TR30RDM050			5000	uF
		TR30RDM090			3300	
		TR30RDM120			2500	
		TR30RDM150			2000	
		TR30RDM180			1670	
		TR30RDM240			1250	
Efficiency	1. $V_{in}=230V_{ac}$ 2. Output is 75% full load 3. Ambient temperature=25°C	TR30RDM050		84		%
		TR30RDM090		88		
		TR30RDM120		88		
		TR30RDM150		88		
		TR30RDM180		88		
		TR30RDM240		88		

## ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input to Output	1 minute	All			4000	$V_{ac}$
Isolation Resistance	Input to output	All	100			MΩ

## FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	Pout=max. rated power	All		65		kHz

## GENERAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	$I_o=100\%$ ; $T_a=25^\circ C$ per MIL-HDBK-217F	All	380			k hours
Humidity	Non-condensing	All			93	% RH
Shock	Meet MIL-STD-810F Table 516.5, Table 516.5-I 10ms, each axis 3 times( $\pm X$ 、 $\pm Y$ 、 $\pm Z$ axis)	All		75		g
Vibration	Meet MIL-STD-810F Table 514.5C-VIII, 15~2000Hz, X、Y、Z axis, 1 hour (each axis),. Total 3 hrs.	All		4		g
Weight		All		170		g
Dimensions		All	3.807x2.283x1.703 inches (96.70x58.00x43.25 mm)			
<b>Safety</b>	Class II, IEC 60601-1:2005+CORR1:2006+CORR2:2007+A1:2012 EN 60601-1:2006+A11:2011+A1:2013+A12:2014 ANSI/AAMI ES 60601-1:2005/(R)2012+A1:2012, C1:2009/(R)2012+A2:2010/(R)2012 IEC/EN 60601-1-11:2015 for Home Healthcare Applications					Ed.3.1
<b>EMC Emission</b>	EN 55011:2009+A1:2010, CISPR 11:2009+A1:2010, Class B, EN 61003-3:2013, FCC 47 CFR Part 18					
Conducted Disturbance	EN 55011:2009+A1:2010, CISPR 11:2009+A1:2010, FCC 47 CFR Part 18					Class B
Radiated Disturbance	EN 55011:2009+A1:2010, CISPR 11:2009+A1:2010, FCC 47 CFR Part 18					Class B
Voltage Fluctuations & Flicker	EN 61000-3-3:2013					
<b>EMC Immunity</b>	EN 60601-1-2:2015, IEC 61000-4-2, 3, 4, 5, 6, 8, 11					Ed.4.0
Electrostatic Discharge (ESD)	IEC 61000-4-2:2008, Air Discharge: $\pm 15kV$ , Contact Discharge: $\pm 8kV$					Criteria A
Radio-Frequency, Continuous Radiated Disturbance	IEC 61000-4-3:2006+A1:2007+A2:2010					Criteria A





# TR30RDM Series

## GENERAL SPECIFICATIONS





Electrical Fast Transient (EFT)	IEC 61000-4-4:2012, $\pm 2\text{kV}$	Criteria A
Surge	IEC 61000-4-5:2014+A1:2017, L-N: $\pm 0.5\text{kV}$ , $\pm 1\text{kV}$	Criteria A
Conducted disturbances, induced by RF fields	IEC 61000-4-6:2013+COR1:2015	Criteria A
Power frequency magnetic field	IEC 61000-4-8:2009	Criteria A
Voltage dips	IEC 61000-4-11:2004+A1:2017, Dips: 30% Reduction, Dips: >95% Reduction	Criteria A
Voltage interruptions	IEC 61000-4-11:2004+A1:2017, >95% reduction	Criteria B
Application Note Link	<a href="#">TR30RDM Series App Notes</a>	

## CHARACTERISTIC CURVE

### Power Derating Curve




### Performance Data






# TR30RDM Series

TR30RDM180 (Eff Vs Io)




TR30RDM240 (Eff Vs Io)



## MECHANICAL SPECIFICATION

All Dimensions are in inches[mm]  
Tolerance: Inches: X.XXX±0.02  
Millimeters: X.XX±0.5







## INTERCHANGEABLE AC PLUG SPECIFICALLY for TR30RDM (SOLD SEPARATELY)

TYPE				
	U.K type (U)	American type (A)	European type (E)	Australian type (S)
ORDER NO.	AC PLUG RA-U	AC PLUG RA-A	AC PLUG RA-E	AC PLUG RA-S



# TR30RDM Series

## STANDARD OUTPUT PLUG

DC Plug Type	Cable Number -XXXXX	A	B	C	Cable Type	Cable Length	Cable AWG
		OD (mm)	ID (mm)	L (mm)			
 <p>Straight/Inner+Outer- + ● -</p>	11G02	Φ5.5	Φ2.1	12	UL1571	1220mm without Core	16AWG for Vo: 5V
	12G02	Φ5.5	Φ2.5	12			
	23G02	Φ5.5	Φ2.1	9.5			
	26G02	Φ5.5	Φ2.5	9.5			
 <p>Right Angle/Inner+Outer- + ● -</p>	01G02	Φ5.5	Φ2.1	12			
	02G02	Φ5.5	Φ2.5	12			
	21G02	Φ5.5	Φ2.5	9.5			
	24G02	Φ5.5	Φ2.1	9.5			
 <p>Straight/Inner+Outer- + ● -</p>	11G03	Φ5.5	Φ2.1	12	UL1571	1800mm without Core	16AWG for Vo: 9V 18AWG for Vo: 12V, 15V 22AWG for Vo: 18V, 24V
	12G03	Φ5.5	Φ2.5	12			
	23G03	Φ5.5	Φ2.1	9.5			
	26G03	Φ5.5	Φ2.5	9.5			
 <p>Right Angle/Inner+Outer- + ● -</p>	01G03	Φ5.5	Φ2.1	12			
	02G03	Φ5.5	Φ2.5	12			
	21G03	Φ5.5	Φ2.5	9.5			
	24G03	Φ5.5	Φ2.1	9.5			

※Other DC Plug Type please refer to the link: <https://www.cincon.com/productdownload/TR30RDM-cable-DC-Plug.pdf>

CINCON Electronics Co. Ltd.  
 Add: 14F, No. 306, Sec.4, Hsin Yi Rd., Taipei, Taiwan  
 Tel: 886-2-27086210  
 Fax: 886-2-27029852  
 E-mail: [sales@cincon.com.tw](mailto:sales@cincon.com.tw)  
 Web: [www.cincon.com](http://www.cincon.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Cincon:

[TR30RDM150-02G03-BK-BK-Level-VI](#) [TR30RDM050-48G11-BK-BK-Level-VI](#) [TR30RDM240-40G11-RD-BK-Level-VI](#)  
[TR30RDM240-02G13-RD-BK-Level-VI](#) [TR30RDM120-12G03-RD-BK-Level-VI](#) [TR30RDM240-11G11-RD-BK-Level-VI](#)  
[TR30RDM240-36G01-BE-BK-Level-VI](#) [TR30RDM180-11G11-BE-BK-Level-VI](#) [TR30RDM050-39G11-RD-BK-Level-VI](#)  
[TR30RDM240-11G02-BE-BK-Level-VI](#) [TR30RDM090-01G12-BE-BK-Level-VI](#) [TR30RDM240-39G11-BK-BK-Level-VI](#)  
[TR30RDM120-48G01-BK-BK-Level-VI](#) [TR30RDM050-01G02-RD-BK-Level-VI](#) [TR30RDM180-12G12-RD-BK-Level-VI](#)  
[TR30RDM150-12G02-BK-BK-Level-VI](#) [TR30RDM050-36G11-BE-BK-Level-VI](#) [TR30RDM120-40G11-BE-BK-Level-VI](#)  
[TR30RDM090-02G03-BE-BK-Level-VI](#) [TR30RDM050-36G02-BE-BK-Level-VI](#) [TR30RDM240-40G11-BE-BK-Level-VI](#)  
[TR30RDM090-11G02-RD-BK-Level-VI](#) [TR30RDM050-12G11-BK-BK-Level-VI](#) [TR30RDM050-12G02-BK-BK-Level-VI](#)  
[TR30RDM120-11G13-BK-BK-Level-VI](#) [TR30RDM050-40G02-RD-BK-Level-VI](#) [TR30RDM240-49G13-RD-BK-Level-VI](#)  
[TR30RDM150-12G01-BE-BK-Level-VI](#) [TR30RDM180-01G02-RD-BK-Level-VI](#) [TR30RDM120-40G03-BE-BK-Level-VI](#)  
[TR30RDM050-35G12-BK-BK-Level-VI](#) [TR30RDM150-01G13-BE-BK-Level-VI](#) [TR30RDM240-49G02-BK-BK-Level-VI](#)  
[TR30RDM240-36G11-BK-BK-Level-VI](#) [TR30RDM120-02G03-BE-BK-Level-VI](#) [TR30RDM120-40G03-BK-BK-Level-VI](#)  
[TR30RDM120-39G01-RD-BK-Level-VI](#) [TR30RDM090-02G13-BE-BK-Level-VI](#) [TR30RDM180-01G03-BE-BK-Level-VI](#)  
[TR30RDM120-02G11-BE-BK-Level-VI](#) [TR30RDM240-12G02-RD-BK-Level-VI](#) [TR30RDM240-39G12-BE-BK-Level-VI](#)  
[TR30RDM090-01G13-BK-BK-Level-VI](#) [TR30RDM240-39G13-BE-BK-Level-VI](#) [TR30RDM120-49G03-BK-BK-Level-VI](#)  
[TR30RDM240-35G02-BK-BK-Level-VI](#) [TR30RDM240-48G13-BE-BK-Level-VI](#) [TR30RDM180-11G12-BE-BK-Level-VI](#)  
[TR30RDM120-35G11-RD-BK-Level-VI](#) [TR30RDM090-12G01-BK-BK-Level-VI](#) [TR30RDM120-01G02-BE-BK-Level-VI](#)  
[TR30RDM240-39G03-BE-BK-Level-VI](#) [TR30RDM120-36G12-RD-BK-Level-VI](#) [TR30RDM150-11G12-BK-BK-Level-VI](#)  
[TR30RDM120-48G02-BE-BK-Level-VI](#) [TR30RDM180-02G01-RD-BK-Level-VI](#) [TR30RDM180-12G11-BE-BK-Level-VI](#)  
[TR30RDM120-12G02-RD-BK-Level-VI](#) [TR30RDM180-12G02-BK-BK-Level-VI](#) [TR30RDM180-01G01-BE-BK-Level-VI](#)  
[TR30RDM050-02G11-RD-BK-Level-VI](#) [TR30RDM120-49G03-RD-BK-Level-VI](#) [TR30RDM090-12G01-RD-BK-Level-VI](#)  
[TR30RDM180-11G12-BK-BK-Level-VI](#) [TR30RDM050-11G11-BE-BK-Level-VI](#) [TR30RDM180-02G03-BE-BK-Level-VI](#)  
[TR30RDM090-02G12-BK-BK-Level-VI](#) [TR30RDM240-11G13-BK-BK-Level-VI](#) [TR30RDM120-48G11-BE-BK-Level-VI](#)  
[TR30RDM050-36G02-BK-BK-Level-VI](#) [TR30RDM120-11G12-RD-BK-Level-VI](#) [TR30RDM240-49G13-BE-BK-Level-VI](#)  
[TR30RDM120-01G01-BK-BK-Level-VI](#) [TR30RDM050-35G12-RD-BK-Level-VI](#) [TR30RDM240-49G02-RD-BK-Level-VI](#)  
[TR30RDM120-39G03-BE-BK-Level-VI](#) [TR30RDM120-02G03-BK-BK-Level-VI](#) [TR30RDM180-11G02-RD-BK-Level-VI](#)  
[TR30RDM120-40G01-RD-BK-Level-VI](#) [TR30RDM120-11G03-BE-BK-Level-VI](#) [TR30RDM050-01G02-BK-BK-Level-VI](#)  
[TR30RDM240-11G01-RD-BK-Level-VI](#) [TR30RDM150-12G02-RD-BK-Level-VI](#) [TR30RDM090-02G01-RD-BK-Level-VI](#)  
[TR30RDM240-35G03-RD-BK-Level-VI](#) [TR30RDM180-01G11-BK-BK-Level-VI](#) [TR30RDM090-11G03-BK-BK-Level-VI](#)

[TR30RDM120-48G13-BE-BK-Level-VI](#) [TR30RDM150-11G03-RD-BK-Level-VI](#) [TR30RDM090-12G11-RD-BK-Level-VI](#)  
[TR30RDM090-01G03-BK-BK-Level-VI](#) [TR30RDM120-ASUE-11G02-BK-BK-Level-VI](#) [TR30RDM240-01G12-BE-BK-](#)  
[Level-VI](#) [TR30RDM050-02G12-BE-BK-Level-VI](#) [TR30RDM240-36G02-RD-BK-Level-VI](#) [TR30RDM150-12G13-BK-BK-](#)  
[Level-VI](#) [TR30RDM150-11G13-RD-BK-Level-VI](#) [TR30RDM180-12G12-BK-BK-Level-VI](#) [TR30RDM180-11G11-BK-BK-](#)  
[Level-VI](#) [TR30RDM120-36G13-RD-BK-Level-VI](#)