

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture PENETRATING OIL FG

Registration number -

Synonyms None.

Product code BDS000597AE

Issue date 13-June-2022

Version number 1.0

Revision date 13-June-2022

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Lubricants

Uses advised against None known.

1.3. Details of the supplier of the safety data sheet

Company name CRC Industries UK Ltd.

Address
Wylids Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom

Telephone +44 1278 727200

Fax +44 1278 425644

E-mail hse.uk@crcind.com

Website www.crcind.com

Company name CRC Industries Europe bv

Address
Touwslagerstraat 1
9240 Zele
Belgium

Telephone +32(0)52/45.60.11

Fax +32(0)52/45.00.34

E-mail hse@crcind.com

Website www.crcind.com

1.4. Emergency telephone number Tel.:(+44)(0)1278 72 7200 (office hours: 9-17h GMT)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

Physical hazards

Aerosols

Category 1

H222 - Extremely flammable aerosol.
H229 - Pressurized container: May burst if heated.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Hazard pictograms



Signal word

Danger

Hazard statements

H222 Extremely flammable aerosol.
H229 Pressurized container: May burst if heated.

Precautionary statements

Prevention

P102 Keep out of reach of children.
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 Do not spray on an open flame or other ignition source.
P251 Do not pierce or burn, even after use.

Response

Not assigned.

Storage

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Disposal

Not assigned.

Supplemental label information EUH066 - Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII. The product does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

Mixture

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	Index No.	Notes
Hydrocarbons, C11-13, n-alkanes, isoalkanes, cyclics, < 2% aromatics	25 - 50	- 920-901-0	01-2119456810-40	-	
Classification: Asp. Tox. 1;H304					
White mineral oil	10 - 25	8042-47-5 232-455-8	01-2119487078-27	-	
Classification: -					

List of abbreviations and symbols that may be used above

#: This substance has been assigned Union workplace exposure limit(s).
ATE: Acute toxicity estimate.
M: M-factor
PBT: persistent, bioaccumulative and toxic substance.
vPvB: very persistent and very bioaccumulative substance.
All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition comments The full text for all H-statements is displayed in section 16.

SECTION 4: First aid measures

General information

Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation If symptoms develop move victim to fresh air. Get medical attention if symptoms persist.
Skin contact Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact Rinse with water. Get medical attention if irritation develops and persists.
Ingestion In the unlikely event of swallowing contact a physician or poison control centre. Rinse mouth. Do not induce vomiting without advice from poison control center. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.

4.2. Most important symptoms and effects, both acute and delayed

Exposure may cause temporary irritation, redness, or discomfort.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

General fire hazards

Extremely flammable aerosol. Will burn if involved in a fire.

5.1. Extinguishing media

Suitable extinguishing media Foam. Dry chemicals. Carbon dioxide (CO₂).

Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
5.2. Special hazards arising from the substance or mixture	Contents under pressure. Pressurised container may explode when exposed to heat or flame. During fire, gases hazardous to health may be formed.
5.3. Advice for firefighters	
Special protective equipment for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Special fire fighting procedures	Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Containers should be cooled with water to prevent vapour pressure build up. For massive fire in cargo area, use unmanned hose holder or monitor nozzles, if possible. If not, withdraw and let fire burn out.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials. In the event of fire and/or explosion do not breathe fumes.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures	
For non-emergency personnel	Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing.
For emergency responders	Keep unnecessary personnel away. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
6.2. Environmental precautions	Avoid discharge into drains, water courses or onto the ground.
6.3. Methods and material for containment and cleaning up	Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil etc) away from spilled material. The product is immiscible with water and will spread on the water surface. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.
6.4. Reference to other sections	For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling	Pressurised container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. All equipment used when handling the product must be grounded. Do not re-use empty containers. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.
7.2. Conditions for safe storage, including any incompatibilities	Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store away from incompatible materials (see Section 10 of the SDS). Storage class (TRGS 510): 2B (Aerosol dispensers and lighters)
7.3. Specific end use(s)	Not available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters	
Occupational exposure limits	No exposure limits noted for ingredient(s).
Biological limit values	No biological exposure limits noted for the ingredient(s).
Recommended monitoring procedures	Follow standard monitoring procedures.

Derived no effect levels (DNELs)

General Population

Components	Value	Assessment factor	Notes
White mineral oil (CAS 8042-47-5)			
Long-term, Systemic, Dermal	93 mg/kg bw/day		
Long-term, Systemic, Inhalation	35 mg/m3		

Workers

Components	Value	Assessment factor	Notes
White mineral oil (CAS 8042-47-5)			
Long-term, Systemic, Dermal	220 mg/kg bw/day		
Long-term, Systemic, Inhalation	160 mg/m3		

Predicted no effect concentrations (PNECs)

Components	Value	Assessment factor	Notes
White mineral oil (CAS 8042-47-5) Secondary poisoning	17 g/kg	300	Oral

8.2. Exposure controls

Appropriate engineering controls

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

General information

Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.

Eye/face protection

Wear safety glasses with side shields (or goggles). Use eye protection conforming to EN 166.

Skin protection

- Hand protection

When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Nitrile gloves are recommended. Suitable gloves can be recommended by the glove supplier.

- Other

Not available.

Respiratory protection

In case of insufficient ventilation, wear suitable respiratory equipment. Chemical respirator with organic vapour cartridge. (Filter type AX)

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

Hygiene measures

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

Environmental exposure controls

Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. Fume scrubbers, filters or engineering modifications to the process equipment may be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state

Liquid.

Form

Aerosol.

Colour

Colourless.

Odour

Characteristic odor.

Odour threshold

Not available.

pH

Not applicable.

Melting point/freezing point

Not available.

Initial boiling point and boiling range

Not available.

Flash point

< 0 °C (< 32.0 °F)

Evaporation rate

Not applicable.

Flammability (solid, gas)

Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)

Not available.

Flammability limit - upper (%)

Not available.

Vapour pressure

1620.1 hPa estimated

Vapour density

Not available.

Relative density

0.8 g/cm³ at 20°C

Solubility(ies)

Solubility (water)

Insoluble in water

Auto-ignition temperature

> 200 °C (> 392 °F)

Decomposition temperature

Not available.

Viscosity

Not available.

Explosive properties	Not explosive.
Oxidising properties	Not oxidising.
9.2. Other information	
Heat of combustion (NFPA 30B)	4.93 kJ/g estimated
Particle size	Not applicable
VOC	541.8 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid	Avoid high temperatures.
10.5. Incompatible materials	Strong oxidising agents.
10.6. Hazardous decomposition products	Carbon oxides.

SECTION 11: Toxicological information

General information Occupational exposure to the substance or mixture may cause adverse effects.

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Eye contact	Based on available data, the classification criteria are not met.
Skin contact	Based on available data, the classification criteria are not met.
Ingestion	May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.

Symptoms Exposure may cause temporary irritation, redness, or discomfort.

11.1. Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Components	Species	Test Results
White mineral oil (CAS 8042-47-5)		
Acute		
Dermal		
LD50	Rabbit	> 2000 mg/kg > 5.001 mg/kg
Inhalation		
LC50	Rat	> 5.01 mg/l
Oral		
LD50	Rat	> 5000 mg/kg > 5.001 mg/kg

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory sensitisation Based on available data, the classification criteria are not met.

Skin sensitisation Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Reproductive toxicity Based on available data, the classification criteria are not met.

Specific target organ toxicity - single exposure Based on available data, the classification criteria are not met.

Specific target organ toxicity - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Not likely, due to the form of the product.

Mixture versus substance information Not available.

SECTION 12: Ecological information

12.1. Toxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
12.2. Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
12.3. Bioaccumulative potential	
Partition coefficient n-octanol/water (log Kow)	
Hydrocarbons, C11-13, n-alkanes, isoalkanes, cyclics, aromatics	< 2% > 4
Bioconcentration factor (BCF)	Not available.
12.4. Mobility in soil	No data available.
12.5. Results of PBT and vPvB assessment	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.
12.6. Other adverse effects	The product contains volatile organic compounds which have a photochemical ozone creation potential. GWP: 2
12.7. Additional information	None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods	
Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Dispose of contents/container in accordance with local/regional/national/international regulations.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Hazard No. (ADR)	Not available.
Tunnel restriction code	D
14.4. Packing group	Not available.
14.5. Environmental hazards	No.
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

RID

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
14.4. Packing group	Not available.
14.5. Environmental hazards	No.
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

ADN

14.1. UN number	UN1950
------------------------	--------

14.2. UN proper shipping name	AEROSOLS
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
14.4. Packing group	Not available.
14.5. Environmental hazards	No.
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

IATA

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
14.4. Packing group	Not available.
14.5. Environmental hazards	No.
ERG Code	10L
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

Other information

Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.

IMDG

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
14.4. Packing group	Not available.
14.5. Environmental hazards	
Marine pollutant	No.
EmS	F-D, S-U
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not established.

ADN; ADR; IATA; IMDG; RID



SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Retained direct EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended

Not listed.

Regulation (EU) 2019/1021 On persistent organic pollutants (recast), as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended

Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended

Not listed.

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA

Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended

Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended

Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended

Not listed.

Other regulations

The product is classified and labelled in accordance with Regulation (EC) 1272/2008 (CLP Regulation) as amended. This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006, as amended.

Follow national regulation for work with chemical agents in accordance with Directive 98/24/EC, as amended.

15.2. Chemical safety assessment

No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

ADN: European Agreement Concerning the International Carriage of Dangerous Goods by Inland Waterways.

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.

ADR: European Agreement Concerning the International Carriage of Dangerous Goods by Road.

AGW: Occupational threshold limit value (Arbeitsplatzgrenzwert – Germany).

ATE: Acute Toxicity Estimate according to REGULATION (EC) No 1272/2008 (CLP).

CAS: Chemical Abstract Service.

Ceiling: Short Term Exposure Limit Ceiling value.

CEN: European Committee for Standardization.

CLP: Classification, Labeling and Packaging REGULATION (EC) No 1272/2008 on classification, labeling and packaging of substances and mixtures.

GWP: Global Warming Potential.

IATA: International Air Transport Association.

IBC Code: International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk.

IMDG: International Maritime Dangerous Goods.

MAC: Maximum Allowed Concentration.

MAK: Threshold limit values Germany (Maximale Arbeitsplatzkonzentration - DFG).

MARPOL: International Convention for the Prevention of Pollution from Ships.

PBT: Persistent, bioaccumulative and toxic.

REACH: Registration, Evaluation and Authorization of Chemicals (REGULATION (EC) No 1907/2006 concerning Registration, Evaluation Authorization and Restriction of Chemicals).

RID: Regulations concerning the international carriage of dangerous goods by rail (Règlement International concernant le transport de marchandises dangereuses par chemin de fer).

RID: Regulations concerning the International Carriage of Dangerous Goods by Rail.

STEL: Short term exposure limit.

TLV: Threshold Limit Value.

TWA: Time Weighted Average.

VLE: Exposure Limit Value.

VME: Exposure Average Value.

VOC: Volatile organic compounds.

vPvB: Very persistent and very bioaccumulative.

STEL: Short-term Exposure Limit.

References

Not available.

Information on evaluation method leading to the classification of mixture

The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.

Full text of any H-statements not written out in full under Sections 2 to 15

H304 May be fatal if swallowed and enters airways.

Revision information

None.

Training information

Follow training instructions when handling this material.

Disclaimer

CRC Industries Europe UK Limited cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.