



MYRRA - SERIE 44000 EI 38-13,6 3,2 VA

SERIE 44000 EI 38-13,6 3,2 VA Primary Voltage 117 V

Secondary Protection mA	Reference	Secondary Voltage V	Secondary Current mA	No-load Voltage V	Ambient, Temperature C	Rating VA
630	44205	6	533	8	T 70 B	3,2
400	44206	9	356	12	T 70 B	3,2
315	44207	12	267	16	T 70 B	3,2
250	44208	15	213	20	T 70 B	3,2
200	44209	18	178	24,1	T 70 B	3,2
160	44210	24	133	32,1	T 70 B	3,2
315	44211	2 x 6	2 x 267	2 x 8	T 70 B	3,2
200	44212	2 x 9	2 x 178	2 x 12	T 70 B	3,2
160	44213	2 x 12	2 x 133	2 x 16	T 70 B	3,2
125	44214	2 x 15	2 x 107	2 x 20	T 70 B	3,2
100	44215	2 x 18	2 x 89	2 x 24	T 70 B	3,2
80	44216	2 x 24	2 x 67	2 x 32,1	T 70 B	3,2

SERIE 44000 EI 38-13,6 3,2 VA Primary Voltage 230 V

Secondary Protection mA	Reference	Secondary Voltage V	Secondary Current mA	No-load Voltage V	Ambient, Temperature C	Rating VA
630	44193	6	533	8	T 70 B	3,2
400	44194	9	356	12	T 70 B	3,2
315	44195	12	267	16	T 70 B	3,2
250	44196	15	213	20	T 70 B	3,2
200	44197	18	178	24,1	T 70 B	3,2
160	44198	24	133	32,1	T 70 B	3,2
315	44199	2 x 6	2 x 267	2 x 8	T 70 B	3,2
200	44200	2 x 9	2 x 178	2 x 12	T 70 B	3,2

160	44201	2 x 12	2 x 133	2 x 16	T 70 B	3,2
125	44201	2 x 15	2 x 107	2 x 20	T 70 B	3,2
100	44203	2 x 18	2 x 89	2 x 24	T 70 B	3,2
80	44204*	2 x 24	2 x 67	2 x 32,1	T 70 B	3,2

- * Vacuum filling
- * Two compartments bobbins
- * Self-extinguishing plastics UL 94 VO
- * Degree of protection IP 00
- * 150 grams weight
- * Resin class B CEI 85 (20 000h testing to CEI 126)
- * Fuse protection on secondary side (see diagram) to be assumed by customer
- * Insulation voltage 4 KV (6 KV MYRRA test)
- * 30 V and 36 V model are VDE EN 60742 certified (Production on request)
- * 100% tested production
- * Certification : CCA procedure on request

* To be noted : 2 * 24 V model is non approved. Protection transformers according to EN 60742 circuit isolation transformer.

