







Features

-  **DS1005:** 10/100BaseT Ethernet port
DS1015: Ethernet, GPRS*, Wi-Fi*
-  8 digital isolated inputs that work with card readers too!
-  6 high-power (10A/30VDC) relays
-  1 RS232/485 port (on a terminal block)
-  IP68-compliant, -30C to +80C range
-  Free remote I/O application available

*optional



About

With eight opto-isolated sensor inputs, six high-power relay outputs, and one simple RS232/485 port, the DS1005 and DS1015 are a great fit for industrial and building automation, security, safety, and access control applications.

The DS1005 offers the Ethernet interface only. The DS1015 features Ethernet, as well as optional Wi-Fi and GPRS.

Unlike many “remote I/O” products, the capabilities of the DS1005 and DS1015 are not limited to just relaying I/O data to a central server. Programmability in Tibbo BASIC means you can create systems where intelligent decisions are taken in real-time by the device itself.

The DS1005 and DS1015 are especially suitable for access control applications: Four of the eight sensor inputs can be used to handle up to two card readers (two inputs per reader), which leaves four sensor inputs for connecting to a door switch, exit button, etc.

The devices come preloaded with an open-source application for remote control/monitoring of the device’s inputs and relays through a web-browser or Tibbo’s AggreGate device management system. This application can easily be customized for any functionality desired.

Specifications

- Network side — NB1000 (DS1005) or NB1010 (DS1015) board:
 - Based on the EM1000 module (DS1005) or compatible with it (DS1015);
 - Optional GA1000 Wi-Fi add-on (DS1015 only);
 - Optional Telit GC864 GPRS modem (DS1015);
 - 10/100BaseT, auto-MDIX Ethernet port;
 - 1024KB flash for firmware, application, and data;
 - 2KB EEPROM for data storage;
 - RTC with backup supercapacitor;
 - Built-in buzzer;
 - 11 status LEDs;
 - Power: 10-18V;
 - Firmware is upgradeable through the serial port or network;
- Interface side — IB1005 board:
 - 8 opto-isolated sensor inputs, four of which can be used to connect up to two Wiegand or clock/data readers;
 - 6 high-power (10A/30VDC) relays;
 - 1 RS232/485 port;
 - 8 status LEDs.
- Dimensions: 91x104x99mm (excluding secondary cover).
- Extruded-profile aluminum body.
- IP68 compliant (when used with secondary cover).
- Operating temperature -30 to +80 degrees C.
- CE- and FCC-certified.

continued on next page

Specifications (continued)

- Included accessories:
 - Wi-Fi antenna (with DS1015G only)
 - GPRS antenna (with DS1015C and DS1015GC)
 - DS1000 waterproof kit with secondary cover, cable glands, screws
 - DMK1000 DIN rail mounting kit
- TB1005 test board
- WAS-P0040 serial cable for firmware upgrades
- Optional Accessories:
 - 12V/1A adaptor: APR-P0008 (US), APR-P0009 (EU), APR-P0010 (UK)
 - WAS-1499 straight Ethernet cable (for this device can be used as crossover cable too)

Programming

Platform Objects

- Sock — socket comms (up to 16 UDP, TCP, and HTTP sessions).
- Net — controls Ethernet port.
- Ser — in charge of serial channels.
- Ssi — up to 4 serial synchronous interface channels (for SPI, I2C...).
- Io — handles I/O lines, ports, and interrupts.
- Rtc — keeps track of date and time.
- Fd — manages flash memory file system and direct sector access.
- Stor — provides access to the EEPROM.
- Romfile — facilitates access to resource files (fixed data).
- Pppoe — accesses the Internet over an ADSL modem.
- Ppp — accesses the Internet over a serial modem (GPRS, etc.).
- Pat — “plays” patterns on five status LED pairs.
- Beep — generates buzzer patterns.
- Button — monitors the setup button.
- Sys — in charge of general device functionality.

Function Groups:

String functions (27 in total!), date/time conversion functions (8), encryption/hash calculation functions (AES128, RC4, MD5, SHA-1), and more.

Variable Types:

Byte, char, integer (word), short, dword, long, real, string, plus user-defined arrays and structures.

Tibbo Integrated Development Environment (TIDE)

All BASIC-programmable Tibbo devices are provided with free TIDE software.

Code in Comfort

Enjoy a modern code editor supporting syntax highlighting, context help, code hinting, and auto-completion.

Debug with Ease

Set breakpoints, watch variables, inspect the stack, step through your code... the built-in debugger in Tibbo IDE provides all the tools for fast and convenient debugging.

Our debugger does not rely on any special hardware like an ICE machine or a JTAG board. Simply connect your Tibbo device to the Ethernet, select it in the IDE, and you are all set!

For more information on TIDE, see <http://basic.tibbo.com/product/tide.html>