

EDLC 3.0V 5F




FEATURES

- Electric double layer capacitor
- Higher power density with ultra low ESR
- Semi-permanent, quick charge and discharge than batteries
- Suitable for short-term peak power assistance application
- UL and ISO/TS certificated, RoHS compliant
- Radial design with lead terminal type



DIMENSIONS



Dimensions in mm			
D +1.0 Max	L ± 1.5	d ± 0.1	P ± 0.5
Φ10.0	20.0	Φ0.6	5.0

This drawing is not to be scaled.

SPECIFICATIONS

Part Number	Rated Voltage, V_R (V)	Rated Capacitance (F)	AC ESR 1kHz (mΩ)	DC IR (mΩ)	Maximum Current (A)	Leakage Current (mA)	Stored Energy (J)	Dimension D x L (mm)	Weight (g)
VEC 3R0 505 QG	3.0	5.	65.00	100.00	5.	0.015	22.5	10.0 x 20.0	2.1

* Maximum Current: 1 second discharge to $\frac{1}{2} \cdot V_R$

* Leakage Current: After 72hours at V_R and 25°C

Item	Characteristics	Remarks
Rated Voltage(V_R)	3.0V	
Capacitance Tolerance	-10 ~ 30%	
Operating Temperature ($T_{min} \sim T_{max}$)	-40 ~ +65°C	$ \Delta cap \leq 30\%$ of initial value at 25°C $ \Delta ESR \leq 100\%$ of specified value at 25°C After 1,000 hours application of V_R at T_{max}
Storage Temperature	-40 ~ 70°C	
Cycle Life	500,000 cycles	$ \Delta cap \leq 30\%$ of initial value at 25°C $ \Delta ESR \leq 100\%$ of specified value at 25°C Cycles from V_R to $\frac{1}{2} \cdot V_R$ under constant current at 25°C
Shelf Life	2 years	$ \Delta cap \leq 10\%$ of initial value at 25°C $ \Delta ESR \leq 50\%$ of specified value at 25°C Without electrical charge under T_{max}