





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		E7	REVISE PER ECR-14-005944	23APR2014	GRZ JL



SECTION A-A
SCALE : 20:1


METRIC

- 1
- PRODUCT PROVIDED IN STRIP FORM ON REELS; BREAKS MAY BE PRESENT.
- 2
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- E6 3
- CRIMP WIDTH: .110 F (AMPLIVAR TYPE)
CRIMP HEIGHT (±.002)=(TOTAL CMA +10,700)/193,400

CRIMP WIDTH: .140 F (AMPLIVAR TYPE)
CRIMP HEIGHT (±.002)=(TOTAL CMA +11,100)/233,300

GENERAL APPLICATION GUIDELINES MUST BE FOLLOWED AS SPECIFIED IN CATALOG # 82221
FOR APPLICATOR INFORMATION CALL: 1-800-722-1111
FOR PRODUCT INFROMATION CALL: 1-800-522-6752
- 4
- NOT FOR USE WITH ALUMINUM MAGNET WIRE,
USE WITH COPPER MAGNET WIRE ONLY

TIN	62306-2
NONE	4 62306-1
FINISH	Part No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 31JAN06	 TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK G.D.PORTA			
		APVD G.D.PORTA	NAME SPLICE, AMPLIVAR 1500-5000 CMA		
		PRODUCT SPEC -			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-2003	SIZE A3	CAGE CODE 00779	DRAWING NO C-62306
MATERIAL REF 0.51±0.03 [.020±.001] BRASS		WEIGHT -	RESTRICTED TO -		
FINISH TIN PL.		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	REV E7