



RoHS

# Parts Drawing




REVISIONS				
SYM	ECN No.	MODIFICATION	DATE	ISSUED

- Note:
- Material:
    - Housing: BLACK G/F,UL94v-0
    - Contact: copper alloy,t=0.25mm
    - Shell: copper/Ferroalloy alloy,t=0.30mm
  - Specification:
    - Current rating:5.0A Max.
    - Dielectric withstanding voltage: 100 V(ac) for 1 min.
    - Contact resistance: 30 mΩ Max.
    - Insulation resistance: 100 MΩ Min.
    - Total mating force: 3.57 Kgf Max.
    - Total unmating force: 1.0 Kgf Min.
  - Finish:
    - Contact: Plated Golt in Mating Area:  
Tin On Solder Talls  
Shell: Nickel Plating
  - Environmental:
    - Temperature range: -55°C~85°C

- PART ON:  
907-222AXXX1Y1XX
- 电镀规格: 02, 镀金1u" 04, 镀金3u" 07, 镀金15u" 08, 镀金30u"
  - 端子材质: 1, 青铜 2, 磷铜
  - 端子规格: D, 90度 Y, 180度 S, SMT贴片
  - 塑胶形态: 1, 双层短体 2, 双层半包
  - 塑胶颜色: 01, 白色 02, 黑色 03, 本色
  - 塑胶材质: 1, PET 2, LCP 3, PA6T 4, PPA 5, PA6T
  - 对称方向: A, 正向 B, 反向
  - 外壳材质: 1, 铁壳 2, 铜壳
  - 插口类型: 1, 有边平弹 2, 无边平弹
  - 外壳脚型: 1, 弯脚 2, 直脚 3, 无脚
  - 类别: 双层系列



RBCOMMENDBD P.C.B PATTBRN LAY OUT



DRAWN	<b>深圳市精拓金电子有限公司</b>			
CHECKED	TITLE	PART NO.		
APPROVED	USB AF 10.5短体双层无脚 无边	SEE PART ON		
		DRAWING NO.		
		R907322A1021Y102		
	UNIT	TOLERANCE	SCALE	SHEET
	mm	.XXX±.10, .XX±.25, X±.38, ANG±15°	1:1	1 OF 1
			SIZE	REV.
			A4	X1