

FatMax®



FatMax® Parallel

- ➔ Large diameter handle offers great torque needed for driving wood screws
- ➔ Colour coded ends make it easy to identify the correct screwdriver for each screw type
- ➔ Smooth domed end for fast spinning action – speed and comfort
- ➔ Shot blasted tips ensure improved torque and corrosion protection
- ➔ Soft grip handle – perfect combination of great grip plus reduces fatigue
- ➔ Chrome vanadium steel bar allows for high torque and reduces the chance of tip breakage
- ➔ Handle moulded direct to bar virtually unbreakable bond. Highly reliable and providing an extra long life

STANLEY	<u>64-978</u>	<u>64-979</u>	<u>64-983</u>
Parallel tip width (mm)	3	3	3.5
Blade length (mm)	50	150	75
STANLEY	<u>64-984</u>	<u>65-006</u>	<u>65-008</u>
Parallel tip width (mm)	3.5	2.5	3
Blade length (mm)	100	50	100
STANLEY	<u>65-017</u>	<u>65-093</u>	<u>65-094</u>
Parallel tip width (mm)	4	4	5.5
Blade length (mm)	100	150	150
STANLEY	<u>65-096</u>	<u>65-097</u>	<u>65-476</u>
Parallel tip width (mm)	6.5	6.5	5.5
Blade length (mm)	150	200	125