

## IE-SW-BL08T-8TX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



- Variations with 5 or 8 ports
- Variations for Gigabit Ethernet
- Sturdy metal housing
- Compact design
- Two redundant power inputs 12/24/48 V DC
- Variations with copper and fibre-optic interface (multimode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

### General ordering data

Version	Network switch, unmanaged, Fast Ethernet, Number of ports: 8x RJ45, IP30, -40 °C...75 °C
Order No.	<a href="#">1286560000</a>
Type	IE-SW-BL08T-8TX
GTIN (EAN)	4050118076967
Qty.	1 pc(s).

Creation date September 16, 2022 3:01:38 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

## IE-SW-BL08T-8TX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	115 mm	Height (inches)	4.528 inch
Width	50 mm	Width (inches)	1.969 inch
Net weight	275 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	9229992a-00b9-4096-8962-200a7f3
------------	----------------	------	---------------------------------

## EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 Ghz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA IIC T4 Gc
Free fall	According to IEC 60068-2-32	Safety standard	UL508
Ship use	DNV-GL	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

## Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

## Guarantee

Time interval	5 years
---------------	---------

## Interfaces

Function DIP switch	1x for enabling/disabling the broadcast storm protection	LED indicator	PWR1, PWR2, 10/100M (TP-Port)
Number of ports	8x RJ45	RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port

Creation date September 16, 2022 3:01:38 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

2

## IE-SW-BL08T-8TX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	2,428,212 h

## Power supply

Connection type	1 removable 4-pin terminal block	
Current consumption	0.13 A at 24 V	
Overload current protection	1.1 A	
Reverse polarity protection	Available	
Voltage supply	12/24/48 V DC, 2 redundant inputs	
Voltage supply range	Voltage type	DC
	Voltage, min.	9.6 V
	Voltage, max.	60 V

## Switch characteristics

Bandwidth backplane	1.6 Gbps	MAC table size	2 K
Packet buffer size	768 Kbit		

## Technical data

Housing main material	Aluminium	Protection degree	IP30
Speed	Fast Ethernet	Switch	unmanaged
Type of mounting	DIN rail, Panel (with optional mounting kit)		

## Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3x for flow control		

## Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ECLASS 9.0	19-17-01-06
ECLASS 9.1	19-17-01-06	ECLASS 10.0	19-17-04-02
ECLASS 11.0	19-17-04-02	ECLASS 12.0	19-17-04-02

## IE-SW-BL08T-8TX


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197
Certificate no. (cULusEX)	E223527

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">DNV certificate</a> <a href="#">ATEX certificate</a> <a href="#">KC certificate</a> <a href="#">EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Product Change Notification	<a href="#">Product Change Notification IE-SW-BL08-series</a>
User Documentation	<a href="#">Hardware Installation Guide</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1286560000](#)