

March 2017

© Diodes Incorporated

40V NPN SMALL SIGNAL TRANSISTOR IN SOT23

Features


- Epitaxial Planar Die Construction
- Complementary PNP Type Available (MMBT3906)
- Ideal for Medium Power Amplification and Switching
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Mechanical Data


- Case: SOT23
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.008 grams (Approximate)







Device Symbol



Top View Pin-Out


Ordering Information (Notes 4 & 5)

Product	Status	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
MMBT3904-7-F	Active	AEC-Q101	K1N	7	8	3,000
MMBT3904Q-7-F	Active	Automotive	K1N	7	8	3,000
MMBT3904Q-13-F	Active	Automotive	K1N	13	8	10,000
MMBT3904-13-F	Active	AEC-Q101	K1N	13	8	10,000

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen and Antimony free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Automotive, AEC-Q101 and standard products are electrically and thermally the same, except where specified. For more information, please refer to http://www.diodes.com/quality/product_compliance_definitions/.
- 5. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information



$$\begin{split} &K1N = Product\ Type\ Marking\ Code \\ &YM = Date\ Code\ Marking \\ &Y\ or\ \overline{Y} = Year\ (ex:\ D=2016) \\ &M\ or\ \overline{M} = Month\ (ex:\ 9=September) \end{split}$$

Date Code Key

Year	2014		2015	2016		2017	2018		2019	2020		2021
Code	В		С	D		Е	F		G	Н		1
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V_{CBO}	60	V
Collector-Emitter Voltage	V_{CEO}	40	V
Emitter-Base Voltage	V_{EBO}	6	V
Collector Current	Ic	200	mA

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit	
Power Dissipation	(Note 6)	ь	310	mW	
Power Dissipation	(Note 7)	- P _D	350		
Thormal Posistanas, Junction to Ambient	(Note 6)	В	403	°C/W	
Thermal Resistance, Junction to Ambient	(Note 7)	R _{0JA}	357	C/VV	
Thermal Resistance, Junction to Leads (Note 8)		$R_{\theta JL}$	350	°C/W	
Operating and Storage Temperature Range		$T_{J,T_{STG}}$	-55 to +150	°C	

ESD Ratings (Note 9)


Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	400	V	С

Notes:

- 6. For a device mounted on minimum recommended pad layout 1oz copper that is on a single-sided FR4 PCB; device is measured under still air For a device mounted of minimum recommended pad layout 102 copper that is conditions whilst operating in a steady-state.
 Same as Note 6, except the device is mounted on 15 mm x 15mm 1oz copper.
 Thermal resistance from junction to solder-point (at the end of the leads).
 Refer to JEDEC specification JESD22-A114 and JESD22-A115.



Thermal Characteristics and Derating Information





Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Max	Unit	Test Condition
OFF CHARACTERISTICS					
Collector-Base Breakdown Voltage	BV _{CBO}	60	_	V	$I_C = 10\mu A, I_E = 0$
Collector-Emitter Breakdown Voltage (Note 10)	BV_{CEO}	40	_	V	$I_C = 10 \text{mA}, I_B = 0$
Emitter-Base Breakdown Voltage	BV _{EBO}	6.0	_	V	$I_E = 10\mu A, I_C = 0$
Collector Cut-Off Current	I _{CEX}	_	50	nA	$V_{CE} = 30V, V_{EB(OFF)} = 3.0V$
Base Cut-Off Current	I_{BL}	_	50	nA	$V_{CE} = 30V, V_{EB(OFF)} = 3.0V$
Emitter Base Cut-Off Current	I _{EBO}	_	50	nA	$V_{EB} = 6V$
Collector-Base Cut-Off Current	I _{CBO}	_	50	nA	V _{CB} = 48V
ON CHARACTERISTICS (Note 10)					
DC Current Gain	h _{FE}	40 70 100 60	— 300 —	_	$I_C = 100\mu A, V_{CE} = 1.0V$ $I_C = 1.0mA, V_{CE} = 1.0V$ $I_C = 10mA, V_{CE} = 1.0V$ $I_C = 50mA, V_{CE} = 1.0V$
		30			I _C = 100mA, V _{CE} = 1.0V
Collector-Emitter Saturation Voltage	V _{CE(SAT)}	_	0.20 0.30	V	I _C = 10mA, I _B = 1.0mA I _C = 50mA, I _B = 5.0mA
Base-Emitter Saturation Voltage	V _{BE(SAT)}	0.65 —	0.85 0.95	V	$I_C = 10mA, I_B = 1.0mA$ $I_C = 50mA, I_B = 5.0mA$
SMALL SIGNAL CHARACTERISTICS					
Output Capacitance	C _{OBO}	_	4.0	pF	$V_{CB} = 5.0V$, $f = 1.0MHz$, $I_E = 0$
Input Capacitance	C _{IBO}		8.0	pF	$V_{EB} = 0.5V$, $f = 1.0MHz$, $I_{C} = 0$
Input Impedance	h _{IE}	1.0	10	kΩ	
Voltage Feedback Ratio	h _{RE}	0.5	8.0	x 10 ⁻⁴	$V_{CE} = 10V, I_{C} = 1.0mA,$
Small Signal Current Gain	h _{FE}	100	400	_	f = 1.0kHz
Output Admittance	h _{OE}	1.0	40	μS	
Current Gain-Bandwidth Product	f⊤	300	_	MHz	$V_{CE} = 20V$, $I_C = 10mA$, $f = 100MHz$
Noise Figure	NF	_	5.0	dB	$V_{CE} = 5.0V$, $I_{C} = 100\mu A$, $R_{S} = 1.0k\Omega$, $f = 1.0kHz$
SWITCHING CHARACTERISTICS					
Delay Time	t _D	_	35	ns	$V_{CC} = 3.0V, I_{C} = 10mA,$
Rise Time	t _R	_	35	ns	$V_{BE(OFF)} = -0.5V, I_{B1} = 1.0mA$
Storage Time	ts	_	200	ns	$V_{CC} = 3.0V, I_{C} = 10mA,$
Fall Time	t _F	_	50	ns	$I_{B1} = I_{B2} = 1.0 \text{mA}$

Note: 10. Measured under pulsed conditions. Pulse width \leq 300 μ s. Duty cycle \leq 2%.



Typical Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)





Fig. 1 Typical DC Current Gain vs. Collector Current






Fig. 2 Typical Collector-Emitter Saturation Voltage vs. Collector Current





Fig. 4 Typical Capacitance Characteristics



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23




SOT23							
Dim	Min	Max	Тур				
Α	0.37	0.51	0.40				
В	1.20	1.40	1.30				
С	2.30	2.50	2.40				
D	0.89	1.03	0.915				
F	0.45	0.60	0.535				
G	1.78	2.05	1.83				
Н	2.80	3.00	2.90				
J	0.013	0.10	0.05				
K	0.890	1.00	0.975				
K 1	0.903	1.10	1.025				
٦	0.45	0.61	0.55				
L1	0.25	0.55	0.40				
M	0.085	0.150	0.110				
а	0°	8°					
All	Dimens	ions in	mm				

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
V4	2.0



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

MMBT3904-7-F MMBT3904Q-7-F