

## D SUB MIXED FE 20 A SHORT CRIMP POWER CO



Image is for illustration purposes only. Please refer to product description.

Part number	09 69 182 7821
Specification	D SUB MIXED FE 20 A SHORT CRIMP POWER CO
HARTING eCatalogue	<a href="https://b2b.harting.com/09691827821">https://b2b.harting.com/09691827821</a>

### Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Crimp contact
Description of the contact	Straight Short version
Features	Tool setting: 5 for AWG 12 and 4 for AWG 14

### Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	2.5 ... 4 mm <sup>2</sup>
Conductor cross-section	AWG 14 ... AWG 12
Operating current	≤20 A
Contact resistance	≤1 mΩ
Stripping length	4.5 mm
Limiting temperature	-55 ... +155 °C
Insertion force	≤7 N
Withdrawal force	≈5 N
Performance level	3



Pushing Performance

## Technical characteristics

Mating cycles ≥50

---

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	0.2 µm Au
Material (locking)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead

---

## Commercial data

Packaging size	100
Net weight	1.81 g
Country of origin	Germany
European customs tariff number	85369010
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09691827821](#)