


Features:

- R Value extension of RMCF product
- Highly stable performance over time
- Power derating from 100% at 70°C to zero at 125°C
- E12 and E24 values
- Nickel barrier terminations
- RoHS compliant by means of exemption 7c-l
- Halogen free
- REACH compliant



Electrical Specifications							
Type/Code	Power Rating (W) @ 70°C	Maximum Working Voltage (V) ⁽¹⁾	Maximum Overload Voltage (V)	TCR (ppm/°C)	Ohmic Range (Ω) and Tolerance		
					1%	5%	10%
HMC0402	0.063	50	100	± 200	11M - 20M	-	
				± 400	22M - 100M		
HMC0603	0.1	50	100	± 200	11M - 20M	-	
				± 400	22M - 100M		
				± 500	-	110M - 1G	
HMC0805	0.125	150	300	± 200	11M - 20M	-	
				± 400	22M - 100M		
				± 500	-	110M - 500M	
				± 1000	-	510M - 1G	
				± 1500	-	1.2G - 10G	
HMC1206	0.25	200	400	± 200	11M - 20M	-	
				± 400	22M - 100M	30M - 100M	
				± 500	-	110M - 500M	
				± 1000	-	510M - 1G	
				± 1500	-	1.2G - 10G	
HMC1210	0.33	200	400	± 200	11M - 20M	-	11M - 20M
				± 400	22M - 100M		
HMC2010	0.75	200	400	± 200	11M - 20M		
				± 400	22M - 100M		
HMC2512	1	250	500	± 200	11M - 20M		
				± 400	22M - 100M		

(1) Lesser of $\sqrt{P \cdot R}$ or maximum working voltage.


Mechanical Specifications						
Type/Code	L Body Length	W Body Width	H Body Height	a Top Termination	b Bottom Termination	Unit
HMC0402	0.039 ± 0.002	0.020 ± 0.002	0.014 ± 0.002	0.008 ± 0.004	0.008 ± 0.004	inches
	1.00 ± 0.05	0.50 ± 0.05	0.35 ± 0.05	0.20 ± 0.10	0.20 ± 0.10	mm
HMC0603	0.063 ± 0.004	0.031 ± 0.004	0.018 ± 0.004	0.012 ± 0.008	0.012 ± 0.008	inches
	1.60 ± 0.10	0.80 ± 0.10	0.45 ± 0.10	0.30 ± 0.20	0.30 ± 0.20	mm
HMC0805	0.079 ± 0.008	0.049 ± 0.004	0.020 ± 0.004	0.016 ± 0.008	0.016 ± 0.008	inches
	2.00 ± 0.20	1.25 ± 0.10	0.50 ± 0.10	0.40 ± 0.20	0.40 ± 0.20	mm

Mechanical Specifications (cont.)						
Type/Code	L Body Length	W Body Width	H Body Height	a Top Termination	b Bottom Termination	Unit
HMC1206	0.122 ± 0.006	0.061 ± 0.004	0.022 ± 0.006	0.020 ± 0.010	0.020 ± 0.008	inches
	3.10 ± 0.15	1.55 ± 0.10	0.55 ± 0.15	0.50 ± 0.25	0.50 ± 0.20	mm
HMC1210	0.126 ± 0.008	0.102 ± 0.006	0.022 ± 0.004	0.020 ± 0.008	0.020 ± 0.008	inches
	3.20 ± 0.20	2.60 ± 0.15	0.55 ± 0.10	0.50 ± 0.20	0.50 ± 0.20	mm
HMC2010	0.197 ± 0.008	0.098 ± 0.006	0.022 ± 0.004	0.024 ± 0.010	0.020 ± 0.008	inches
	5.00 ± 0.20	2.50 ± 0.15	0.55 ± 0.10	0.60 ± 0.25	0.50 ± 0.20	mm
HMC2512	0.250 ± 0.008	0.126 ± 0.006	0.022 ± 0.004	0.024 ± 0.010	0.020 ± 0.008	inches
	6.35 ± 0.20	3.20 ± 0.15	0.55 ± 0.10	0.60 ± 0.25	0.50 ± 0.20	mm


Performance Characteristics		
Test	Test Condition (JIS C 5202)	Test Result
Long Term Stability	Nominal temperature & humidity for 1000 hours	± 0.5%
High Temperature Loading	15 VDC, 1.5 hour ON, 0.5 hour OFF, 1000 hours 70°C	± 3%
Resistance to Solder Heat	260°C ± 5°C, 10 seconds +1/-0	± 1%
Short Time Overload	5 seconds at maximum overload voltage	± 2%
Voltage Coefficient of Resistance	Per JIS C 5202	± 0.5%/V

Operating temperature range is -55°C to +125°C

Power Derating Curve:



Recommended Pad Layouts



Type/Code	A	B	C	Unit
HMC0402	0.020	0.018	0.024	inches
	0.50	0.45	0.60	mm
HMC0603	0.035	0.024	0.035	inches
	0.90	0.60	0.90	mm
HMC0805	0.047	0.028	0.051	inches
	1.20	0.70	1.30	mm
HMC1206	0.079	0.035	0.063	inches
	2.00	0.90	1.60	mm
HMC1210	0.079	0.035	0.110	inches
	2.00	0.90	2.80	mm
HMC2010	0.150	0.035	0.110	inches
	3.80	0.90	2.80	mm
HMC2512	0.193	0.063	0.138	inches
	4.90	1.60	3.50	mm

Recommended Solder Profile

This information is intended as a reference for solder profiles for Stackpole resistive components. These profiles should be compatible with most soldering processes. These are only recommendations. Actual numbers will depend on board density, geometry, packages used, etc., especially those cells labeled with “*”.

100% Matte Tin / RoHS Compliant Terminations

Soldering iron recommended temperatures: 330°C to 350°C with minimum duration.
Maximum number of reflow cycles: 3.


Wave Soldering

Description	Maximum	Recommended	Minimum
Preheat Time	80 seconds	70 seconds	60 seconds
Temperature Diff.	140°C	120°C	100°C
Solder Temp.	260°C	250°C	240°C
Dwell Time at Max.	10 seconds	5 seconds	*
Ramp DN (°C/sec)	N/A	N/A	N/A

Temperature Diff. = Difference between final preheat stage and soldering stage.

Convection IR Reflow

Description	Maximum	Recommended	Minimum
Ramp Up (°C/sec)	3°C/sec	2°C/sec	*
Dwell Time > 217°C	150 seconds	90 seconds	60 seconds
Solder Temp.	260°C	245°C	*
Dwell Time at Max.	30 seconds	15 seconds	10 seconds
Ramp DN (°C/sec)	6°C/sec	3°C/sec	*



RoHS Compliance

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union’s directive regarding “Restrictions on Hazardous Substances” (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

RoHS Compliance Status						
Standard Product Series	Description	Package / Termination Type	Standard Series RoHS Compliant	Lead-Free Termination Composition	Lead-Free Mfg. Effective Date (Std Product Series)	Lead-Free Effective Date Code (YY/WW)
HMC	High Value Thick Film Surface Mount Chip Resistor	SMD	YES(1)	100% Matte Sn over Ni	Jan-04	04/01

Note (1): RoHS Compliant by means of exemption 7c-l.

“Conflict Metals” Commitment

We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the “conflict region” of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.


Compliance to “REACH”

We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, “The Registration, Evaluation, Authorization and Restriction of Chemicals”, otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

Environmental Policy

It is the policy of Stackpole Electronics, Inc. (SEI) to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.

How to Order



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SEI Stackpole:

HMC0805JT50M0	HMC0402JT100M	HMC1206JT50M0	HMC1206JT500M	HMC0402JT50M0	HMC0603JT100M
HMC0805JT500M	HMC0402JT30M0	HMC0805JT100M	HMC0603JT50M0	HMC1206JT100M	HMC0402FT100M
HMC0603JT51M0	HMC0805JT27M0	HMC0805JT75M0	HMC2010JT27M0	HMC2512JT68M0	HMC2512JT75M0
HMC0402JT62M0	HMC0603JT200M	HMC0603JT91M0	HMC0805JT33M0	HMC0805KT1G20	HMC1206JT160M
HMC2010JT47M0	HMC2010JT82M0	HMC2512JT24M0	HMC0805JT43M0	HMC0805JT47M0	HMC0805KT75M0
HMC1206JT62M0	HMC1210JT100M	HMC1210JT82M0	HMC0603JT470M	HMC0805JT250M	HMC0805JT82M0
HMC1206KT150M	HMC1206KT1G00	HMC1210JT47M0	HMC2010JT24M0	HMC0402FT20M0	HMC0402FT22M0
HMC0402JT91M0	HMC0805JT24M0	HMC0805JT91M0	HMC2010JT33M0	HMC2512JT100M	HMC0402JT24M0
HMC0402JT51M0	HMC0603KT68M0	HMC0805JT390M	HMC0805JT5G00	HMC1206JT20M0	HMC2010JT68M0
HMC0402KT50M0	HMC0603JT75M0	HMC0805KT100M	HMC1206JT36M0	HMC1206KT50M0	HMC1210JT50M0
HMC2010JT20M0	HMC2010JT39M0	HMC2512JT51M0	HMC2512KT100M	HMC0603FT100M	HMC0805FT20M0
HMC0805JT36M0	HMC0805KT82M0	HMC1210JT62M0	HMC2010JT91M0	HMC0402FT49M9	HMC0402JT22M0
HMC0603JT33M0	HMC0805JT56M0	HMC0805JT62M0	HMC1206KT510M	HMC1210KT100M	HMC2010JT100M
HMC2512JT50M0	HMC2512JT56M0	HMC0402FT30M0	HMC0805JT22M0	HMC1206KT10G0	HMC1206KT200M
HMC2010KT100M	HMC0603JT22M0	HMC0603JT27M0	HMC0603KT100M	HMC0603KT4G70	HMC0805KT47M0
HMC1206JT51M0	HMC1210JT22M0	HMC2010JT56M0	HMC0402JT27M0	HMC0402JT36M0	HMC1210JT68M0
HMC2010JT50M0	HMC2512JT36M0	HMC2512JT43M0	HMC0402JT82M0		