

APPROVAL SHEET

PRODUCT NAME	CUSTOMER NAME OR MODEL
AEB156	
CABLE LENGTH	CUSTOMER APPROVED BY
CONNECTOR TYPE	APPROVED DATE

SPECIFICATION

Product Name: AEB156

Description: 5/8 Wave Multi-Band Antenna



VERSION INFORMATION

VERSION	DATE	REVISION DESCRIPTION	PREPARED	CHECKED	APPROVED
1.0	12/11/15	New Issued	JMT	JF	

PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	1/12


1. Electrical Characteristics		
1	Antenna model	AEB156
2	Frequency range	GSM850 / GSM900 / GSM1800 / GSM1900 / UMTS 2.1GHz (3G)
3	Gain	3-4dBi
4	Polarisation	Linear
5	Impedance	50Ω
6	VSWR	Less than 3:1

2. Material		
1	Antenna substrate	
2	Electrode	
3	Mounting	
4	RoHS compliant?	Yes

3. Cable		
1	Cable Type	RG58
2	Velocity factor	66%
3	Nominal Diameter	5mm
4	RoHS compliant?	Yes



PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	2/12

4. Dimensions (±0.5mm)



PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	3/12


5. Efficiency and gain plots



PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	4/12

6. Typical radiation patterns


830MHZ



Bi-section 0.00° Amplitude Cut

Bi-section 90.00° Amplitude Cut

921MHZ




Bi-section 0.00° Amplitude Cut

Bi-section 90.00° Amplitude Cut

PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	5/12

Typical radiation patterns (continued)


1700MHz



Bi-section 0.00° Amplitude Cut

Bi-section 90.00° Amplitude Cut

1800MHz




Bi-section 0.00° Amplitude Cut

Bi-section 90.00° Amplitude Cut

PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	6/12

Typical radiation patterns (continued)


1900MHz



Bi-section 0.00° Amplitude Cut

Bi-section 90.00° Amplitude Cut

2100MHz




Bi-section 0.00° Amplitude Cut


Bi-section 90.00° Amplitude Cut

PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	7/12

7. VSWR plot




8. Return/Loss plot



PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	8/12

9. Test environment




Testing hardware:

Keysight FieldFox Microwave Analyser N9915A
EMSCAN RFX2

Testing software:

EMSCAN RFxpert v4.1
Keysight FieldFox Data Link v5.06



PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	9/12

10. Mounting method

Select your location ensuring you can trace the cable(s) from this point to your GPS unit/telephone antenna connection.

1. Drill a 19mm diameter in the metal of the vehicle roof.
2. Clean mounting area so that the edges of the hole are free of sharp edges.
3. To ensure good earth/ground contact, remove the paint around the hole on the underside to reveal the bare metal. This will enable the base to sit tightly into the rubber seal, which comes into direct contact with the roof.

IMPORTANT: Apply a suitable conductive grease to prevent any rusting.

4. Position the base so that it is centred properly in the middle of the hole.
5. Using a 22mm spanner (not provided), tighten the watertight nut from inside the vehicle so that the antenna is completely immobile. Once the antenna is tight, make one ¼ turn extra.



CAUTION: The reception of the signal must not be restricted by anything placed near or onto the antenna. (e.g. roof rack).

After it's use, this product must be processed as electronic scrap for proper disposal according to the prevailing waste disposal regulations of your community/district/state.

PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	10/12

11. Packaging

Package	Qty
Poly Bag	1
Medium Box	Dependant on cable length
Large Box	Dependant on cable length



PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	11/12

12. Environmental specifications

Temperature range: 25±3°C

Relative Humidity range: 55~75%RH

Operating Temperature range: -40°C~+85°C

Storage Temperature range: -40°C~+110°C

Moisture Proof

The device should satisfy the electrical characteristics after exposed to the temperature 40±2°C and the relative humidity 90~95% RH for 96 hours and 1~2 hours recovery time under normal condition.

Vibration Resist

The device should satisfy the electrical characteristics after applied to the vibration of 10 to 55Hz with amplitude of 1.5mm for 2 hours each in X, Y and Z directions.

Drop Shock

The device should satisfy the electrical characteristics after dropping onto the hard wooden board from the height of 30cm for 3 times each facet of the 3 dimensions of the device.

High Temperature Endurance

The device should satisfy the electrical characteristics after exposed to temperature 80±5°C for 24±2 hours and 1~2 hours recovery time under normal temperature.

Low Temperature Endurance

The device should also satisfy the electrical characteristics after exposed to the temperature -40°C±5°C for 24±2 hours and to 2 hours recovery time under normal temperature.

PRODUCT NAME	Prepared Date	Page
AEB156	12/11/15	12/12

13. Notes

- i. This product specification guarantees the quality of our product as a single unit. Please make sure that your product is evaluated and confirmed against your specifications when our product is mounted to your product.
- ii. We cannot warrant against failure caused by any use of our product that deviates from the intended use as described in this product specification.