

Aluminum Electrolytic Capacitors

Radial Lead Type

M-A series



■ Not available in Japan

Features


● Endurance : 85 °C 2000 h● Smaller than series SU

RoHS compliant

Specifications								
Category temp. range	–40 °C to -	+85 ℃	–25 °C to +85 °C					
Rated voltage range	6.3 V to 1	100 V	160 V to 450 V					
Capacitance range	2.2 µF to 22	2000 μF	2.2 μF to 470 μF					
Capacitance tolerance		±20 % (120	Hz / +20℃)					
Leakage current	I ≦ 0.01 CV or 3 (μA (Which is g	,	I ≤ 0.06 CV + 10 (μA) After 2 minutes					
Dissipation factor (tan δ)	Please see the attached characteristics list							
	After applying rated working voltage for 2000 hours at +85 °C±2 ℃, when the capacitors are							
	restored to 20°C, capacitors shall meet the following limits.							
Endurance	Capacitance change	Within ±20 % of the initial value						
	Dissipation factor (tan δ)	≤ 150 % of the initial limit						
	DC leakage current	Within the initial limit						
	After storage for 1000 h at +8	35 ℃±2 ℃ with no voltage	applied and then being					
Shelf life	stabilized at +20 °C, capacitors shall meet the limits specified in endurance.							
	(With voltage treatment)							

Frequency correction factor for ripple current Cap. (μF) 50, 60 120 1 k 10 k to 2.2 to 22000 0.70 1.00 1.30 1.70

Dimensions



Endurance : 85 ℃ 2000 h

Rated	Omnoritore	Case size (mm)		Specification		Lead length (mm)					Min. Packaging Q'ty (PCS)	
voltage (V)	Capacitance (±20 %) (µF)	øD	L	Ripple current*1 (mA rms)	tan δ ^{*2}	Lead dia. (ød)	Straight	_ead spac Taping *B	e Taping *i	Part No.	Strai- ght leads	Taping
	220	5.0	11.0	240	0.28	0.5	2.0	5.0	2.5	ECA0JM221()	200	2000
	470	6.3	11.2	380	0.28	0.5	2.5	5.0	2.5	ECA0JM471()	200	2000
	1000	8.0	11.5	580	0.28	0.6	3.5	5.0	_	ECA0JM102()	200	1000
	2200	10.0	16.0	890	0.30	0.6	5.0	5.0	_	ECA0JM222()	200	500
6.0	3300	10.0	20.0	1020	0.32	0.6	5.0	5.0	_	ECA0JM332()	200	500
6.3	4700	12.5	20.0	1170	0.34	0.6	5.0	5.0	_	ECA0JM472()	200	500
	6800	12.5	25.0	1270	0.38	0.6	5.0	5.0	_	ECA0JM682()	200	500
	10000	16.0	25.0	1450	0.46	0.8	7.5	7.5	_	ECA0JM103()	100	250
	15000	16.0	31.5	1700	0.56	0.8	7.5	_	_	ECA0JM153	100	_
	22000	18.0	35.5	1900	0.70	0.8	7.5	_	_	ECA0JM223	50	_
	330	6.3	11.2	330	0.24	0.5	2.5	5.0	2.5	ECA1AM331()	200	2000
	1000	10.0	12.5	630	0.24	0.6	5.0	5.0	_	ECA1AM102()	200	500
	2200	10.0	20.0	920	0.26	0.6	5.0	5.0	_	ECA1AM222()	200	500
10	3300	12.5	20.0	1090	0.28	0.6	5.0	5.0	_	ECA1AM332()	200	500
	4700	12.5	25.0	1200	0.30	0.6	5.0	5.0	_	ECA1AM472()	200	500
	6800	16.0	25.0	1400	0.34	0.8	7.5	7.5	_	ECA1AM682()	100	250
	10000	16.0	31.5	1600	0.42	0.8	7.5	_	_	ECA1AM103	100	_
	15000	18.0	35.5	1850	0.52	0.8	7.5	_	_	ECA1AM153	50	_
	10	5.0	11.0	30	0.20	0.5	2.0	5.0	2.5	ECA1CM100()	200	2000
	22	5.0	11.0	75	0.20	0.5	2.0	5.0	2.5	ECA1CM220()	200	2000
	33	5.0	11.0	110	0.20	0.5	2.0	5.0	2.5	ECA1CM330()	200	2000
	47	5.0	11.0	130	0.20	0.5	2.0	5.0	2.5	ECA1CM470()	200	2000
	100	5.0	11.0	180	0.20	0.5	2.0	5.0	2.5	ECA1CM101()	200	2000
	220	6.3	11.2	280	0.20	0.5	2.5	5.0	2.5	ECA1CM221()	200	2000
16	470	8.0	11.5	440	0.20	0.6	3.5	5.0	_	ECA1CM471()	200	1000
	1000	10.0	16.0	680	0.20	0.6	5.0	5.0	_	ECA1CM102()	200	500
	2200	12.5	20.0	1000	0.22	0.6	5.0	5.0	_	ECA1CM222()	200	500
	3300	12.5	25.0	1200	0.24	0.6	5.0	5.0	_	ECA1CM332()	200	500
	4700	16.0	25.0	1360	0.26	0.8	7.5	7.5	_	ECA1CM472()	100	250
	6800	16.0	31.5	1600	0.30	8.0	7.5	_	_	ECA1CM682	100	_
	10000	18.0	35.5	1800	0.38	8.0	7.5	_	_	ECA1CM103	50	_
	100	6.3	11.2	180	0.16	0.5	2.5	5.0	2.5	ECA1EM101()	200	2000
	330	8.0	11.5	390	0.16	0.6	3.5	5.0	_	ECA1EM331()	200	1000
	470	10.0	12.5	480	0.16	0.6	5.0	5.0	_	ECA1EM471()	200	500
) F	1000	10.0	20.0	850	0.16	0.6	5.0	5.0	_	ECA1EM102()	200	500
25	2200	12.5	25.0	1200	0.18	0.6	5.0	5.0	_	ECA1EM222()	200	500
	3300	16.0	25.0	1300	0.20	0.8	7.5	7.5	_	ECA1EM332()	100	250
	4700	16.0	31.5	1500	0.22	8.0	7.5	_	_	ECA1EM472	100	_
	6800	18.0	35.5	1750	0.26	0.8	7.5	_	_	ECA1EM682	50	_

^{*1:} Ripple current (120 Hz / +85 °C)

^{*2:} tan δ (120 Hz / +20 ℃)

[•] When requesting taped product, please put the letter "B" or "i" between the "()". Lead wire pitch ★B=5 mm, 7.5 mm, i=2.5 mm

[·] Please refer to the page of "Taping dimensions".

Endurance : 85 ℃ 2000 h

Rated	Capacitance (±20 %) (µF)	Case size (mm)		Specification		Lead length (mm)					Min. Packaging Q'ty (PCS)	
voltage				- ·			Lead space		9	Part No.	Ctura:	
(V)		øD	L	Ripple current ^{*1} tan δ ^{*2}	Lead dia. (ød)	Straight	Taping *B	Taping * i		Strai- ght leads	Taping	
	10	5.0	11.0	60	0.12	0.5	2.0	5.0	2.5	ECA1VM100()	200	2000
	47	5.0	11.0	130	0.14	0.5	2.0	5.0	2.5	ECA1VM470()	200	2000
	100	6.3	11.2	210	0.14	0.5	2.5	5.0	2.5	ECA1VM101()	200	2000
	220	8.0	11.5	350	0.14	0.6	3.5	5.0	_	ECA1VM221()	200	1000
35	330	10.0	12.5	440	0.14	0.6	5.0	5.0	_	ECA1VM331()	200	500
33	470	10.0	16.0	550	0.14	0.6	5.0	5.0	_	ECA1VM471()	200	500
	1000	12.5	20.0	900	0.14	0.6	5.0	5.0	_	ECA1VM102()	200	500
	2200	16.0	25.0	1250	0.16	0.8	7.5	7.5	-	ECA1VM222()	100	250
	3300	16.0	31.5	1400	0.18	0.8	7.5	_	-	ECA1VM332	100	_
	4700	18.0	35.5	1600	0.20	0.8	7.5	_	-	ECA1VM472	50	_
·	2.2	5.0	11.0	20	0.12	0.5	2.0	5.0	2.5	ECA1HM2R2()	200	2000
	3.3	5.0	11.0	35	0.12	0.5	2.0	5.0	2.5	ECA1HM3R3()	200	2000
	4.7	5.0	11.0	45	0.12	0.5	2.0	5.0	2.5	ECA1HM4R7()	200	2000
	10	5.0	11.0	65	0.12	0.5	2.0	5.0	2.5	ECA1HM100()	200	2000
	22	5.0	11.0	100	0.12	0.5	2.0	5.0	2.5	ECA1HM220()	200	2000
	33	5.0	11.0	110	0.12	0.5	2.0	5.0	2.5	ECA1HM330()	200	2000
50	47	6.3	11.2	130	0.12	0.5	2.5	5.0	2.5	ECA1HM470()	200	2000
50	100	8.0	11.5	250	0.12	0.6	3.5	5.0		ECA1HM101()	200	1000
	220	10.0	12.5	400	0.12	0.6	5.0	5.0	-	ECA1HM221()	200	500
	330	10.0	16.0	500	0.12	0.6	5.0	5.0	_	ECA1HM331()	200	500
	470	10.0	20.0	650	0.12	0.6	5.0	5.0	_	ECA1HM471()	200	500
	1000	12.5	25.0	1050	0.12	0.6	5.0	5.0		ECA1HM102()	200	500
	2200	16.0	31.5	1300	0.14	0.8	7.5	_	-	ECA1HM222	100	_
	3300	18.0	35.5	1500	0.16	0.8	7.5	_	-	ECA1HM332	50	_
	10	5.0	11.0	70	0.11	0.5	2.0	5.0	2.5	ECA1JM100()	200	2000
	22	5.0	11.0	105	0.11	0.5	2.0	5.0	2.5	ECA1JM220()	200	2000
	33	6.3	11.2	130	0.11	0.5	2.5	5.0	2.5	ECA1JM330()	200	2000
	47	6.3	11.2	160	0.11	0.5	2.5	5.0	2.5	ECA1JM470()	200	2000
63	100	8.0	11.5	270	0.11	0.6	3.5	5.0		ECA1JM101()	200	1000
03	220	10.0	16.0	450	0.11	0.6	5.0	5.0		ECA1JM221()	200	500
	330	10.0	20.0	550	0.11	0.6	5.0	5.0	-	ECA1JM331()	200	500
	470	12.5	20.0	750	0.11	0.6	5.0	5.0	-	ECA1JM471()	200	500
	1000	16.0	25.0	1100	0.11	0.8	7.5	7.5	-	ECA1JM102()	100	250
	2200	18.0	35.5	1400 0.13		8.0	7.5	_	_	ECA1JM222	50	_

^{*1:} Ripple current (120 Hz / +85 °C)

^{*2:} tan δ (120 Hz / +20 °C)

[•] When requesting taped product, please put the letter "B" or "i" between the "()". Lead wire pitch *B=5 mm, 7.5 mm, i=2.5 mm

[•] Please refer to the page of "Taping dimensions".

Endurance : 85 ℃ 2000 h

Rated	Capacitance	Case size (mm)		Specification		Lead length (mm)					Min. Packaging Q'ty (PCS)	
voltage (V)	(±20 %) (μF)			Dinala		1	I	Lead space	е	Part No.	Strai-	
		øD	L	Ripple current*1 (mA rms)	tan δ ^{*2}	Lead dia. (ød)	Straight	Taping * B	Taping * i		ght leads	Taping
	2.2	5.0	11.0	30	0.10	0.5	2.0	5.0	2.5	ECA2AM2R2()	200	2000
	3.3	5.0	11.0	40	0.10	0.5	2.0	5.0	2.5	ECA2AM3R3()	200	2000
	4.7	5.0	11.0	50	0.10	0.5	2.0	5.0	2.5	ECA2AM4R7()	200	2000
	10	5.0	11.0	70	0.10	0.5	2.0	5.0	2.5	ECA2AM100()	200	2000
	22	6.3	11.2	115	0.10	0.5	2.5	5.0	2.5	ECA2AM220()	200	2000
100	33	8.0	11.5	145	0.10	0.6	3.5	5.0	_	ECA2AM330()	200	1000
100	47	8.0	11.5	180	0.10	0.6	3.5	5.0	_	ECA2AM470()	200	1000
	100	10.0	16.0	350	0.10	0.6	5.0	5.0		ECA2AM101()	200	500
	220	12.5	20.0	550	0.10	0.6	5.0	5.0		ECA2AM221()	200	500
	330	12.5	25.0	700	0.10	0.6	5.0	5.0	-	ECA2AM331()	200	500
	470	16.0	25.0	900	0.10	0.8	7.5	7.5		ECA2AM471()	100	250
	1000	18.0	35.5	1300	0.10	8.0	7.5	_	-	ECA2AM102	50	_
	2.2	6.3	11.2	53	0.16	0.5	2.5	5.0	2.5	ECA2CM2R2()	200	2000
	3.3	6.3	11.2	66	0.16	0.5	2.5	5.0	2.5	ECA2CM3R3()	200	2000
	4.7	6.3	11.2	78	0.16	0.5	2.5	5.0	2.5	ECA2CM4R7()	200	2000
	10	10.0	12.5	105	0.16	0.6	5.0	5.0		ECA2CM100()	200	500
	22	10.0	16.0	175	0.16	0.6	5.0	5.0		ECA2CM220()	200	500
160	33	10.0	20.0	235	0.16	0.6	5.0	5.0	_	ECA2CM330()	200	500
	47	12.5	20.0	320	0.16	0.6	5.0	5.0	_	ECA2CM470()	200	500
	100	12.5	25.0	515	0.16	0.6	5.0	5.0	_	ECA2CM101()	200	500
	220	16.0	31.5	830	0.16	0.8	7.5	_	_	ECA2CM221	100	_
E	330	18.0	31.5	1090	0.16	8.0	7.5	_		ECA2CM331	50	_
EC	470	18.0	40.0	1440	0.16	8.0	7.5	_		ECA2CM471	50	_
	2.2	6.3	11.2	50	0.18	0.5	2.5	5.0	2.5	ECA2DM2R2()	200	2000
	3.3	6.3	11.2	62	0.18	0.5	2.5	5.0	2.5	ECA2DM3R3()	200	2000
	4.7	8.0	11.5	86	0.18	0.6	3.5	5.0		ECA2DM4R7()	200	1000
	10	10.0	12.5	100	0.18	0.6	5.0	5.0		ECA2DM100()	200	500
200	22	10.0	20.0	180	0.18	0.6	5.0	5.0		ECA2DM220()	200	500
200	33	10.0	20.0	220	0.18	0.6	5.0	5.0		ECA2DM330()	200	500
	47	12.5	20.0	300	0.18	0.6	5.0	5.0		ECA2DM470()	200	500
	100	16.0	25.0	475	0.18	8.0	7.5	7.5		ECA2DM101()	100	250
EC	220	18.0	31.5	835	0.18	8.0	7.5	_		ECA2DM221	50	_
E	330	18.0	40.0	1140	0.18	8.0	7.5	_		ECA2DM331	50	_

^{*1:} Ripple current (120 Hz / +85 $^{\circ}$ C)

EOL End of life

^{*2:} tan δ (120 Hz / +20 ℃)

[•] When requesting taped product, please put the letter "B" or "i" between the "()". Lead wire pitch ★B=5 mm, 7.5 mm, i=2.5 mm

[•] Please refer to the page of "Taping dimensions".

Endurance : 85 ℃ 2000 h

Rated	Capacitance	Case size (mm)		Specification		Lead length (mm)					Min. Packaging Q'ty (PCS)	
voltage	(±20 %)			Dinnlo		Lead	Lead space		е	Part No.	Strai-	
(V)	(µF)	øD	L	Ripple current*1 (mA rms)	tan δ ^{*2}	dia. (ød)	Straight	Taping * B	Taping * i		ght leads	Taping
	2.2	6.3	11.2	50	0.18	0.5	2.5	5.0	2.5	ECA2EM2R2()	200	2000
	3.3	8.0	11.5	72	0.18	0.6	3.5	5.0	_	ECA2EM3R3()		1000
	4.7	8.0	11.5	86	0.18	0.6	3.5	5.0	_	ECA2EM4R7()	200	1000
	10	10.0	16.0	110	0.18	0.6	5.0	5.0	_	ECA2EM100()	200	500
250	22	10.0	20.0	180	0.18	0.6	5.0	5.0	_	ECA2EM220()	200	500
	33	12.5	20.0	250	0.18	0.6	5.0	5.0	_	ECA2EM330()	200	500
	47	12.5	25.0	330	0.18	0.6	5.0	5.0	_	ECA2EM470()	200	500
	100	16.0	31.5	530	0.18	0.8	7.5	_	_	ECA2EM101	100	_
E	220	18.0	40.0	930	0.18	0.8	7.5	_		ECA2EM221	50	_
-	2.2	8.0	11.5	55	0.20	0.6	3.5	5.0	_	ECA2VM2R2()	200	1000
	3.3	8.0	11.5	60	0.20	0.6	3.5	5.0	_	ECA2VM3R3()	200	1000
	4.7	10.0	12.5	65	0.20	0.6	5.0	5.0	_	ECA2VM4R7()	200	500
250	10	10.0	20.0	115	0.20	0.6	5.0	5.0	_	ECA2VM100()	200	500
350	22	12.5	20.0	195	0.20	0.6	5.0	5.0	_	ECA2VM220()	200	500
	33	16.0	25.0	300	0.20	0.8	7.5	7.5	_	ECA2VM330()	100	250
	47	16.0	25.0	325	0.20	0.8	7.5	7.5	_	ECA2VM470()	100	250
E	100	18.0	31.5	535	0.20	0.8	7.5	_		ECA2VM101	50	_
-	2.2	8.0	11.5	50	0.20	0.6	3.5	5.0	_	ECA2GM2R2()	200	1000
	3.3	10.0	12.5	54	0.20	0.6	5.0	5.0	_	ECA2GM3R3()	200	500
	4.7	10.0	16.0	72	0.20	0.6	5.0	5.0	_	ECA2GM4R7()	200	500
400	10	10.0	20.0	115	0.20	0.6	5.0	5.0	_	ECA2GM100()	200	500
400	22	12.5	25.0	215	0.20	0.6	5.0	5.0	_	ECA2GM220()	200	500
	33	16.0	25.0	275	0.20	0.8	7.5	7.5	_	ECA2GM330()	100	250
	47	16.0	31.5	350	0.20	0.8	7.5	_	_	ECA2GM470	100	_
EC	100	18.0	40.0	600	0.20	0.8	7.5	_		ECA2GM101	50	_
-	2.2	10.0	12.5	44	0.20	0.6	5.0	5.0	_	ECA2WM2R2()	200	500
	3.3	10.0	16.0	60	0.20	0.6	5.0	5.0	_	ECA2WM3R3()	200	500
450	4.7	10.0	20.0	79	0.20	0.6	5.0	5.0		ECA2WM4R7()	200	500
450	10	12.5	20.0	130	0.20	0.6	5.0	5.0		ECA2WM100()	200	500
	22	16.0	25.0	210	0.20	0.8	7.5	7.5	_	ECA2WM220()	100	250
	33	16.0	31.5	285	0.20	0.8	7.5	_	_	ECA2WM330	100	_

^{*1:} Ripple current (120 Hz / +85 ℃)

EOL End of life

^{*2:} tan δ (120 Hz / +20 °C)

[•] When requesting taped product, please put the letter "B" or "i" between the "()". Lead wire pitch *****B=5 mm, 7.5 mm, i=2.5 mm
• Please refer to the page of "Taping dimensions".



Safety and Legal Matters to Be Observed

Product specifications and applications

- Please be advised that this product and product specifications are subject to change without notice for improvement purposes. Therefore, please request and confirm the latest delivery specifications that explain the specifications in detail before the final design, or purchase or use of the product, regardless of the application. In addition, do not use this product in any way that deviates from the contents of the company's delivery specifications.
- Unless otherwise specified in this catalog or the product specifications, this product is intended for use in general electronic equipment (AV products, home appliances, commercial equipment, office equipment, information and communication equipment, etc.).

 When this product is used for the following special cases, the specification document suited to each application shall be signed/sealed (with Panasonic and the user) in advance.. These include applications requiring special quality and reliability, wherein their failures or malfunctions may directly threaten human life or cause harm to the human body (e.g.: space/aircraft equipment, transportation/traffic equipment, combustion equipment, medical equipment, disaster prevention/crime prevention equipment, safety equipment, etc.).

Safety design and product evaluation

- Please ensure safety through protection circuits, redundant circuits, etc., in the customer's system design so that a defect in our company's product will not endanger human life or cause other serious damage.
- This catalog shows the quality and performance of individual parts. The durability of parts varies depending on the usage environment and conditions. Therefore, please ensure to evaluate and confirm the state of each part after it has been mounted in your product in the actual operating environment before use.
 If you have any doubts about the safety of this product, then please notify us immediately, and be sure to conduct a technical review including the above protection circuits and redundant circuits at your company.

Laws / Regulations / Intellectual property

- The transportation of dangerous goods as designated by UN numbers, UN classifications, etc., does not apply to this product. In addition, when exporting products, product specifications, and technical information described in this catalog, please comply with the laws and regulations of the countries to which the products are exported, especially those concerning security export control.
- Each model of this product complies with the RoHS Directive (Restriction of the use of hazardous substances in electrical and electronic equipment) (2011/65/EU and (EU) 2015/863). The date of compliance with the RoHS Directive and REACH Regulation varies depending on the product model. Further, if you are using product models in stock and are not sure whether or not they comply with the RoHS Directive or REACH Regulation, please contact us by selecting "Sales Inquiry" from the inquiry form.
- During the manufacturing process of this product and any of its components and materials to be used, Panasonic does not intentionally use ozone-depleting substances stipulated in the Montreal Protocol and specific bromine-based flame retardants such as PBBs (Poly-Brominated Biphenyls) / PBDEs (Poly-Brominated Diphenyl Ethers). In addition, the materials used in this product are all listed as existing chemical substances based on the Act on the Regulation of Manufacture and Evaluation of Chemical Substances.
- With regard to the disposal of this product, please confirm the disposal method in each country and region where it is incorporated into your company's product and used.
- The technical information contained in this catalog is intended to show only typical operation and application circuit examples of this product. This catalog does not guarantee that such information does not infringe upon the intellectual property rights of Panasonic or any third party, nor imply that the license of such rights has been granted.

Panasonic Industry will assume no liability whatsoever if the use of our company's products deviates from the contents of this catalog or does not comply with the precautions. Please be advised of these restrictions.



Matters to Be Observed When Using This Product

(Conductive polymer hybrid aluminum electrolytic capacitor / Aluminum electrolytic capacitor)

Use environments and cleaning conditions

- This product (capacitor) is intended for standard general-purpose use in electronic equipment, and is not designed for use in the specific environments described below. Using the product in such specific environments or service conditions, therefore, may affect the performance of the product.
 - Check with us about the performance and reliability of the product first before using the product.
 - (1) Used at a temperature higher than the upper limit category temperature or lower than the lower limit category temperature.
 - (2) Used in an environment where the product is directly exposed to water, salt water, oil, etc., or in a liquid, such as water, oil, chemicals, and organic solvents.
 - (3) Used in an outdoor environment where the product is exposed to direct sunlight, ozone, radiation, UV-rays, etc., or in a dusty place.
 - (4) Used in a wet place (dew concentration on a resistor, water leakage, etc.), a place exposed to sea breeze, or a place filled with a corrosive gas, such as Cl₂, H₂S, NH₃, SO₂, or NO_X.
 - (5) Used in an environment filled with a toxic gas (hydrogen sulfide, sulfurous acid, nitrous acid, chlorine and chlorine compound, bromine and bromine compound, ammonia, etc.)
 - (6) Used in an environment where static electricity and electromagnetic waves are strong.
 - (7) Located close to heating component or a flammable material, such as a vinyl cable.
 - (8) Sealed with a resin, etc.
 - (9) Cleansed with a solvent, water, or a water-soluble cleaner, to remove solder flux after soldering.
 - (10) Used in an environment where an acidic or alkali atmosphere is present.
 - (11) Used in an environment where excessive vibration or mechanical shocks exceeding a specified range is applied to the product (even if the applied vibration or mechanical shocks is within the specified range, it may cause the product to resonate, in which a large vibration acceleration may be generated. Make sure to evaluate/check such vibrations or impacts applied to the product in an actual service condition).
 - (12) Used under a low atmospheric pressure condition or depressurized condition.
- The capacitor withstands an immersion cleaning process where the board carrying the product is immersed in a cleaning solution of 60 °C or lower for less than 5 minutes and withstands an ultrasonic cleaning process as well. However, ensure to thoroughly rinse and dry it. Some cleaning methods erase or blur notes on the capacitor in some cases. Some types of capacitors are not washable and some cleaning solutions cannot be used to clean a capacitor. If you are not sure about which type of capacitor is not washable or which cleaning solution cannot be used, please contact us. Solvents you can use to clean the board are as follows.
 - Pine Alpha ST-100S, Aqua Cleaner 210SEP, Cleanthrough 750H/750L/710M, Sun Elec B-12, Techno Cleaner 219, Cold Cleaner P3-375, DK Be clear CW-5790, Terpene Cleaner EC-7R, Techno Care FRW-17/FRW-1/FRV-1
- Keep the cleaning solution under strict contamination control (conductivity, pH, specific gravity, water content, etc.). A contaminated cleaning solution will show a high chlorine concentration, thereby corroding the interior of the capacitor in some cases. Keep the flux concentration in the cleaning solution at a 2% mass or less.
- Unless otherwise specified in the specifications, avoid cleaning the capacitor with a halogen-based solvent, an alkaline solvent, a petroleum-based solvent, xylene, or acetone. Using a halogen-based solvent may result in a case where the solvent infiltrates (leaks) into the capacitor and break-down releasing chlorine, which reacts with aluminum which can corrode the capacitor interior. 1-1-1 trichloroethane is particularly harmful to a capacitor. Never use it to clean a capacitor. A alkaline solvent may corrode (dissolve) an aluminum case, a petroleum-based solvent and xylene may damage the sealing rubber and accelerate its deterioration, and acetone may erase notes on the capacitor.
 - To protect the global environment, refrain from using an ozone depleting substance as the cleaning solution.
- Right after the board cleaning, subject the capacitor to a forced drying process so that no cleaning solution remains between the sealing part of the capacitor and the printed board. Set a drying temperature equal to or lower than the upper limit category temperature.
- When an adhesive or coating agent is used to fix the capacitor and prevent dampening of the board, specific types of solvents included in some adhesives or coating agents may corrode the capacitor. Select a non-halogen solvent for the material making up the adhesive or coating agent. Do not use a chloroprene-based polymer. Solidify and dry the adhesive or coating agent sufficiently to prevent its solvent component from remaining on the capacitor. Leave at least 1/3 of the sealing part unsealed on the surface to which the adhesive or coating agent is applied.



- Do not use the product in a structure sealed by potting or molding. The pressure of a molding resin on a capacitor may deform the capacitor. In addition, the resin covering the capacitor may affect its heat dissipation performance or may leak into the product. These factors lead to the significant degradation of the capacitor's characteristics and reliability. There is also a concern that an electrolytic solution permeating the sealing rubber may agglomerate and cause a short circuit.
- When the capacitor is used in a circuit where an impact voltage is applied or a high voltage is applied in a short period (transient phenomenon) or a high pulse voltage is applied, make sure to use the capacitor at a voltage equal to or lower than its rated voltage.
- The product contains an electrolytic. Improper use of the capacitor leads not only to the rapid degradation of its characteristics but also to electrolytic leakage. These problems damage the circuit board and may lead to destruction of the entire circuit set.

Response to anomalies and handling conditions

- When you see gas coming out of an activated pressure relief valve of a capacitor during use of a circuit set, turn off the main power supply of the circuit set or pull the power cord plug out of the wall-outlet. If you leave the power supply on and the capacitor short-circuits, it will damage the circuit, or the gas can turn into a liquid, which will cause the circuit to short. In the worst case scenarios, these events may develop into a more serious incident, such as burnout of the circuit set. The gas coming out of the pressure relief valve of a capacitor is not smoke, but is the electrolytic solution in its gaseous state.
- When the pressure valve of the capacitor is activated, it emits a high-temperature gas of over 100 °C. Do not bring your face near the valve. In case the gas jetting out of the valve gets in your eyes or comes into your mouth, wash your eyes with water or rinse your mouth immediately. If the gas hits your skin, wash it away with soap.
- If you touch a terminal of the product during use of the circuit set, you will get an electric shock. The aluminum case of the product has an exposed part with no insulation. Do not touch the exposed part because it is as dangerous as the terminal.
- Do not create a short circuit between terminals of the product by inserting a conductor therebetween. Do not splash a conductive solution, such as an acidic or alkali solution, on the capacitor. It puts the capacitor in a shorted state, which causes the circuit to fail and destroys the capacitor as well.
- When a silicone material containing a relatively large amount of a low-molecular-weight siloxane is located close to the product, it may cause the capacitor problems with its electrical performance.
- When electronic equipment having the capacitor built therein is exported to overseas markets, wooden packaging materials are fumigated with a halogen compound, such as methyl bromide. In such cases, if the packaging material subjected to the fumigation treatment is not dried sufficiently, halogen remaining on the packaging material may leach into the capacitor during transportation and trigger a corrosive reaction in the capacitor. When carrying out the fumigation treatment, carefully examine the dried packaging material to confirm that no halogen remains on the packaging material. Never fumigate the entire electronic equipment in its packaged state.

Reliability and product life

- The product life is affected by temperatures. In general, a 10 °C drop in the temperature will double the life. Use the capacitor at a temperature as low as possible from the upper limit category temperature.
- Using a capacitor under a temperature condition outside a specified temperature range causes heavy degradation of the capacitor characteristics, which may result in breakage of the capacitor. You need to confirm not only the ambient temperature and internal temperature of the capacitor but also the temperature of the capacitor's top surface, which is given by radiant heat from built-in heating elements (a power transistor, IC, resistance, etc.) and heat generated by self-heating induced by ripple current. Do not place a heating element on the back of the capacitor.



■ The product life is given by the following equation.

L2 = L1 x 2
$$\frac{T_1-(T_2+\Delta T)}{10}$$

L1 : Guaranteed life (h) at temperature T₁ (°C)

L2 : Expected life (h) at temperature T₂ (°C) * In the case of a hybrid type, category temperature (°C) T1 : Upper category temperature (°C) + temperature increase caused by rated ripple current (°C)

T2 : Ambient temperature of capacitor (°C)

△T : Temperature increase caused by ripple current (°C)

■ Do not use the product for a period longer than its specified service life. A capacitor with its service life ended may cause the following problems: rapid degradation of the product characteristics, short circuit, unnecessary activation of the pressure valve, electrolytic solution leakage, etc. Note that the estimated service life is not longer than 15 years due to the limited environment-resistant property of the sealing rubber.

■ When the capacitor is used under a high-temperature condition for a long period, minute cracks develop on the surface of the sealing rubber or the case surface turns brown in some cases. These phenomena, however, have no effects on the reliability of the capacitor.

■ A capacitor conforming to "AEC-Q200" refers to a capacitor having passed some or all of evaluation test items defined in AEC-Q200.

To know the detailed specifications of each capacitor or specific evaluation test scores, please contact us. We issue a the product specifications sheet for each product ordered. Please confirm the product specifications sheet when you place an order to us.

Circuit design and circuit board design

■ The electrical characteristics change as a result of temperature/frequency fluctuations. Take electrical characteristic changes into consideration when working out a circuit design.

(1) Temperature fluctuations

High-temperature condition : increase in leak current

Low-temperature condition : decrease in capacitance, increase in the tangent to the loss angle,

increase in impedance (the hybrid type is excluded), etc.

(2) Frequency fluctuations

High-frequency condition : decrease in capacitance, increase in the tangent to the loss angle,

decrease in impedance, etc.

Low-frequency condition : more heat generation by ripple current as a result of an increase in

equivalent series resistance

■ The group of factors described below may lead to rapid degradation of the capacitor characteristics, short circuit, or electrolytic solution leakage. They may give rise to sharp heat/gas generation, too, in which case the increasing internal pressure actuates the pressure valve, causes the electrolytic solution to leak out of the sealing part, and, in a worst-case scenario, causes an explosion or ignition incident. When a capacitor bursts, it may scatter flammable materials (electrolytic solution, etc.) in its surroundings.

(1) Reverse voltage: The capacitor has preset polarity. Do not apply a reverse voltage to the capacitor. Confirm the polarity indicated on the capacitor and then use it.

(2) Charge/discharge: Avoid using the capacitor in a circuit that frequently repeats sharp charge/discharge cycles or a circuit that requires relatively slow but highly frequent charge/discharge cycles. In cases where you use the capacitor in such circuits, make sure to inform us of the charge/discharge conditions.

Ensure that a rush current does not exceed 100 A.

(3) ON/OFF: Avoid using the capacitor in an on/off circuit that repeatedly switches on and off more than 10,000 times a day. In cases where you use the product in such circuits, make sure to inform us of the circuit conditions, etc.

(4) Overvoltage: Do not apply an overvoltage higher than the rated voltage (higher than the surge voltage when the voltage application period is short). A peak value given by superposing a ripple voltage (AC component) on a DC voltage must be equal to or lower than the rated voltage.

(5) Ripple current: Do not allow an excessively large ripple current (larger than the rated ripple current specified in the specifications) to flow through the capacitor. Even if a ripple current flow in the capacitor is equal to or smaller than the rated ripple current, a reverse voltage flow may be generated in the capacitor when the DC bias voltage is low flow in the capacitor. Keep the ripple current flow within a range in which no reverse voltage is generated.
Even if the ripple current flow is kept equal to or smaller than the rated ripple current, using the capacitor for a period

longer than its service life intensifies the degradation of the ESR characteristics, resulting in an increase in internal heating caused by the ripple current. As a result, the pressure valve is actuated, the exterior case or rubber swells, the electrolytic solution leaks, and, in a worst-case scenario, the capacitor short-circuits and ignites or explodes.



- Because the impedance of the capacitor is close to the circuit impedance, capacitors connected in parallel in the circuit may damage the whole current balance, in which, a ripple current higher than the rated ripple current may flow in some of the capacitors. To prevent concentration of ripple current on the low-impedance side, use capacitors with the same part number and avoid the partiality of cable impedances. Do not use capacitors connected in series.
- When the capacitor is mounted on a double-side wiring board, do not place the wiring pattern directly underneath where the product is mounted. In case the electrolytic solution leaks out, it may short-circuit the pattern and cause tracking or migration. Consider a case where the product is a radial lead capacitor and is mounted on a board with through-holes. In this case, if the sealing part of the capacitor and the board surface stick close to each other, solder flows up to the capacitor during a dip soldering process, which may cause short circuit between the anode and cathode of the capacitor. In such a case, the outer laminate of the product may be damaged. The position of holes, therefore, must be determined properly.
- When designing a printed board carrying radial lead capacitors, make through-holes across the gap equal to the gap between the leads (terminals) of the capacitor. If the gap between the through-holes is narrower or wider than the gap between the leads, stress is applied to the leads when the capacitor is inserted in the holes.

 This may result in increasing leak current, short circuit, wire breaking, or electrolytic solution leakage.
- A capacitor which has the pressure valve on the case must be provided with a space formed above the pressure valve so that the pressure valve operates without hinderance. When the product is 6.3 mm to 16 mm in diameter, form a space of 2 mm or larger. When the product is 18 mm in diameter, form a space of 3 mm or larger. If the space is not large enough, it will impair the operability of the pressure valve and may lead to an explosion incident.
- Design the circuit in such that the pattern, especially a line pattern carrying high voltage or large current, is not formed above the pressure valve. Upon its activation, the pressure valve emits a flammable high-temperature gas of over 100 °C. This may cause a secondary accident, such as the gas condensing on the pattern and the wire sheathing being melted and catching on fire.
- Be careful with resonance of the capacitor mounted on the board. When a large load is applied to the capacitor at the frequency close to the resonance frequency, it may cause the capacitor to come off or widely change its characteristics.
- Completely isolate the case of the capacitor from the cathode terminal and the circuit pattern.
- The laminate or outer sleeve covering of the product is for displaying information on the product and does not have a guaranteed insulating function.
 - The laminate may turn brown under a high-temperature condition. However, that does not cause problems with markings recognition on the product surface or electrical performance.
 - The outer sleeve may crack when dipped in a xylene or toluene solution and exposed to high temperature.

Mounting conditions

- Do not reuse a capacitor that was incorporated in a circuit set and energized in the past. Do not use a capacitor that was dropped on the floor.
 - Do not use a capacitor in its compressed form. Compressing the capacitor makes it less airtight, resulting in poor performance, shorter guaranteed life, and electrolyte leakage.
- \blacksquare A re-striking voltage is generated in a capacitor in some cases. In such a case, let the capacitor discharge through a resistor of about 1 kΩ.
- When a capacitor is kept in storage for a long period, you may find the leak current from the capacitor has increased. In such a case, make voltage adjustment through a resistor of about 1 kΩ.
- Before mounting the capacitor on the board, confirm the ratings (capacitance, rated voltage, etc.) and polarity of the capacitor. Before mounting a surface-mounted type capacitor, confirm its terminal dimensions and land size. Before mounting a radial lead type capacitor, confirm its terminal interval and hole interval. If the terminal interval is not the specified one, stress is applied to internal elements, which may cause problems, such as a short circuit and insufficient mounting strength.
 - When the terminal interval and the hole interval of the radial lead type capacitor do not match and therefore the capacitor's leads need to be readjusted, make sure that the readjustment does not apply any stress to the capacitor's body.



- Confirm the applied pressure when using an automatically mounting process for a surface-mounted type capacitor. Excessive pressure may result in increasing leak current, short circuit, the capacitor coming off from the board, and the like. When automatically mounting the radial lead type capacitor, check the wear of a cutter for cutting the leads and confirm that the angle of clinching the leads is not too acute with regards to the board. Clinching the leads at too acute of an angle applies tensile stress to the leads, which may lead to destruction of the capacitor.
- Follow soldering conditions (preheating, soldering temperature/time, the number of soldering, etc.) in the specification sheet. A high peak temperature or a long heating time causes the degradation of electrical characteristics or a reduction in the guaranteed life. Note that the specified soldering conditions indicate conditions under which the degradation of capacitor characteristics do not occur but do not indicate conditions under which stable soldering can be performed. Check and set conditions under which stable soldering can be performed, on a case-by-case basis. Measure the temperature of the capacitor, using a thermocouple bonded to the top of the capacitor with an epoxy-based adhesive. This temperature measurement must be conducted in a mass-production setup.
- The surface-mounted type capacitor is soldered by reflow soldering only. It cannot be soldered by flow soldering or dip soldering. Carry out reflow soldering with an atmospheric heat transfer method using infrared hot air, etc. When carrying out two rounds of reflow processes, carry out the second reflow process after the capacitor's temperature settles down to a normal temperature. In the case of VPS reflow, a sharp rise in the capacitor temperature causes a change in the characteristics and appearance of the capacitor, which may give rise to a problem with capacitor mounting. We therefore recommend execution of VPS flow at a temperature rise rate of 3 °C/second or lower. For more information about this matter, please contact us.
- Reflow soldering, under the reflow conditions we recommend, might result in discoloring or swelling of the case or crack formation on the ink mark indicating the cathode. These minor problems, however, do not affect the reliability of the capacitor at all.
- A 6.3-mm diameter vibration-resistant capacitor has a structure that covers the auxiliary terminals to the sides of a seat plate. In cases where you confirm formation of a fillet on the sides of the auxiliary terminals by an image recognition means, etc., examine soldering conditions for the formation of a sufficient fillet on the auxiliary terminals in advance before carrying out the soldering process.

 Even if the formation of a sufficient fillet on the auxiliary terminals is not confirmed, a solder junction between the lower surface of the auxiliary terminals and the board ensures vibration-resistant performance, meaning the reliability of the capacitor is not affected.
- The radial lead type capacitor cannot be soldered by reflow soldering. Do not dip the capacitor body, except the leads, in solder. Heat from the solder raises the internal pressure of the capacitor and destroys it. Solder the capacitor according to the following soldering conditions: soldering temperature of 260 °C ±5 °C and soldering time of 10 seconds ±1 second.
- Ensure that other components do not come in contact with the capacitor during the soldering process. When a radial lead type capacitor is set in close contact with the board, check the soldered state of the capacitor well, because its sealing rubber has no venting structure.
- When manually soldering the capacitor, follow the soldering conditions (soldering temperature/time) specified in the specification sheet or adopt a soldering temperature of 350 °C and a soldering time of 3 seconds or less. When you need to remove a capacitor already soldered, remove it after the solder is melted sufficiently so that no stress is applied to the terminals of the capacitor. Be careful not to let the solder iron tip touch the capacitor. The solder iron touching the capacitor may damage the capacitor.
- When the temperature of the capacitor becomes extremely high due to preheating, solidification of the setting resin, etc., may cause the outer sleeve of the capacitor to shrink or crack. When treating the capacitor in a thermosetting furnace, etc., place the capacitor in an atmosphere of 150 °C for 2 minutes or less.
- Do not tilt or twist the capacitor soldered to a printed board or hold the capacitor to carry the board or hit the capacitor against something. Such actions apply a force to the internal elements through the terminals and may destroy the product.
- Using highly active halogenous (chlorine-based or bromic) solder flux poses a concern that residual solder flux will have negative impact on the performance and reliability of the capacitor. Check the influence of residual solder flux before using such solder flux.



Storage conditions

- A capacitor left for a long period is prone to have a greater flow of leak current. This happens because the oxide film deteriorates under a no-load condition. Voltage application to the capacitor reduces the leak current. However, at the start of voltage application, a large flow of film recovery current increases the leak current, which may cause a circuit failure, etc.
- The storage period of a capacitor is 42 months from the shipment inspection day. However, the storage period of capacitors not listed in the following table is specified as 12 months.

 Store the capacitor in a place where a normal temperature condition (5°C to 35°C) and a normal humidity condition (45% to 85%) are maintained and direct sunlight is blocked.

Product category	Series	Storage period
Hybrid type	All hybrid series	
Surface-mounted type other than the hybrid type	S (hot lead-free reflow), HA (hot lead-free reflow) HB (hot lead-free reflow, 5.4 mm in height) HC, HD, FCA, FC, FKA, FK, FKS, FP, FT, FH TG, TK, TP, TC, TCU, TQ	42 months from the shipment inspection day
Radial lead type other than the hybrid type	FC-A, FK-A, HD-A, TA-A, TP-A, FP-A	

- Avoid storing the capacitor in environments not specified in the delivery specification sheet or in the following environments or conditions.
 - (1) Used at a temperature higher than the upper limit category temperature or lower than the lower limit category temperature
 - (2) Environments where the capacitor is exposed to water, salt water, or oil
 - (3) Environments where dew concentrates on the capacitor
 - (4) Environments filled with a toxic gas (hydrogen sulfide, sulfurous acid, nitrous acid, chlorine and chlorine compound, bromine and bromine compound, ammonia, etc.)
 - (5) Environments where the product is exposed to ozone, radiation, UV-rays, etc.
 - (6) Environments where vibrations or mechanical shocks exceeding a specified range is applied to the capacitor

Reference information

Guidelines

Some of the product use guidelines described herein are excerpted from JEITA RCR-2367D "Safety application guide for fixed aluminum electrolytic capacitors for use in electronic equipment," a technical report issued by the Japan Electronics and Information Technology Industries Association on October 2017. For more detailed information, please see the above technical report.

Intellectual property

Panasonic Group provides customers with safe products and services. We are also making great efforts to protect our intellectual property rights for Panasonic Group products. Typical patents related to this product are as follows. (Hybrid type)

[U.S. patent]

USP Nos. 7497879, 7621970, 9208954, 9595396, 9966200, 10453618, 10559432, 10679800, 10685788, and 10790095.

[Japanese patent]

Japanese Patent No. 5360250

[European patent]

EP-A Nos. 1808875 and 2698802

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

ECA-0JM101 ECA-0JM102 ECA-0JM103 ECA-0JM153 ECA-0JM221 ECA-0JM221B ECA-1CM100 ECA1CM1001 ECA-1CM101 ECA-1CM102 ECA-1CM102B ECA-1CM103 ECA-1CM20 ECA-1CM221 ECA-1CM222
ECA-1CM330 ECA-1CM331 ECA-1CM332 ECA-1AM101 ECA-1AM102 ECA-1AM102B ECA-1AM103 ECA1AM153 ECA-1AM221 ECA-1AM222 ECA-1AM331 ECA-1AM332 ECA-1AM471 ECA-1AM472 ECA-1AM682
ECA-0JM222 ECA-0JM223 ECA-0JM331 ECA-0JM332 ECA-0JM471 ECA-0JM471 ECA-0JM472 ECA-0JM472B
ECA-0JM682 ECA-1CM470 ECA-1CM470B ECA-1CM471 ECA-1CM472 ECA-1CM682 ECA-1JM100 ECA1JM101 ECA-1JM102 ECA-1JM220 ECA-1JM221 ECA-2AM010 ECA-2AM100 ECA-2AM101 ECA-2AM101B
ECA-2AM102 ECA-2AM220 ECA-1EM472 ECA-1EM682 ECA-1HMR22 ECA-1HMR33 ECA-1HMR47 ECA1VM471 ECA-1VM472 ECA-1EM100 ECA-1EM101 ECA-1EM101B ECA-1EM101I ECA-1EM102 ECA-1EM220
ECA-1EM221 ECA-1EM222 ECA-1HM330 ECA-1EM331 ECA-1EM331BJ ECA-1EM332 ECA-1HM332 ECA-1HM333
ECA-1HM470 ECA-1HM471 ECA-1HM471 ECA-1HM471 ECA-1HM471 ECA-1HM332 ECA-1HM332 ECA-1HM333
ECA-1HM470 ECA-1HM471 ECA-1HM471B ECA-1HM487 ECA-1VM100 ECA-1VM101 ECA-1VM102 ECA-1VM202 ECA-1VM201 ECA-1VM201 ECA-1VM301 ECA-1VM302 ECA-1VM3032 ECA-1VM302 ECA-1VM3032 ECA-1VM3032 ECA-1VM3032 ECA-1VM3032 EC