


# PRODUCT DATA SHEET

Part Number: 1340100H

Type	Size	Rating	Description
Incandescent	T10	2.5V 0.83A	MES Halogen lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
2.5	747	830	913	-	-	-	-

Notes:

- 1 **Base Type** E10/13 Nickel plated
- 2 **Filament Shape** C-6
- 3 **Lamp Marking** 2.5V 0.83A
- 4 **Environmental** RoHS & REACH SVHC compliant