

## Magnecraft

191 Waukegan Rd, Ste 206

Northfield, IL 60093-2743

Phone: (847)441-2526


Fax: (847)441-2522

Email: info@magnecraft.com

## Item # 70S2-01-A-05-N, 70S2 Series Solid State Relays/N and S Style

### 70S2 Series Solid State Relays/N and S Style

The 70S2 Series relays have excellent thermal performance and are designed for medium-power loads. Its compact size makes it ideal for designs where space is limited. The design incorporates a triac output for AC loads and MOSFETs for DC loads. Optical isolation protects the control from transients. The 70S2 is available in a combination of screw, fast-on or PCB terminals.



[SPECIFICATIONS](#) · [OUTPUT CHARACTERISTICS](#) · [INPUT CHARACTERISTICS](#) · [PERFORMANCE CHARACTERISTICS](#) · [ENVIRONMENT](#) · [MISCELLANEOUS CHARACTERISTICS](#)

### SPECIFICATIONS

Component Type	Solid State
Mounting Type	Panel
Rated Current Load	5 A
Contact Configuration	SPST-NO
Control Voltage	DC
Load Type	DC
Input Voltage Range	3 to 30 VDC
Output Voltage Range	3 to 60 VDC

Switching Type	DC Switching
----------------	--------------

## OUTPUT CHARACTERISTICS

Switching Device	Triac
Current Rating	5 A
Switching Voltage	3 to 60 VDC
Min. Load Current to Maintain On	100 mA
Non-Repetitive Surge Current (1 cycle)	7 (1 SEC) A
Max. Off State Leakage Current [rms]	10 $\mu$ A
Minimum Peak Blocking Voltage	105 VDC
Typical On State Voltage Drop [rms]	1.85 VDC

## INPUT CHARACTERISTICS

Voltage Range	3 to 30 VDC
Must Release Voltage	1 VDC
Typical Input Current at 5VDC or 240VAC	5 to 40 mA
Maximum Reverse Control Voltage	3 VDC

## PERFORMANCE CHARACTERISTICS

Electrical Life (UL508), Operations at Rated Current (Resistive)	100000
Mechanical Life, Unpowered	10000000
Operating Time (Response Time) - On	ms 75 $\mu$ s
Operating Time (Response Time) - Off	ms 750 $\mu$ s
Dielectric Strength, Terminals to Chassis	2500 VAC

## ENVIRONMENT

Product Certifications, Standard Version	CSA UR
Ambient Air Temperature around the Device - Storage	-40 to +125 °C
Ambient Air Temperature around the Device - Operation	-40 to +100 °C

## MISCELLANEOUS CHARACTERISTICS

Thermal Resistance (Junction to Case)	4 °C/W
---------------------------------------	--------

---