Chip Beads (2512063007Y0)



Part Number: 2512063007Y0

MULTI- LAYER CHIP BEAD

Part Number System: Example 2512063017Y1

25	1206	301	7	Υ	1
Chip Bead	Package Size	Impedance Code	Packaging Code	Material Code	Current Code 0 < 1.0A
Code	Code	300 Ω	6= Bulk Packed Taped and Reeled 7" Reel	Y = Standard Signal Speed Z = High Signal Speed	1 ≥ 1.0A < 2.0A 3 > 3.0A < 4.0A
			Taped and Reeled 13" Reel	H = GHz Speed	5 ≥ 3.0A < 4.0A ETC

Fair- Rite offers a broad selection of cost effective multi- layer chip beads to suppress conducted EMI signals. Chip beads can be used in an array of devices such as cellular phones, computers, laptops, pagers, etc. The small package sizes accommodate automated placements and allow for a dense packaging of circuit boards.

Chip Beads are available in standard, high and GHz signal speeds.

Recommended Soldering Profile

Packaging Options:

- All multi- layer chip beads are supplied taped and reeled, if required bulk packed chip beads can be provided.


The suggested land patterns are in accordance to the latest revision of IPC-7351.

Weight: 0.03 (g)

Package Size: 1206 (3216)

1 acma	50 5120	. 1200 (321	<u> </u>		
Dim	mm	mm tol	nominal inch	inch misc.	
A	1.1	±0.20	0.043	_	
В	1.6	±0.20	0.063		
С	3.2	±0.20	0.126		
D	0.7	±0.30	0.028	_	
Land	Pattern	S			
V		W	X	Y	Z
1.20		2.80	1.80	1.60	
(0.04)	7")	(0.110")	(0.071")	(0.063")	_

Reel Informa	tion			
Tape Width mm	Pitch mm	Parts 7" Reel	Parts 13" Reel	Parts 14" Reel
8	4	3000	10000	




	A	В	C	D	Wt. (g)	Land Patterns			Reel Information			
Pkg. Size						٧	W (ref)	×	Y	Tape Width mm	Pitch	Part 7" Reel
0402 (1005)	0.5±0.05 0.020	0.5±0.05 0.020	1.0±0.05 0.040	0.25±0.15 0.010	0.002	0.40 0.016	1.30 0.051	0.70 0.028	0.90 0.035	8	4	1000
0603 (1608)	0.8±0.15 0.031	0.8±0.15 0.031	1.6±0.15 0.063	0.4±0.2 0.016	0.006	0.60 0.024	1.70 0.067	1.00	1.10 0.043	8	4	4000
0805 (2012)	0.9±0.2 0.035	1.25±0.2 0.049	2.0±0.2 0.079	0.5±0.3 0.020	0.01	0.60 0.024	1.90 0.075	1.50 0.059	1.30 0.051	8	4	4000
1206 (3216)	1.1±0.2 0.043	1.6±0.2 0.063	3.2±0.2 0.126	0.7±0.3 0.028	0.03	1.20 0.047	2.80 0.110	1.80 0.071	1.60 0.063	8	4	3000
1806 (4516)	1.6±0.2 0.063	1.6±0.2 0.063	4.5±0.2 0.177	0.7±0.3 0.028	0.06	2.00 0.079	3.90 0.154	1.80 0.071	1.90 0.075	12	8	2000
1812 (4532)	1.5±0.2 0.069	3.2±0.2 0.126	4.5±0.2 0.177	0.7±0.3 0.028	0.09	2.00	3.90 0.154	3.40 0.134	1.90 0.075	12	8	1000

Chart Legend + Test frequency

Typical Impe	edance (Ω)
50 MHz	22.5
100 MHz ⁺	30 ±25%
500 MHz	46
1000 MHz ⁺	-

Electrical Proper	rties
Max DCR (Ω)	0.1
Max Current (mA)	800

The impedance values listed are typical values. The nominal impedance with a \pm -25% tolerance is specified for the \pm marked 100 MHz. Chip beads are measured for impedance on the HP 4291A and fixture HP 16192A. Chip beads are 100% tested for impedance and dc resistance.



CSV Download

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fair-Rite: 2512063007Y0