
# 大容量積層セラミックコンデンサ HIGH VALUE MULTILAYER CERAMIC CAPACITORS

OPERATING TEMP.	BJ	BJ	-25~+85°C
		X7R	-55~+125°C
		X5R	-55~+85°C
	F	F	-25~+85°C
		Y5V	-30~+85°C



## 特長 FEATURES

- ・電極にNi金属を使用し、端子電極部にメッキをしてあることにより、はんだ付け性および耐熱性にすぐれ、マイグレーションもほとんど発生せず、高い信頼性を示します
- ・等価直列抵抗(ESR)が小さく、ノイズ吸収性にすぐれています。特にタンタルおよびアルミ電解コンデンサに比較した場合
- ・高い許容リップル電流値
- ・高い定格電圧でありながら小型形状
- ・絶縁抵抗、破壊電圧が高く信頼性にすぐれる 等の特徴があります

- The use of Nickel(Ni) as material for both the internal and external electrodes improves the solderability and heat resistance characteristics. This almost completely eliminates migration and raises the level of reliability significantly.
- Low equivalent series resistance(ESR) provides excellent noise absorption characteristics.
- Compared to tantalum or aluminum electrolytic capacitors these ceramic capacitors offer a number of excellent features, including:

Higher permissible ripple current values

Smaller case sizes relative to rated voltage

Improved reliability due to higher insulation resistance and break-down voltage.

#### 用途 APPLICATIONS

- ・デジタル回路全般
- ・電源バイパスコンデンサ 液晶モジュール用 液晶駆動電圧ライン用 電源電圧の高いLSI、IC、OPアンプ用
- ・平滑コンデンサ DC-DCコンバータ(入力、出力側用) スイッチング電源(2次側用)

- · General digital circuit
- Power supply bypass capacitors
   Liquid crystal modules
   Liquid crystal drive voltage lines
   LS I, I C, converters(both for input and output)
- Smoothing capacitors DC-DC converters (both for input and output) Switching power supplies (secondary side)

#### 形名表記法 ORDERING CODE


4



2			
シリー	·ズ名		
M	<b>秸屋コンデンサ</b>		

3		
端子電	極	
K	メッキ品	1

形状寸法 (EIA)L×W(mm		
	107(0603)	1.6×0.8
	212(0805)	2.0×1.25
	316(1206)	3.2×1.6
	325(1210)	3.2×2.5
	432(1812)	4.5×3.2



公称前	電容量 (pF)
例	
473	47,000
105	1,000,000

U		
容量許	F容差	
K	±10	%
M	±20	%
Z	± 80 ± 20	%


8	
製品厚	[み(mm)
Α	0.8
D	0.85
F	1.15
G	1.25
Н	1.5
L	1.6
N	1.9
M	2.5
U	3.2

個別仕	:様		
_	標準		
10			
包装			
В	単品(袋づめ)		
T	リールテーピング		
1			
当社管	当社管理記号		
Δ	標準品		
	△= スペース		

9



6



2			
Series name			
М	Multilayer ceramic		
IVI	capacitors		



4	
Dimensions(ca	ase size)(mm)
107(0603)	1.6×0.8
212(0805)	2.0×1.25
316(1206)	3.2×1.6
325(1210)	3.2×2.5
432(1812)	4.5×3.2

Temperature characteristics code		
△F Y5V		-30~+85℃ +22/-82%
BJ X7R	-55~+125℃ ±15%	
ВЈ	X5R	-55~+85℃ ±15%
		△=Blank space


6	△-blank space	
Nomin	al capacitance(pF)	_
example		_
473	47,000	
105	1,000,000	_
		_

Capaci	tance tolerances(%)
K	±10
М	±20
Z	± 80 ± 20
8	
Thickr	ness(mm)
Α	0.8
D	0.85
F	1 15

Thickn	iess(mm)
Α	0.8
D	0.85
F	1.15
G	1.25
Н	1.5
L	1.6
N	1.9
М	2.5
Ū	3.2

9	
Specia	al code
_	Standard products
Packa	ging
В	Bulk
Т	Tape & reel
<b>①</b>	
Interna	al code

#### 外形寸法 EXTERNAL DIMENSIONS



Type(EIA)	L	W	Т		е
□MK107	1.6±0.10	0.8±0.10	0.45±0.05 (0.018±0.002)	к	0.35±0.25
(0603)	(0.063±0.004)	(0.031±0.004)	0.8±0.10 (0.031±0.004)	Α	(0.014±0.010)
			0.45±0.05 (0.018±0.002)	К	
□MK212 (0805)	2.0±0.10 (0.079±0.004)	1.25±0.10 (0.049±0.004)	0.85±0.10 (0.033±0.004)	D	0.5±0.25 (0.02±0.010)
			1.25±0.10 *1 (0.049±0.004)	G	
			0.85±0.10 (0.033±0.004)	D	
□MK316	3.2±0.15	1.6±0.15	1.15±0.10 (0.045±0.004)	F	0.5 <sup>+0.35</sup> <sub>-0.25</sub>
(1206)	(0.126±0.006)	(0.063±0.006)	1.25±0.10 (0.049±0.004)	G	$(0.020^{+0.014}_{-0.010})$
			1.6±0.20 (0.063±0.008)	L	
			0.85±0.10 (0.033±0.004)	D	
			1.15±0.10 (0.045±0.004)	F	
□MK325 (1210)	3.2±0.30 (0.126±0.012)	2.5±0.20 (0.098±0.008)	1.5±0.10 (0.059±0.004)	Н	0.6±0.3 (0.024±0.012)
			1.9±0.20 (0.075±0.008)	N	
			2.5±0.20 (0.098±0.008)	М	
□MK432	4.5±0.40	3.2±0.30	2.5±0.20 (0.098±0.008)	М	0.9±0.6
(1812)	(0.177±0.016)	(0.126±0.012)	3.2±0.30 (0.125±0.012)	U	(0.035±0.024)

Unit: mm (inch)

注:\*1. ±0.15mm公差あり

Note: \*1. Includding dimension tolerance  $\pm 0.15$ mm ( $\pm 0.006$ inch).

## 概略バリエーション AVAILABLE CAPACITANCE RANGE

■汎用積層セラミックコンデンサ General Multilaver Ceramic Capacitors

//\t/H.	17570											٠		······	, 0.				_	чρ	u01																												
Cap	Тур	е			1	07										2	12											3	16									3	25							4	132		
	Temp.C				BJ/X				Ύ5۷			J/X						(5R				=/Y				BJ/						/Y5			J/X				/X5I			F/Y				J/X5		F/\	
	VDC		5 16	25	16	10	3.3	16	106.	350	35	25	16	10	50	35	25	16	10	6.3	50	16	10	6.3	50	35 2	5 1	6 10	16	6.3	50	35	10	50	25	16 1	0 3	5 25	16	6.3	50	35	10€	3.3 2	25 1	6 1	0 6.3	3 10	6.3
[μF]	[pF:3diç	gits]																																															
0.022	223	3 /	Α							С																																							
0.033	333	3	Α							С	_																$\perp$															$\perp$	$\perp$	$\perp$					
0.047	473	3	Α							G		D				$\perp$											$\perp$	$\perp$	$\perp$													$\perp$	$\perp$						
0.068	683	3	Α							G		D															$\perp$															$\perp$	$\perp$	$\perp$					
0.10			Α	Α						G						$\perp$													$\perp$													$\perp$	$\perp$						
0.15			$\perp$		Α					G	à			Ц	_							_			F	Ε	4																_						
0.22					Α		_	Α						Ш	G	_					D			_	L	F	_		$\perp$									$\perp$	$\perp$			_	_	_				Ш.	
0.33		_	$\perp$			Α					G			Ш								$\perp$				F	=																_					<u> </u>	
0.47	474					Α		Α					L			G					G				L													$\perp$	$\perp$			_	_	_				Ш.	
0.68		_	$\perp$		_	А	_						G		_	_						$\perp$			_	LI	_ F																_					<u> </u>	
1.0	105		$\perp$			Α			A					G		$\perp$		G		(	G					L	F	3	$\perp$					ΗΙ	Ν			$\perp$				_		$\perp$		$\perp$			
1.5	155	_	$\perp$												_	_	_										L			$\perp$									$\perp$		$\sqcup$	_						Ш.	
2.2	225						Α		P	4						_			G			G					L				G				Н		N		$\perp$				_					Ш.	
3.3		_				_	_	_		$\perp$	$\perp$			Ш	_	_	_			G	_	_			_	$\perp$	$\perp$	L	L		╙				Ν		$\perp$	┖		╙		_	$\perp$	_	_			₩.	Ш
4.7	475		$\perp$			_	_	_		_				Ш	_	_	_		_	G	_		G		_	_	$\perp$	L	L		╙	G				Ν		Ν			Н	4	$\dashv$	4	_	_		$\perp$	
6.8			$\perp$			_	_	_		_				Ш	_	_	_	_	_		_	_	_		_	_	$\perp$	_	_		_	<u> </u>			_		_		$\perp$		$\sqcup$	_	$\rightarrow$	4	_	_		₩.	Ш
10.0			$\perp$			_	_	_		_				Ш	_	_	_			G	_	_		G	_	_	$\perp$	$\perp$	$\perp$	L			L			1	1	M	I N		_	Н	_		V			Щ.	
22.0			_	_	Ш	_	_	_		1	1	1	_	Ш	_	_	_		_	_	_	_			_	4	$\perp$	1	1	L		_	L		_	_	1	1	$\perp$	М	$\Box$	4	Ν	_	Ν	NΝ			
47.0			$\perp$			_	_	_		1	$\perp$			Ш	_	_			_		_				_	_	$\perp$	$\perp$	$\perp$	$\perp$	_	$\perp$					$\perp$	$\perp$	$\perp$	М	$\leftarrow$	_		Ν	_	$\perp$		IM	
100.0	107	7			Ш																						$\perp$														ш	ᆚ	_	M	丄	止	U		M

■低背積層セラミックコンデンサ Low profile Multilayer Ceramic Capacitors

	Туре	10				212				31	6				325		
	Temp.Char	BJ/X5R	F/Y5V	BJ/	X7R	BJ/X5R	F/\	/5V	BJ/X7R	BJ/X5R	F/Y	′5V	BJ/X7R	BJ/X7R	BJ/X5R	F/Y	′5V
	VDC	6.3	6.3	16	10	6.3	10	6.3	10	6.3	10	6.3	25	10	6.3	16	10
[μF]	[pF:3digits]																
0.47	474	K		D													
0.68	684			D													
1.0	105		K		D	K							D				
2.2	225						D		D								
3.3	335								F	D				D			
4.7	475							D		D	D			F			
6.8	685									F							
10.0	106										F	D			D	F	
22.0	226																F

			温度特性				
温度特性コード			Temperature chara	acteristics		静電容量許容差[%]	tanδ(%)
Temp. char.Code	準抄	0.規格	温度範囲[℃]	基準温度(℃)	静電容量変化率(%)	Capacitance tolerance	Dissipation factor
	Applicabl	le standard	Temperature range	Ref. Temp.	Capacitance change		
BJ	JIS	BJ	-25~85	20	±10	±20(M)	2.5%max.**
D0	EIA	X7R*	<b>−55~125</b>	25	±15	±10(K)	2.5 /011147.
	JIS	F	-25~85	20	+30 -80	+80 -20(Z)	7.0%max.***
F	EIA	Y5V	<b>−30~85</b>	25	+22 -82	-20 <sup>(Z)</sup>	/.u√ornax."""

★Some exceptions apply, Refer to the available capacitance range table for the parts which are only available in X5R.

★★3.5%max:LMKtype; 107type (C≤0.47μF), 212type (C>1.0μF), 316/y25/432type

■ 325type (C>22μF), 432type (C>10μF), 低背316type (C=4.7μF)

■ EMKtype; 107/212/316/325/432type

\*★★3.5/max : LMktype ; 107type (C≤0.47 μF), 212type (C≤1.0 μF), 316/325/432type EMktype ; 107/212/316/325/432type TMktype ; 107/212/316/325/432type TMktype ; 216type (C≤0.47 μF), 325type, 432type GMktype ; 212type, 316type, 325type UMktype ; 212type (C>0.1 μF), 316type (C≥0.47 μF), 325type

5.0%max : JMKtype ; 107type ( $C \le 1.0 \mu F$ ), 212type( $C \le 4.7 \mu F$ ), 316type( $C \le 10.0 \mu F$ ), 325type( $C \le 2.2 \mu F$ ), 432type( $C \le 4.7 \mu F$ )

LMKtype ; 107type (C>0.47 $\mu$ F), 212type (C\ge 2.2 $\mu$ F)

セレクションガイド Selection Guide アイテム一覧 Part Numbers

特性図 Electrical Characteristics

梱包 Packaging

信頼性 Reliability Data

UMKtype; 325type 16%max:JMKtype; 107/212/316/325/432type LMKtype; 107/325/432, 汎用316type (C>10 μF)

使用上の注意 Precautions

**■** P.8







39

## アイテム一覧 PART NUMBERS

#### ■107TYPE (0603 case size) -

<b>—</b> 10/111 L (	3000 0030 3120)						
定格	形名	公 称 静電容量	温度特性	$ an\delta$	実装条件 Soldering method	静電容量 許容差	厚 ア Thickness
電 圧 RatedVoltage	Ordering code	Capacitance [ $\mu$ F]	Temperature characteristics	Dissipation factor [%]Max.	R:リフロー Reflow soldering W:フロー Wave soldering	Capacitance tolerance	[mm] (inch)
25V	TMK107BJ223□A	0.022	BJ/X7R	2.5			
250	TMK107BJ104□A	0.1	BJ/X5R				
	EMK107BJ333□A	0.033					
	EMK107BJ473□A	0.047	BJ/X7R				
16V	EMK107BJ683□A	0.068			R,W		
100	EMK107BJ104□A	0.1		3.5		±10%	$0.8\pm0.10$
	EMK107BJ154□A	0.15				±20%	$(0.031\pm0.004)$
	EMK107BJ224□A	0.22					
	LMK107BJ334□A	0.33					
10V	LMK107BJ474□A	0.47	BJ/X5R				
100	LMK107BJ684□A	0.68		5	R		
	LMK107BJ105□A	1.0		3	, n		
6.3V	JMK107BJ225MA*	2.2		10		+20%	
16V	EMK107F224ZA	0.22		7	R,W		
100	EMK107F474ZA	0.47	F/Y5V	,	Π, ۷۷	+80%	$0.8\pm0.10$
10V	LMK107F105ZA	1.0	1/150	16	R	-20%	$(0.031\pm0.004)$
6.3V	JMK107F225ZA	2.2		10	n		

形名の $\square$ には静電容量許容差記号が入ります。  $\square$  Please specify the capacitance tolerance code.

#### ■212TYPE (0805 case size)

定格	形名	公 称	温度特性	$ an \delta$	実装条件	静電容量	厚み
電圧		静電容量	Temperature	B'	Soldering method	許容差	Thickness
RatedVoltage	Ordering code	Capacitance	characteristics	Dissipation factor	R:リフロー Reflow soldering	Capacitance	[mm] (inch)
Tialca voltage	Grading code	[μF]	ond dotonous	[%]Max.	W:フロー Wave soldering	tolerance	[IIIII] (IIII)
	UMK212BJ223□D	0.022					0.85±0.1
	UMK212BJ333□D	0.033					$(0.033\pm0.004)$
	UMK212BJ473□G	0.047	BJ/X7R	2.5			
50V	UMK212BJ683□G	0.068	DU/A/11				
	UMK212BJ104□G	0.1					1.25±0.1
	UMK212BJ154□G	0.15				±10%	(0.049±0.004)
	UMK212BJ224□G	0.22	BJ/X5R	3.5	R,W	±10% ±20%	(0.049±0.004)
05)/	GMK212BJ334□G	0.33	BJ/X7R	3.5		±20%	
35V	GMK212BJ474□G	0.47	BJ/X5R				
051/	TMK212BJ473□D	0.047		0.5	]		0.85±0.1
25V	TMK212BJ683□D	0.068	BJ/X7R	2.5			(0.033±0.004)
40)/	EMK212BJ684□G	0.68					
16V	EMK212BJ105□G	1.0	BJ/X5R	3.5			1.25±0.1
10V	LMK212BJ105□G	1.0	BJ/X7R				$(0.049\pm0.004)$
100	LMK212BJ225MG	2.2					
2.01/	JMK212BJ335MG	3.3	BJ/X5R	5	R	±20%	1.25±0.15
6.3V	JMK212BJ475MG	4.7	DJ/ASH		l n	±20%	
	JMK212BJ106MG*	10		10			(0.049±0.006)
	UMK212F224ZD	0.22					0.85±0.1(0.033±0.004)
50V	UMK212F474ZG	0.47		7	R,W		
	UMK212F105ZG	1.0	F/Y5R	1	n,vv	+80%	
16V	EMK212F225ZG	2.2	F/TOH			-20%	1.25±0.1
10V	LMK212F475ZG	4.7	İ	9	R	20%	$(0.049\pm0.004)$
6.3V	JMK212F106ZG	10		16	1 8		

形名の $\square$ には静電容量許容差記号が入ります。  $\square$  Please specify the capacitance tolerance code.

<sup>\*</sup>高温負荷試験の試験電圧は定格電圧の1.5倍 \* Test Voltage of Loading at high temperature test is 1.5 time of the rated voltage.

<sup>\*</sup>高温負荷試験の試験電圧は定格電圧の1.5倍 \* Test Voltage of Loading at high temperature test is 1.5 time of the rated voltage.

#### ■316TYPE(1206 case size) —

		公 称			実装条件	静電容量	
定格	形名		温度特性	$tan \delta$			厚み
電圧		静電容量	Temperature	Dissipation	Soldering method	許容差	Thickness
RatedVoltage	Ordering code	Capacitance	characteristics	factor	R:リフロー Reflow soldering	Capacitance	(inch)
- iaioa i oilago	Ordoning codo	[μF]	onaraotonouoo	[%]Max.	W:フロー Wave soldering	tolerance	(IIICII)
	UMK316BJ154□F	0.15		2.5			1.15±0.1 (0.045±0.004)
50V	UMK316BJ224□L	0.22		2.5			
	UMK316BJ474□L	0.47					1 0 1 0 0 (0 000 1 0 000)
35V	GMK316BJ684□L	0.68		3.5			1.6±0.2 (0.063±0.008)
33 V	GMK316BJ105□L	1.0					
	TMK316BJ154□D	0.15				±10%	0.85±0.1 (0.033±0.004)
	TMK316BJ224□ F	0.22	BJ/X7R	2.5	R,W	±20%	1.15±0.1 (0.045±0.004)
25V	TMK316BJ334□F	0.33					1.10±0.1 (0.040±0.004)
	TMK316BJ684□L	0.68					1.6±0.2 (0.063±0.008)
	EMK316BJ684□ F	0.68					4.45.4.4.40.4.5.4.00.40
	EMK316BJ105□ F	1.0					1.15±0.1 (0.045±0.004)
16V	EMK316BJ225ML	2.2		3.5			
	EMK316BJ335ML	3.3	BJ/X5R				
	EMK316BJ475ML	4.7	Do/ASIT				
10V	LMK316BJ335ML	3.3	BJ/X7R			±20%	1.6±0.2 (0.063±0.008)
100	LMK316BJ475ML	4.7	- D3/X/H		R		
6.3V	JMK316BJ106ML	10	BJ/X5R	5			
0.3 V	JMK316BJ226ML*	22	DJ/ASH	10	1		
50V	UMK316F225ZG	2.2		-	R,W		1 05 10 1 (0 010 10 001)
35V	GMK316F475ZG	4.7	F 0/5)/	7		+80%	1.25±0.1 (0.049±0.004)
10V	LMK316F106ZL	10	F/Y5V	9	R	-20%	1.0.10.0.(0.000.10.000)
100	LMK316F226ZL	22	]	16			1.6±0.2 (0.063±0.008)

形名の $\square$ には静電容量許容差記号が入ります。  $\square$  Please specify the capacitance tolerance code.

#### ■325TYPE(1210 case size) -

定格	形名	公 称	温度特性	$ an\delta$	実装条件	静電容量	厚み
電圧	,,, ,	静電容量	Temperature	D'antantan	Soldering method	許容差	Thickness
RatedVoltage	Ordering code	Capacitance	characteristics	Dissipation factor	R:リフロー Reflow soldering		[mm] (inch)
- lated voltage	Ordering code	[μF]	Characteristics	[%]Max.	W:フロー Wave soldering	tolerance	[mm] (inch)
50V	UMK325BJ105□H	1.0	BJ/X7R		R,W	±10% ± 20%	1.5±0.1 (0.059±0.004)
35V	GMK325BJ225MN	2.2	BJ/X5R				1.9±0.2 (0.075±0.008)
	TMK325BJ225MH	2.2	BJ/X7R				1.5±0.1 (0.059±0.004)
25V	TMK325BJ335MN	3.3	20/74/11				1 0+0 0 (0 075+0 000)
257	TMK325BJ475MN	4.7	BJ/X5R	3.5			1.9±0.2 (0.075±0.008)
	TMK325BJ106MM*	10	DJ/A3N	3.5			2.5±0.2 (0.098±0.008)
16V	EMK325BJ475MN	4.7	BJ/X7R		R	±20%	
	EMK325BJ106MN	10	BJ/X5R				1.9±0.2 (0.075±0.008)
10V	LMK325BJ106MN	10	BJ/X7R				
6.3V	JMK325BJ226MM	22	BJ/X5R	5			2.5±0.2 (0.098±0.008)
0.5 V	JMK325BJ476MM*	47	DJ/ASN	10			2.020.2 (0.00020.000)
50V	UMK325F475ZH	4.7		9			1.5±0.1 (0.059±0.004)
35V	GMK325F106ZH	10		7		1.0007	1.020.1 (0.00020.001)
10V	LMK325F226ZN	22	F/Y5V		R	+80%	1.9±0.2 (0.075±0.008)
6.3V	JMK325F476ZN	47		16		-20%	1.0_0.2 (0.070±0.000)
U.3V	JMK325F107ZM*	100					2.5±0.2 (0.098±0.008)

<sup>\*</sup>高温負荷試験の試験電圧は定格電圧の1.5倍 \* Test Voltage of Loading at high temperature test is 1.5 time of the rated voltage.

形名の $\square$ には静電容量許容差記号が入ります。  $\square$  Please specify the capacitance tolerance code.

<sup>\*</sup>高温負荷試験の試験電圧は定格電圧の1.5倍 \* Test Voltage of Loading at high temperature test is 1.5 time of the rated voltage.

## アイテム一覧 PART NUMBERS

■432TYPE(1812 case size) —

0= =(	312 0a30 3120)						
定格 電圧	形名	公 新電容量 Capacitance	温度特性 Temperature	tan δ Dissipation	実装条件 Soldering method R:リフロー Reflow soldering	静電容量 許容差 Capacitance	厚 み Thickness
RatedVoltage	Ordering code	Capacitance [μF]	characteristics	factor	W:7D — Wave soldering	tolerance	[mm] (inch)
25V	TMK432BJ106MM	10					
16V	EMK432BJ226MM*	22		3.5			
10V	LMK432BJ226MM	22	BJ/X5R		R	±20%	2.5±0.2 (0.098±0.008)
6.3V	JMK432BJ476MM*	47		5			
0.01	JMK432BJ107MU*	100		10			3.2±0.3 (0.125±0.012)
10V	LMK432F476ZM*	 47	F/Y5V	16	R	+80%	2.5±0.2 (0.098±0.08)
6.3V	JMK432F107ZM*	100	1713	10		-20%	2.0±0.2 (0.000±0.00)

<sup>\*</sup>高温負荷試験の試験電圧は定格電圧の1.5倍

<sup>\*</sup> Test voltage of Loading at high temperature test is 1.5 times of the rated voltage.

# アイテム一覧 PART NUMBERS

■107TYPE(00	603 case size) ———						
定格電圧	形名	公 称 静電容量	温度特性 Temperature	tan δ	実装条件 Soldering method	静電容量 許容差	厚 み Thickness
RatedVoltage	Ordering code	Capacitance [µF]	characteristics	tactor		Capacitance tolerance	[mm] (inch)
6.3V	JMK107BJ474□K	0.47	BJ/X5R	5	R	±10%,±20%	0.45±0.05
0.5 V	JMK107F105ZK	1.0	F/Y5V	16		+80%,-20%	$(0.018\pm0.002)$

形名の□には静電容量許容差記号が入ります。

■212TYPE(0805 case size)
--------------------------

<b>-</b> 212111 L(00	000 0000 0120)						
定格電圧	形名	公 称 静電容量	温度特性 Temperature	tan δ	実装条件 Soldering method	静電容量 許容差	厚 み Thickness
RatedVoltage	Ordering code	Capacitance [µF]	characteristics		R:リフロー Reflow soldering W:フロー Wave soldering	Capacitance tolerance	[mm] (inch)
16V	EMK212BJ474□D	0.47			R, W	±10%	
160	EMK212BJ684□D	0.68	BJ/X7R	3.5	Π, ۷۷	±10% ±20%	0.85±0.1 (0.033±0.004)
10V	LMK212BJ105□D	1.0			R	±20%	
6.3V	JMK212BJ105□K	1.0	BJ/X5R	5		±10%	0.45±0.05 (0.018±0.002)
10V	LMK212F225ZD	2.2	F/Y5V	9	R	+80%	0.85±0.1 (0.033±0.004)
6.3V	JMK212F475ZD	4.7	F/15V	16	n	-20%	0.00-0.1 (0.000-0.004)

形名の□には静電容量許容差記号が入ります。

## ■316TYPE(1206 case size) —


_0101111(12	200 0000 0120)							
定格 電圧 RatedVoltage	形名	公 新電容量 Capacitance	温度特性 Temperature	tan δ Dissipation factor	実装条件 Soldering method R:リフロー Reflow soldering	静電容量 許容差 Capacitance	厚 Thick	
nateuvoitage	Ordering code	[μF]	characteristics	[%]Max.	W:フロー Wave soldering	tolerance	[mm]	(inch)
10V	LMK316BJ225MD	2.2	BJ/X7R	3.5			0.85±0.1 (0	.033±0.004)
100	LMK316BJ335MF	3.3	D0/X/11	3.5		±20%	1.15±0.1 (0	.045±0.004)
	JMK316BJ335MD	3.3			R		0.85±0.1 (0	.033±0.004)
6.3V	JMK316BJ475MD	4.7	BJ/X5R	5			(0	
	JMK316BJ685MF	6.8					1.15±0.1 (0	.045±0.004)
10V	LMK316F475ZD	4.7		9		+80% -20%	0.85±0.1 (0	.033±0.004)
	LMK316F106ZF	10	F/Y5V	16	R		1.15±0.1 (0	.045±0.004)
6.3V	JMK316F106ZD	10		10			0.85±0.1 (0	.033±0.004)


#### ■325TYPE(1210 case size) —


定格 電圧 RatedVoltage	形 名 Ordering code	公 称 静電容量 Capacitance [µF]	温度特性 Temperature characteristics		実装条件 Soldering method R:リフロー Reflow soldering W:フロー Wave soldering	静電容量 許容差 Capacitance tolerance	厚 み Thickness [mm] (inch)
25V	TMK325BJ105MD	1.0					0.85±0.1 (0.033±0.004)
10V	LMK325BJ335MD	3.3	BJ/X7R	3.5	R	±20%	0.00=0.1 (0.000=0.001)
100	LMK325BJ475MF	4.7					1.15±0.1 (0.045±0.004)
6.3V	JMK325BJ106MD	10	BJ/X5R	5			0.85±0.1 (0.033±0.004)
16V	EMK325F106ZF	10	F/Y5V	7	R	+80%	1.15±0.1 (0.045±0.004)
10V	LMK325F226ZF	22	F/Y5V	16		-20%	1.10±0.1 (0.043±0.004)


## インピーダンス・ESR-周波数特性例 Example of Impedance ESR vs. Frequency characteristics


・当社積層セラミックコンデンサ例 (Taiyo Yuden multilayer ceramic capacitor)












































## Multilayer Ceramic Capacitor Chips

			Specific					
Item		Temperature Compensating (Class 1)		High Permitivity (Class 2)		Test Methods and Remarks		
		Standard	High Frequency Type	Standard Note1	High Value			
1.Operating Range	Temperature	-55 to +125℃		B: −55 to +125°C F: −25 to +85°C	-25 to +85℃	High Capacitance Type BJ(X7R) : −55 to +125°C BJ(X5R) : −55 to +85°C F(Y5V) : −30 to +85°C		
2.Storage	Temperature	-55 to +125℃		B: −55 to +125°C	-25 to +85℃	High Capacitance Type BJ(X7R): −55 to +125°C BJ(X5R): −55 to +85°C		
Range 3.Rated Volta	ge	50VDC,25VDC,	16VDC	F: -25 to +85°C 50VDC,25VDC	50VDC,35VDC,25VDC	F(Y5V): -30 to +85°C		
on latea Tona	90	16VDC		00150,20150	16VDC,10VDC,6.3VDC 4DVC			
4.Withstandin	g Voltage	No breakdown or dam-	No abnormality	No breakdown or dama	ge	Applied voltage: Rated voltage×3 (Class 1)		
Between ter	rminals	age				Rated voltage×2.5 (Class 2) Duration: 1 to 5 sec. Charge/discharge current: 50mA max. (Class 1,2)		
5.Insulation F	lesistance	10000 MΩ min.		smaller.	$M\Omega .,$ whichever is the	Applied voltage: Rated voltage Duration: 60±5 sec.		
6 Canacitano	a (Tolerance)	0.5 to 5 pE: +0.25 pE	0.5 to 2 pF : +0.1 pF	Note 4	B1:+10% +20%	Charge/discharge current: 50mA max.  Measuring frequency:		
оография	T to TupF: ±0.5 pF  5 to 10 pF: ±1 pF  11 pF or over: ±5%  ±10%  105TYPERA, SA, TA, UA only  0.5~2pF: ±0.1pF  2.2~200F: ±5%  Clas  Clas		Class1: 1MHz±10%(C≦1000pF) 1 k Hz±10%(C>1000pF) Class2: 1 k Hz±10%(C≤22 <sub>µ</sub> F) 120Hz±10Hz(C>22 <sub>µ</sub> F)					
7.Q or Tangen (tan &)	it of Loss Angle	Under 30 pF : Q≥400 + 20C 30 pF or over : Q≥1000 C= Nominal capacitance	Refer to detailed specification	B: 2.5% max.(50V, 25V) F: 5.0% max. (50V, 25V)	BJ: 2.5% max. (50V, 35V, 25V) 3.5% max. % 5.0% max. % 10.0% max. % F: 7.0% max. 5.0% max. % 9.0% max. % 11.0% max. % 16.0% max. % 20.0% max. % % See Table.1	Multilayer: $\begin{array}{l} \text{Multilayer:} \\ \text{Measuring frequency:} \\ \text{Class1:} 1\text{MHz}\pm10\%(\text{C} \leq 1000\text{pF}) \\ 1\text{ k Hz}\pm10\%(\text{C} > 1000\text{pF}) \\ \text{Class2:} 1\text{ k Hz}\pm10\%(\text{C} \leq 22_{\mu}\text{F}) \\ 120\text{Hz}\pm10\text{Hz}(\text{C} > 22_{\mu}\text{F}) \\ \text{Measuring voltage:} \\ \text{Class1:} 0.5\sim5\text{Vrms}(\text{C} \leq 1000\text{pF}) \\ 1\pm0.2\text{Vrms}(\text{C} > 1000\text{pF}) \\ \text{Class2:} 1\pm0.2\text{Vrms}(\text{C} \leq 22_{\mu}\text{F}) \\ 0.5\pm0.1\text{Vrms}(\text{C} > 22_{\mu}\text{F}) \\ \text{Bias application: None} \\ \text{High-Frequency-Multilayer:} \\ \text{Measuring frequency:} 1\text{GHz} \\ \text{Measuring equipment:} \text{HP4291A} \\ \text{Measuring ijg:} \text{HP16192A} \\ \end{array}$		
8.Temperature Characteristic of Capacitance	(Without voltage application)	CK: 0±250 CJ: 0±120 CH: 0±60 CG: 0±30 PK: -150±250 PJ: -150±120 PH: -150±60 RK: -220±250 RJ: -220±120 RH: -220±60 SK: -330±250 SJ: -330±120 SH: -330±60 TK: -470±250 TJ: -470±120 TH: -470±60 UK: -750±250 UJ: -750±120	CH: 0±60 RH: -220±60 (ppm/C)	B:±10%(-25~85°) F: +30 %(-25~85°) B(X7R):±15% F(Y5V): +82 %	BJ: ±10%(-25~85°C) F: +30 % (-25~85°C) BJ(X7R,XSR): ±15% F(Y5V): +22 %	According to JIS C 5102 clause 7.12.  Temperature compensating: Measurement of capacitance at 20°C and 85°C shall be mad to calculate temperature characteristic by the following equation.  (Cess - C20)  C20 × ΔT  × 10 6 (ppm/C)  High permittivity: Change of maximum capacitance deviation in step 1 to Temperature at step 1: +20°C  Temperature at step 2: minimum operating temperature Temperature at step 3: +20°C (Reference temperature) Temperature at step 4: maximum operating temperature Temperature at step 5: +20°C  Reference temperature for X7R, X5R and Y5V shall be +25°C		
9.Resistance Substrate	to Flexure of	SL: +350 to -1000 (ppm/C) Appearance: No abnormality Capacitance change: Within ±5% or ±0.5 pF, whichever is larger.	Appearance: No abnormality Capacitance change: Within±0.5 pF	Appearance: No abnormality Capacitance change: B, BJ: Within ±12.5% F: Within ±30%		Warp: 2mm Testing board: paper-phenol substrate Thickness: 1.6mm The measurement shall be made with board in the bent positi  Board  Warp  Warp  (Unit: mm)		

#### Multilayer Ceramic Capacitor Chips

	Specified Value						
Item	Temperature Com	pensating (Class 1)	High Permitti	ivity (Class 2)	Test Methods and Remarks		
	Standard	High Frequency Type	Standard Note1	High Value			
10.Body Strength	_	No mechanical damage.	_	_	High Frequency Multilayer:  Applied force: 5N  Duration: 10 sec.  Press  Chip  L  L  W  O.6L  L  W		
11.Adhesion of Electrode	No separation or indication of separation of electrode.				Applied force: 5N  Duration: 30±5 sec.  Hooked jig  Reds  Chip  Cross-section		
12.Solderability	At least 95% of terminal	electrode is covered by n	new solder.		Solder temperature: 230±5°C  Duration: 4±1 sec.		
13.Resistance to soldering	Appearance: No abnormality Capacitance change: Within ± 2.5% or ±0.25pF, whichever is larger. Q: Initial value Insulation resistance: Initial value Withstanding voltage (between terminals): No abnormality	Appearance: No abnormality Capacitance change: Within ±2.5% Q: Initial value Insulation resistance: Initial value Withstanding voltage (between terminals): No abnormality	Appearance: No abnormality Capacitance change: Within ±7.5% (B, BJ) Within ±20% (F) Solder temperat Duration: 3±0.5 Preheating condi Withstanding voltage (between terminals): No abnormality  Appearance: No abnormality Capacitance change: Within ±7.5% (B, BJ) Within ±20% (F) Capacitance change: Within ±7.5% (B, BJ) Within ±20% (F) Conditions for 1 Step 1: Minimun Step 2: Room te Withstanding voltage (between terminals): No abnormality  Step 3: Maximun Step 4: Room te Number of cycle		Preconditioning: Thermal treatment (at 150°C for 1 hr) (Applicable to Class 2.) Solder temperature: 270±5°C Duration: 3±0.5 sec. Preheating conditions: 80 to 100°C, 2 to 5 min. or 5 to 10 min 150 to 200°C, 2 to 5 min. or 5 to 10 min Recovery: Recovery for the following period under the stan dard condition after the test. 24±2 hrs (Class 1) 48±4 hrs (Class 2)		
14.Thermal shock	Appearance: No abnormality Capacitance change: Within ± 2.5% or ±0.25pF, whichever is larger. Q: Initial value Insulation resistance: Initial value Withstanding voltage (between terminals): No abnormality	Appearance: No abnormality Capacitance change: Within ±0.25pF Q: Initial value Insulation resistance: Initial value Withstanding voltage (between terminals): No abnormality			Preconditioning: Thermal treatment (at 150°C for 1 hr)  (Applicable to Class 2.)  Conditions for 1 cycle:  Step 1: Minimum operating temperature 30±3 min.  Step 2: Room temperature 15 min.  Step 3: Maximum operating temperature 30±3 min.  Step 4: Room temperature 15 min.  Number of cycles: 5 times  Recovery after the test: 24±2 hrs (Class 1)  48±4 hrs (Class 2)		
15.Damp Heat (steady state)	Appearance: No abnormality Capacitance change: Within ±5% or ±0.5pF, whichever is larger. Q: C≥30 pF : Q≥350 10≤C<30 pF: Q≥275 +2.5C C<10 pF : Q≥200 + 10C C: Nominal capacitance Insulation resistance: 1000 MΩ min.	Appearance: No abnormality Capacitance change: Within ±0.5pF, Insulation resistance: 1000 MΩ min.	Appearance: No abnormality Capacitance change: B: Within $\pm 12.5\%$ F: Within $\pm 30\%$ tan $\delta$ : B: 5.0% max. F: 7.5% max. Insulation resistance: 50 M $\Omega$ $\mu$ F or 1000 M $\Omega$ whichever is smaller.	Appearance: No abnormality Capacitance change: BJ: Within $\pm 12.5\%$ F: Within $\pm 30\%$ $\tan \delta$ : BJ: 5.0% $\max$ . 7.5% $\max$ .% 20.0% $\max$ .% F: 11.0% $\max$ . 7.5% $\max$ .% 16.0% $\max$ .% 19.5% $\max$ .% 25.0% $\max$ .% % See Table.2 Insulation resistance: 50 $\max \mu$ F or 1000 $\min \mu$ C whichever is smaller.	Multilayer:  Preconditioning: Thermal treatment (at 150°C for 1 hr)  (Applicable to Class 2.)  Temperature: 40±2°C  Humidity: 90 to 95% RH  Duration: 500 +24 hrs  Recovery: Recovery for the following period under the standard condition after the removal from test chamber.  24±2 hrs (Class 1)  48±4 hrs (Class 2)  High-Frequency Multilayer:  Temperature: 60±2°C  Humidity: 90 to 95% RH  Duration: 500 +24 hrs  Recovery: Recovery for the following period under the standard condition after the removal from test chamber.  24±2 hrs (Class 1)		

#### Multilayer Ceramic Capacitor Chips

		Specifie				
Item	Temperature Compensating (Class 1)		High Permittivity (Class 2)		Test Methods and Remarks	
	Standard	High Frequency Type	Standard Note1	High Value		
6.Loading under Damp Heat	Appearance: No abnor-	Appearance: No abnor-	Appearance: No abnor-	Appearance: No abnor-	According to JIS C 5102 Clause 9. 9.	
	mality	mality	mality	mality	Multilayer:	
	Capacitance change:	Capacitance change:	Capacitance change:	Capacitance change:	Preconditioning: Voltage treatment (Class 2)	
	Within ± 7.5% or	C≦2 pF: Within ±0.4 pF	B: Within ±12.5%	BJ: Within ± 12.5%	Temperature: 40±2℃	
	±0.75pF, whichever is	C>2 pF: Within ±0.75	F: Within ±30%	(50V, 35V, 25V)	Humidity: 90 to 95% RH	
	larger.	pF	tan δ: B: 5.0% max.	Within ± 15.0% (16V	Duration: $500^{+24}_{-0}$ hrs	
	Q: C≧30 pF: Q≧200	C: Nominal capaci-	F: 7.5% max.	and under)	Applied voltage: Rated voltage	
	C<30 pF: Q≥100 +	tance		F: Within ±30%	Charge and discharge current: 50mA max. (Class 1,2)	
	10C/3	Insulation resistance:	Insulation resistance:	tan δ: BJ: 5.0% max.	Recovery: Recovery for the following period under the stand	
	C: Nominal capaci-	500 MΩ min.	25 M $\Omega \mu$ F or 500 M $\Omega$ ,	7.5% max. **	condition after the removal from test chamber.	
	tance		whichever is the smaller.	20.0% max. **	24±2 hrs (Class 1)	
	Insulation resistance:			F: 11.0% max.	48±4 hrs (Class 2)	
	500 MΩ min.			7.5% max.*	High-Frequency Multilayer:	
				16.0% max.*	Temperature: 60±2℃	
				19.5% max.*	Humidity: 90 to 95% RH	
				25.0% max.*	Duration: 500 $^{+24}_{-0}$ hrs	
				*See Table.2	Applied voltage: Rated voltage	
				Insulation resistance:	Charge and discharge current: 50mA max.	
				25 MΩ μF or 500 MΩ,	Recovery: 24±2 hrs of recovery under the standard cor	
				whichever is the smaller.	tion after the removal from test chamber.	
7.Loading at High Tempera-	Appearance: No abnor-	Appearance: No abnor-	Appearance: No abnor-	Appearance: No abnormality	According to JIS C 5102 clause 9.10.	
ture	mality	mality	mality	Capacitance change:	Multilayer:	
	Capacitance change:	Capacitance change:	Capacitance change:	BJ: Within ±12.5%	Preconditioning: Voltage treatment (Class 2)	
	Within ±3% or	Within ±3% or	B: Within ±12.5%	F: Within ±30%	Temperature:125±3°C(Class 1, Class 2: B, BJ(X7R))	
	±0.3pF, whichever is	±0.3pF, whichever is	F: Within ±30%	tan δ: 5.0% max.	85±2℃ (Class 2: BJ,F)	
	larger.	larger.	tan δ:	7.5% max.*	Duration: 1000 +48 hrs	
	Q: C≧30 pF : Q≧350	Insulation resistance:	B: 4.0% max.	20.0% max.*	Applied voltage: Rated voltage×2, , ×1.5 (Table.4)	
	10≦C<30 pF: Q≧275	1000 MΩ min.	F: 7.5% max.	F: 11.0% max.	Recovery: Recovery for the following period under the st	
	+ 2.5C	1000 1112 111111	Insulation resistance:	7.5% max.*	dard condition after the removal from test chamber.	
	C<10 pF: Q≥200 +		50 M $\Omega$ μF or 1000 M $\Omega$ ,	16.0% max.*	As for Ni product, thermal treatment shall be perforn	
	10C		whichever is smaller.	19.5% max.*	prior to the recovery.	
	C: Nominal			25.0% max.*	24±2 hrs (Class 1)	
	capacitance			%See Table.2	48±4 hrs (Class 2)	
	Insulation resistance:			Insulation resistance: 50	High-Frequency Multilayer:	
	1000 MΩ min.			$M\Omega \mu F$ or 1000 $M\Omega$ , which-	Temperature: 125±3°C (Class 1)	
	TOOO IVISZ TIIITI.			ever is smaller.	Duration: 1000 +48 hrs	
				ever is smaller.	Applied voltage: Rated voltage×2	
					Recovery: 24±2 hrs of recovery under the standard co	
					necovery. 24±2 firs of recovery under the standard col	

Note 1: For 105 type, specified in "High value".

Note 2: Thermal treatment (Multilayer): 1 hr of thermal treatment at 150 +0 /-10 °C followed by 48±4 hrs of recovery under the standard condition shall be performed before the measurement.

Note 3: Voltage treatment (Multilayer): 1 hr of voltage treatment under the specified temperature and voltage for testing followed by 48±4 hrs of recovery under the standard condition shall be performed before the measurement.

Note on standard condition: "standard condition" referred to herein is defined as follows: 5 to 35°C of temperature, 45 to 85% relative humidity, and 86 to 106kPa of air pressure.

When there are questions concerning measurement results: In order to provide correlation data, the test shall be conducted under condition of 20±2°C of temperature, 65 to 70% relative humidity, and 86 to 106kPa of air pressure. Unless otherwise specified, all the tests are conducted under the "standard condition."

Note 4: Specified value for Instration Resistance of Table.3 only: 100MΩ μF or more.

Table	1	tans(D	F)

Table. 1 tanδ(D. F.)	
Item	tan∂
BJ: LMK type; 063 type  105 type ( $C \le 0.047 \mu F$ )  107 type ( $C \le 0.47 \mu F$ )  212 type ( $C \le 1.4 F$ )  316 / 325 / 432 type  EMK type; 105 / 107 / 212 / 316 / 325 type  TMK type; 316 type( $C > 0.47 \mu F$ )  325 / 432 type  GMK type;212 type ( $C \ge 0.22 \mu F$ )  316 type ( $C \ge 0.68 \mu F$ )  325 type  UMK type;212 type ( $C \ge 0.1 \mu F$ )  316 type ( $C \ge 0.47 \mu F$ )  316 type ( $C \ge 0.47 \mu F$ )  325 type ( $C \ge 0.47 \mu F$ )	3.5%max.
BJ: JMK type; 063 type 107 type (C > 2.2 $\mu$ F) 212type (C > 10 $\mu$ F) 316type (C > 10 $\mu$ F) 325type (C > 22 $\mu$ F) 432type (C > 100 $\mu$ F) LMK type; 105 type (C≥0.056 $\mu$ F) 107 type (C > 0.47 $\mu$ F) 212 type (C > 1 $\mu$ F) J4K, E4K, L4K, J2K, L2K type F: 105 type (50V, 25V)	5.0% max.
F: LMK type; 212 type 316 type (C=10 μF): 汎用 (C=4.7 μF): 低背 325 type (C > 10 μF) EMK type; 105 type (C ≥ 0.068 μF) UMK type; 325 type (C ≥ 4.7 μF)	9.0% max.
BJ: Table. 3	10.0% max.
F: LMK type; 105 type (C =0.22 μF)	11.0% max.
F: JMK type; 105 / 107 / 212 / 316 / 325 / 432 type LMK type; 107 type,325 type 432 type,316 type (C > 10 \( \mu \)F)	16.0% max.
F: JMK type; 105 type (C=1μF) AMK type; 063 type	20.0% max.

Table 2 tans(D F)

Item	tan∂	
BJ: JMK type; 107 type ( $C > 2.2 \mu F$ )		
212type (C > 10 μF)		
316type (C > $22 \mu$ F)		
325type (C > $47 \mu$ F)		
432type (C > 100 μF)		
LMK type; 063 type	7.5% max.	
105 type (C≧0.056 μF)		
107 type (C≧0.47 μF)		
212 type (C > 1 μF)		
J4K, E4K, L4K, J2K, L2K type		
F: 105 type(50V, 25V)		
F: LMK type; 105 type (C=0.22μF)	16.0% max.	
F: JMK type; 105 / 107 / 212 / 316 / 325 / 432 type		
LMK type; 107 type	19.5% max.	
432 type		
BJ: Tabie.3	20.0% max.	
F: JMK type; 105 type (C =1 μF)	25.0% max.	
AMK type; 063 type		

#### Table. 3

Item
BJ: JMK type; 105 type (C =1 μF)
107(C > 1.0 μ F)
212(C>4.7 μF)
316(C>10 μF)
325(C>22 μF)
432(C>4.7 μF)

Table, 4

Table. 4
Item
BJ: 105(C>0.1 μF)
107(C>1.0 μF)
212(C>4.7 μF)
316(C>10 μF)
325(C>22 μF)
432(C>47 μF)
F: 105(C>0.47 μF)
212(C>4.7 μF)
325(C>22 μF)
432(C>47 μF)

## 梱包 PACKAGING

## ①標準数量 Standard quantity ■袋づめ梱包 Bulk packaging


The state of the s						
形式(EIA) Type	製品厚み Thickness		標準数量 Standard quantity			
Туре	mm(inch)	code	[pcs]			
□MK105(0402)	0.5 (0.020)	V				
E VK105(0402)	, ,	W				
□MK107(0603)	0.8 (0.031)	A Z				
□MK212(0805)	0.85 (0.033)	D				
_IVII (2 12 (0000)	1.25 (0.049)	G				
□4K212(0805)	0.85 (0.033)	D				
□2K212(0805)	0.85 (0.033)	D				
	0.85 (0.033)	D	1000			
□MK316(1206)	1.15 (0.045)	F				
□IVII\310(1200)	1.25 (0.049)	G				
	1.6 (0.063)	┙				
□4K316(1206)	1.15 (0.045)	F				
	0.85 (0.033)	D				
□MK325(1210)	1.15 (0.045)	F				
	1.5 (0.059)	Н				
	1.9 (0.075)	N				
	2.5 (0.098)	М				


■テーピング梱包 Taped packaging

形式(EIA) Type	製品厚み Thickness			数量 d quantity cs]
	mm(inch)		紙テープ paper	エンボステープ Embossed tape
□MK063(0201)	0.3 (0.012)	Р	15000	_
□MK105(0402)	0.5 (0.020)	V	10000	_
E VK105(0402)	, ,	W		
□MK107(0603)	0.45 (0.018)	К	4000	_
	0.8 (0.031)	A Z	4000	_
	0.45 (0.018)	K	4000	_
□MK212(0805)	0.85 (0.033)	D	4000	_
	1.25 (0.049)	G	_	3000
□4K212(0805)	0.85 (0.033)	D	4000	_
□2K212(0805)	0.85 (0.033)	D	4000	_
	0.85 (0.033)	D	4000	_
□MK316(1206)	1.15 (0.045)	F		3000
	1.25 (0.049)	G		3000
	1.6 (0.063)	L	_	2000
□4K316(1206)	1.15 (0.045)	F		3000
	0.85 (0.033)	D		
	1.15 (0.045)	F		0000
□MK325(1210)	1.5 (0.059)	Н		2000
	1.9 (0.075)	N		
	2.5 (0.098)	М	_	500
□MK432(1812)	2.5 (0.098)	М	_	500
□MK550(2220)	2.5 (0.098)	М	_	500


## ②テーピング材質 Taping material


紙テープ Card board carrier tape






エンボステープ Embossed Tape






## ③バルクカセット Bulk Cassette



105, 107, 212形状で個別対応致しますのでお問い合せ下さい。 Please contact any of our offices for accepting your requirement according to dimensions 0402, 0603, 0805.(inch)


## ③テーピング寸法 Taping dimensions 紙テープ Paper Tape (8mm幅) (0.315inches wide)



Type	チッフ	<sup>プ</sup> 挿入部	挿入ピッチ	テープ厚み
(EIA)	Chip	Cavity	Insertion Pitch	Tape Thickness
	Α	В	F	Т
□MK063(0201)	0.37±0.06	0.67±0.06	2.0±0.05	0.45max.
_IVIR-003(0201)	(0.06±0.002)	(0.027±0.002)	(0.079±0.002)	(0.018max.)
□MK105(0402)	0.65±0.1	1.15±0.1	2.0±0.05	0.8max.
E VK105(0402)	(0.026±0.004)	(0.045±0.004)	(0.079±0.002)	(0.031max.)
□MK107(0603)	1.0±0.2	1.8±0.2	4.0±0.1	1.1max.
□IVII(107(0003)	(0.039±0.008)	(0.071±0.008)	(0.157±0.004)	(0.043max.)
☐MK212(0805)	1.65±0.2	2.4+0.2		
□4K212(0805)	(0.065±0.008)	(0.094±0.008)	4.0±0.1	1.1max.
□2K212(0805)	(0.000±0.000)	(0.004±0.000)	(0.157±0.004)	(0.043max.)
□MK316(1206)	2.0±0.2	3.6±0.2	(0.107 ±0.004)	(0.0401118X.)
	(0.079±0.008)	(0.142±0.008)		

Unit: mm(inch)


#### エンボステープ Embossed tape (8mm幅) (0.315inches wide)



Туре	チップ挿入部		挿入ピッチ	テーフ	プ厚み
(EIA)	Chip	cavity	Insertion Pitch	Tape Th	ickness
	Α	В	F	K	Т
□MK212(0805)	1.65±0.2	2.4±0.2			
	(0.065±0.008)	(0.094±0.008)			
□MK316(1206)					
	2.0±0.2	3.6±0.2	4.0±0.1	2.5max.	0.6max
□4K316(1206)	(0.079±0.008)	(0.142±0.008)	(0.157±0.004)	(0.098max.)	(0.024max.)
□MZ205/1010\	2.8±0.2	3.6±0.2		3.4max.	
□MK325(1210)	(0.110±0.008)	(0.142±0.008)		(0.134max.)	

Unit: mm(inch)


エンボステープ Embossed tape (12mm幅) (0.472inches wide)




Туре	チップ挿入部		挿入ピッチ	テーフ	プ厚み
(EIA)	Chip cavity		Insertion Pitch	Tape Th	nickness
	A B		F	K	Т
□MK432(1812)	3.7±0.2 (0.146±0.008)	4.9±0.2 (0.193±0.008)	8.0±0.1 (0.315±0.004)	3.4max. (0.134max.)	0.6max. (0.024max.)
□MK550(2220)	5.4±0.2 (0.213±0.008)	6.1±0.2 (0.240±0.008)	8.0±0.1 (0.315±0.004)	3.5max. (0.138max.)	0.6max. (0.024max.)

Unit: mm(inch)

#### ④リーダ部/空部 Leader and Blank portion




#### ⑤リール寸法 Reel size



#### ⑥トップテープ強度 Top Tape Strength

トップテープのはがし力は下図矢印方向に $70.1\sim0.7$ Nとなります。 The top tape requires a peel-off force of  $0.1\sim0.7$ N in the direction of the arrow as illustrated below.



Stages	Precautions	Technical considerations
Stages  1.Circuit Design	Precautions  Verification of operating environment, electrical rating and performance  1. A malfunction in medical equipment, spacecraft, nuclear reactors, etc. may cause serious harm to human life or have severe social ramifications. As such, any capacitors to be used in such equipment may require higher safety and/or reliability considerations and should be clearly differentiated from components used in general purpose applications.  Operating Voltage (Verification of Rated voltage)  1. The operating voltage for capacitors must always be lower than their rated values.  If an AC voltage is loaded on a DC voltage, the sum of the two peak voltages should be lower than the rated value of the capacitor chosen. For a circuit where both an AC and a pulse voltage may be present, the sum of their peak voltages should also be lower than the capacitor's rated voltage.	Technical considerations
	Even if the applied voltage is lower than the rated value, the	
	reliability of capacitors might be reduced if either a high fre- quency AC voltage or a pulse voltage having rapid rise time is	
	present in the circuit.	
2.PCB Design	Pattern configurations (Design of Land-patterns)  1. When capacitors are mounted on a PCB, the amount of solder used (size of fillet) can directly affect capacitor performance. Therefore, the following items must be carefully considered in the design of solder land patterns:  (1) The amount of solder applied can affect the ability of chips to withstand mechanical stresses which may lead to breaking or cracking. Therefore, when designing land-patterns it is necessary to consider the appropriate size and configuration of the solder pads which in turn determines the amount of solder necessary to form the fillets.  (2) When more than one part is jointly soldered onto the same land or pad, the pad must be designed so that each component's soldering point is separated by solder-resist.	1.The following diagrams and tables show some examples of recommended patterns to prevent excessive solder amourts.(larger fillets which extend above the component end terminations)  Examples of improper pattern designs are also shown.  (1) Recommended land dimensions for a typical chip capacitor land patterns for PCBs Land pattern  Chip capacitor  Solder-resist  Chip capacitor  Chip capacitor  Type 107 212 316 325  L 1.6 2.0 3.2 3.2  Size W 0.8 1.25 1.6 2.5  A 0.8~1.0 1.0~1.4 1.8~2.5 1.8~2.5  B 0.5~0.8 0.8~1.5 0.8~1.7 0.8~1.7  C 0.6~0.8 0.9~1.2 1.2~1.6 1.8~2.5
		Recommended land dimensions for reflow-soldering (unit: mm)
		Type 063 105 107 212 316 325 432 550  L 0.6 1.0 1.6 2.0 3.2 3.2 4.5 5.7
		Size W 0.3 0.5 0.8 1.25 1.6 2.5 3.2 5.0
		A 0.20~0.30 0.45~0.55 0.6~0.8 0.8~1.2 1.8~2.5 1.8~2.5 2.5~3.5 3.7~4.7
		B 0.20~0.30 0.40~0.50 0.6~0.8 0.8~1.2 1.0~1.5 1.0~1.5 1.5~1.8 1.5~2.3 C 0.25~0.40 0.45~0.55 0.6~0.8 0.9~1.6 1.2~2.0 1.8~3.2 2.3~3.5 3.5~5.5
		Excess solder can affect the ability of chips to withstand mechanical stresses. Therefore please take proper precautions when designing land-patterns.
		Type 316 (4 circuits) 212 (4 circuits)  a
		Type 212 (2 circuits)
		0   W   1.25   a   0.5~0.6   b   0.5~0.6   a   □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □

а b

С d 0.5~0.6 0.5~0.6

1.0

Stages	Precautions	Technical considerations			
2.PCB Design		(2) Examples of	of good and bad solder applica	tion	
		Items	Not recommended	Recommended	
		Mixed mounting of SMD and leaded components	Lead wire of component	Solder-resist	
		Component placement close to the chassis	Chassis Solder(for grounding)	Solder-resist	
		Hand-soldering of leaded components near mounted components	Lead wire of component- Soldering iron	Solder-resist -	
		Horizontal component placement		Solder-resist	
	Pattern configurations (Capacitor layout on panelized [breakaway] PC boards)  1. After capacitors have been mounted on the boards, chips can	1-1. The following are examples of good and bad capacitor layout; SMD capac     be located to minimize any possible mechanical stresses from board warp or			
	be subjected to mechanical stresses in subsequent manufac-		Not recommended	Recommended	
	turing processes (PCB cutting, board inspection, mounting of additional parts, assembly into the chassis, wave soldering the reflow soldered boards etc.) For this reason, planning pattern configurations and the position of SMD capacitors should be carefully performed to minimize stress.	Deflection of the board		Position the component at a right angle to the rection of the mechanical stresses that are anticipated.	
	ondata so datorati, pontoninos to minimizo da doci.	1-2. To layout the ca	apacitors for the breakaway PC	board, it should be noted that the amount	
		of mechanical	stresses given will vary deper	nding on capacitor layout. The example	
		below shows re	commendations for better des	ign.	
		Perforati	on C Slit Magnitude of stress	D 0000	
		the capacitors of in order from le	an vary according to the metho	tions, the amount of mechanical stress on d used. The following methods are listed push-back, slit, V-grooving, and perfora- ust also consider the PCB splitting proce-	

dure.

Stages	Precautions		Technical consider	rations
3.Considerations for automatic placement	auto-  1. Excessive impact load should not be imposed on the capacitors when mounting onto the PC boards.  2. The maintenance and inspection of the mounters should be conducted periodically.		sing damage. To avoid this, the the pick-up nozzle: of the pick-up nozzle should be a ecting for deflection of the board. essure should be adjusted between amount of deflection of the board of the should be arount of deflection of the board of the samount of deflection of the should be adjusted between the sh	en 1 and 3 N static loads. caused by impact of the pick-up nozzl under the PC board. The following di
			Not recommended	Recommended
		Single-sided mounting	Cracks	Supporting pin
		Double-sided mounting	Solder peeling Cracks	Supporting pin-
		cracking of the this, the monito	capacitors because of mechanic ring of the width between the align	e nozzle height can cause chipping tal impact on the capacitors. To avo nment pin in the stopped position, ar pin should be conducted periodically
	Selection of Adhesives  1. Mounting capacitors with adhesives in preliminary assembly, before the soldering stage, may lead to degraded capacitor characteristics unless the following factors are appropriately checked; the size of land patterns, type of adhesive, amount applied, hardening temperature and hardening period. Therefore, it is imperative to consult the manufacturer of the adhesives on proper usage and amounts of adhesive to use.	shrinkage perce on the capacitor to the board ma should be noted	entage of the adhesive and that or rs and lead to cracking. Moreover, ay adversely affect component pla d in the application of adhesives.	esistance. The difference between the first the capacitors may result in stress, too little or too much adhesive applicacement, so the following precaution
		a. The adhesive s solder process. b. The adhesive s c. The adhesive s d. The adhesive s e. The adhesive s f. The adhesive r	hould have sufficient strength at he hould have good coating and thick hould be used during its prescribe hould harden rapidly nust not be contaminated.	kness consistency. ed shelf life.
			hould have excellent insulation che hould not be toxic and have no er	
		(2)The recommen	ded amount of adhesives is as fo	llows;
		Figure	212/316 case size	es as examples
		a	0.3mm	
		b c	100 ~12  Adhesives should no	· ·
		Amou	nt of adhesive A	After capacitors are bonded

Stages	Precautions	Technical considerations
. Soldering	Selection of Flux  1. Since flux may have a significant effect on the performance of capacitors, it is necessary to verify the following conditions prior to use;  (1) Flux used should be with less than or equal to 0.1 wt%  (equivelent to chroline) of halogenated content. Flux having a strong acidity content should not be applied.  (2) When soldering capacitors on the board, the amount of flux applied should be controlled at the optimum level.  (3) When using water-soluble flux, special care should be taken to properly clean the boards.	1-1. When too much halogenated substance (Chlorine, etc.) content is used to activate the flux, or highly acidic flux is used, an excessive amount of residue after soldering malead to corrosion of the terminal electrodes or degradation of insulation resistance of the surface of the capacitors.  1-2. Flux is used to increase solderability in flow soldering, but if too much is applied, a larg amount of flux gas may be emitted and may detrimentally affect solderability. To min mize the amount of flux applied, it is recommended to use a flux-bubbling system.  1-3. Since the residue of water-soluble flux is easily dissolved by water content in the air, the residue on the surface of capacitors in high humidity conditions may cause a degradation of insulation resistance and therefore affect the reliability of the components. The cleaning methods and the capability of the machines used should also be considered carefully when selecting water-soluble flux.
	Soldering Temperature, time, amount of solder, etc. are specified in accordance with the following recommended conditions.	1-1. Preheating when soldering Heating: Ceramic chip components should be preheated to within 100 to 130°C of the so dering.  Cooling: The temperature difference between the components and cleaning process should not be greater than 100°C.  Ceramic chip capacitors are susceptible to thermal shock when exposed to rapid or concertrated heating or rapid cooling. Therefore, the soldering process must be conducted wit great care so as to prevent malfunction of the components due to excessive thermal shock
		Recommended conditions for soldering [Reflow soldering] Temperature profile
		Temperature  (C) 300 250 250 150 100 0ver 1 minute Over 1
		1. The ideal condition is to have solder mass (fillet) controlled to 1/2 to 1/3 of the thic ness of the capacitor, as shown below:  Capacitor  Capacitor  PC board
		Because excessive dwell times can detrimentally affect solderability, soldering dur tion should be kept as close to recommended times as possible.
		[Wave soldering]  Temperature profile  Temperature (C) 300 250 Preheating 230°C 250°C 250°
		Caution  1. Make sure the capacitors are preheated sufficiently.  2. The temperature difference between the capacitor and melted solder should not ligreater than 100 to130°C  3. Cooling after soldering should be as gradual as possible.  4. Wave soldering must not be applied to the capacitors designated as for reflow soldering only.

Stages	Precautions	Technical considerations
4. Soldering		[Hand soldering] Temperature profile
		Temperature (C) 300 250 250 150 100 Over 1 minute Within Gradual 3 cooling seconds
		Caution  1. Use a 20W soldering iron with a maximum tip diameter of 1.0 mm.  2. The soldering iron should not directly touch the capacitor.
5.Cleaning	Cleaning conditions  1. When cleaning the PC board after the capacitors are all mounted, select the appropriate cleaning solution according to the type of flux used and purpose of the cleaning (e.g. to remove soldering flux or other materials from the production process.)	The use of inappropriate solutions can cause foreign substances such as flux residue to adhere to the capacitor or deteriorate the capacitor's outer coating, resulting in a degradation of the capacitor's electrical properties (especially insulation resistance).      Inappropriate cleaning conditions (insufficient or excessive cleaning) may detrimentally affect the performance of the capacitors.
	Cleaning conditions should be determined after verifying, through a test run, that the cleaning process does not affect the capacitor's characteristics.	(1)Excessive cleaning In the case of ultrasonic cleaning, too much power output can cause excessive vibration of the PC board which may lead to the cracking of the capacitor or the soldered portion, or decrease the terminal electrodes' strength. Thus the following conditions should be carefully checked;
		Ultrasonic output Below 20 W/ℓ Ultrasonic frequency Below 40 kHz Ultrasonic washing period 5 min. or less
6.Post cleaning processes	With some type of resins a decomposition gas or chemical reaction vapor may remain inside the resin during the hardening period or while left under normal storage conditions resulting in the deterioration of the capacitor's performance.	
	When a resin's hardening temperature is higher than the capacitor's operating temperature, the stresses generated by the excess heat may lead to capacitor damage or destruction.  The use of such resins, molding materials etc. is not recommended.	
7.Handling	Breakaway PC boards (splitting along perforations)  1. When splitting the PC board after mounting capacitors and other components, care is required so as not to give any stresses of deflection or twisting to the board.  2. Board separation should not be done manually, but by using the appropriate devices.	
	Mechanical considerations  1. Be careful not to subject the capacitors to excessive mechanical shocks.  (1)If ceramic capacitors are dropped onto the floor or a hard surface, they should not be used.	
	(2)When handling the mounted boards, be careful that the mounted components do not come in contact with or bump against other boards or components.	

Stages	Precautions	Technical considerations
8.Storage conditions	Storage  1. To maintain the solderability of terminal electrodes and to keep the packaging material in good condition, care must be taken to control temperature and humidity in the storage area. Humidity should especially be kept as low as possible.  Recommended conditions  Ambient temperature Below 40°C  Humidity Below 70% RH  The ambient temperature must be kept below 30°C. Even under ideal storage conditions capacitor electrode solderability decreases as time passes, so ceramic chip capacitors should be used within 6 months from the time of delivery.  The packaging material should be kept where no chlorine or sulfur exists in the air.  2. The capacitance value of high dielectric constant capacitors (type 2 &3) will gradually decrease with the passage of time, so this should be taken into consideration in the circuit design. If such a capacitance reduction occurs, a heat treatment of 150°C for 1hour will return the capacitance to its initial level.	If the parts are stored in a high temperature and humidity environment, problems such as reduced solderability caused by oxidation of terminal electrodes and deterioration of taping/packaging materials may take place. For this reason, components should be used within 6 months from the time of delivery. If exceeding the above period, please check solderability before using the capacitors.