

SCS215AM SiC Schottky Barrier Diode


V _R	650V
I _F	15A
Q _C	23nC

Features


Construction

- 1) Shorter recovery time
- 2) Reduced temperature dependence
- 3) High-speed switching possible

Outline



Inner circuit



Packaging specifications

	Packaging	Tube
	Reel size (mm)	-
Tuno	Tape width (mm)	-
Туре	Basic ordering unit (pcs)	50
	Packing code	С
	Marking	SCS215AM

Silicon carbide epitaxial planer Schottky Diode

●Absolute maximum ratings (T _j = 25°C)					
Parameter	Symbol	Value	Unit		
Reverse voltage (repetitive peak)	V _{RM}	650	V		
Reverse voltage (DC)	V _R	650	V		
Continuous forward current	I _F	15* ¹	А		
	I _{FSM}	55* ²	А		
Surge no repetitive forward current		200* ³	А		
		43* ⁴	А		
Repetitive peak forward current	I _{FRM}	34* ⁵	А		
Total power disspation	P _D	39* ⁶	W		
Junction temperature	T _j	175	°C		
Range of storage temperature	T _{stg}	-55 to +175	°C		

*1 T_c=55°C *2 PW=8.3ms sinusoidal, T_i=25°C *3 PW=10 μ s square, T_i=25°C

*4 PW=8.3ms sinusoidal, $T_j=150^{\circ}C$ *5 $T_c=100^{\circ}C$, $T_j=150^{\circ}C$, Duty cycle=10% *6 Tc=25°C

•Electrical characteristics ($T_j = 25^{\circ}C$)

Parameter	Symbol	Conditions	Values			L locit
Parameter			Min.	Тур.	Max.	Unit
DC blocking voltage	V _{DC}	I _R =0.3mA	600	-	-	V
	V _F	I _F =15A,T _j =25°C	-	1.35	1.55	V
Forward voltage		I _F =15A,T _j =150°C	-	1.55	-	V
		I _F =15A,T _j =175°C	-	1.63	-	V
Reverse current	I _R	V _R =600V,T _j =25°C	-	3	300	μA
		V _R =600V,T _j =150°C	-	45	-	μA
		V _R =600V,T _j =175°C	-	105	-	μA
Total capacitance	С	V _R =1V,f=1MHz	-	550	-	pF
		V _R =600V,f=1MHz	-	56	-	pF
Total capacitive charge	Q _c	V _R =400V,di/dt=350A/μs	-	23	-	nC
Switching time	t _c	V _R =400V,di/dt=350A/μs	-	18	-	ns

•Thermal characteristics

Parameter	Symbol	Conditions	Values			Unit
Falameter	Symbol		Min.	Тур.	Max.	Unit
Thermal resistance	R _{th(j-c)}	-	-	3.2	3.8	°C/W

•Electrical characteristic curves

Fig.1 V_F - I_F Characteristics





Fig.2 V_F - I_F Characteristics

Fig.3 V_R - I_R Characteristics

Fig.4 V_R-Ct Characteristics



•Electrical characteristic curves






Fig.5 Thermal Resistance vs. Pulse Width

Fig.7 Ip-Tc Derating Curve



Fig.6 Power Dissipation





125

150

175

Average Rectified Forward Current : Io [A]

	Notes
1)	The information contained herein is subject to change without notice.
2)	Before you use our Products, please contact our sales representative and verify the latest specifications :
3)	Although ROHM is continuously working to improve product reliability and quality, semicon ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The periphera conditions must be taken into account when designing circuits for mass production.
5)	The technical information specified herein is intended only to show the typical functions of an examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly any license to use or exercise intellectual property or other rights held by ROHM or any othe parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use or such technical information.
6)	The Products specified in this document are not designed to be radiation tolerant.
7)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.
8)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
9)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
10)	ROHM has used reasonable care to ensur the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
11)	Please use the Products in accordance with any applicable environmental laws and regulations such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
12)	When providing our Products and technologies contained in this document to other countries you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
13)	This document, in part or in whole, may not be reprinted or reproduced without prior consent or ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

General Precaution

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in an y way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.