CSM_A16_DS_E_8_1

Separate Construction with Cylindrical 16-dia. Body

- Miniature design of 28.5 mm, the smallest class in the industry.
- Detachable Switch Unit.
- The same contacts can be used for both standard loads and microloads.
- Easy-to-wire terminal arrangement.
- Certified for EN 60947-5-1.



Refer to Safety Precautions for All Pushbutton Switches and Safety Precautions on page 24.


List of Models

		Model	
	Rectangular	Square	Round
Solder terminals	A16□-J Series	A16□-A Series	A16□-T Series
PCB terminals	A16□-J Series	A16□-A Series	A16□-T Series
Voltage- reduction lighting solder terminals	A16□-J Series	A16□-A Series	A16□-T Series
Screw-less clamp models	A16□-J Series	A16□-A Series	A16□-T Series

OMRON

Model Number Structure

Model Number Legend The model numbers used to order sets of Units are illustrated below. One set comprises the Pushbutton, Lamp (lighted models only), Case, and Switch. For information on combinations, refer to Ordering Information on pages 3 to 7.



- Solder terminals are available only with 100-V models.
- The Voltage Reduction Unit is not available for models with PCB terminals.
- "T2" is available only for the Screw-less Clamp type.

Ordering as a SetThe model numbers used to order sets of Units are given in the following tables. One set comprises the Pushbutton, Lamp (lighted models only), Case, and Switch.

Solder Terminal Models

Rectangular Models



IP40

			A10 0		
Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *1
	LED without	5 VDC	A16L-J□M-5D-1	A16L-J□A-5D-1	R: red, Y: yellow PY: pure yellow
	Voltage Reduction	12 VAC/VDC	A16L-J□M-12D-1	A16L-J□A-12D-1	G: green, A: blue W: white
	Unit	24 VAC/VDC	A16L-J□M-24D-1	A16L-J□A-24D-1	PW: pure white
SPDT	Incandescent lamp	5 VAC/VDC	A16L-J□M-5-1	A16L-J□A-5-1	R: red, Y: yellow
		12 VAC/VDC	A16L-J□M-12-1	A16L-J□A-12-1	PY: pure yellow
		24 VAC/VDC	A16L-J□M-24-1	A16L-J□A-24-1	G: green, W: white A: blue
	Non-lighted		A16-J□M-1	A16-J□A-1	B: black *2
	LED without	5 VDC	A16L-J□M-5D-2	A16L-J□A-5D-2	R: red, Y: yellow PY: pure yellow
	Voltage Reduction	12 VAC/VDC	A16L-J□M-12D-2	A16L-J□A-12D-2	G: green, A: blue W: white
	Unit	24 VAC/VDC	A16L-J□M-24D-2	A16L-J□A-24D-2	PW: pure white
DPDT		5 VAC/VDC	A16L-J□M-5-2	A16L-J□A-5-2	R: red, Y: yellow
	Incandescent lamp	12 VAC/VDC	A16L-J□M-12-2	A16L-J□A-12-2	PY: pure yellow
		24 VAC/VDC	A16L-J□M-24-2	A16L-J□A-24-2	G: green, W: white A: blue
	Non-lighted		A16-J□M-2	A16-J□A-2	B: black *2

^{*1.} Enter the desired color symbol for the Pushbutton in the \square . *2. Black ("B") Pushbuttons are only available for non-lighted models.



Oil-resistant IP65

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *1
	LED without	5 VDC	A165L-J□M-5D-1	A165L-J□A-5D-1	R: red, Y: yellow
	Voltage Reduction	12 VAC/VDC	A165L-J□M-12D-1	A165L-J□A-12D-1	PY: pure yellow G: green, A: blue W: white
	Unit	24 VAC/VDC	A165L-J□M-24D-1	A165L-J□A-24D-1	PW: pure white
SPDT		5 VAC/VDC	A165L-J□M-5-1	A165L-J□A-5-1	R: red, Y: yellow
	Incandescent lamp	12 VAC/VDC	A165L-J□M-12-1	A165L-J□A-12-1	PY: pure yellow G: green, W: white A: blue
		24 VAC/VDC	A165L-J□M-24-1	A165L-J□A-24-1	
	Non-lighted		A165-J□M-1	A165-J□A-1	B: black *2
	LED without	5 VDC	A165L-J□M-5D-2	A165L-J□A-5D-2	R: red, Y: yellow PY: pure yellow
	Voltage Reduction	12 VAC/VDC	A165L-J□M-12D-2	A165L-J□A-12D-2	G: green, A: blue W: white
DDDT	Unit	24 VAC/VDC	A165L-J□M-24D-2	A165L-J□A-24D-2	PW: pure white
DPDT		5 VAC/VDC	A165L-J□M-5-2	A165L-J□A-5-2	R: red, Y: yellow PY: pure yellow
	Incandescent lamp	12 VAC/VDC	A165L-J□M-12-2	A165L-J□A-12-2	
	р	24 VAC/VDC	A165L-J□M-24-2	A165L-J□A-24-2	G: green, W: white A: blue
	Non-lighted		A165-J□M-2	A165-J□A-2	B: black *2

^{*1.} Enter the desired color symbol for the Pushbutton in the \square .

Individual models: Refer to pages 9 to 13.

(The Pushbutton, Lamp, Case, and Switch can be ordered separately.)

- Ratings: Refer to page 16. Characteristics: Refer to page 16.
- Accessories: Refer to page 15.

^{*2.} Black ("B") Pushbuttons are only available for non-lighted models.

Ordering as a Set The model numbers used to order sets of Units are given in the following tables. One set comprises the Pushbutton, Lamp (lighted models only), Case, and Switch.

Solder Terminal Models

Square Models



IP40

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *1
	LED without	5 VDC	A16L-A□M-5D-1	A16L-A□A-5D-1	R: red, Y: yellow PY: pure yellow
	Voltage Reduction	12 VAC/VDC	A16L-A□M-12D-1	A16L-A□A-12D-1	G: green, A: blue W: white
	Unit	24 VAC/VDC	A16L-A□M-24D-1	A16L-A□A-24D-1	PW: pure white
SPDT		5 VAC/VDC	A16L-A□M-5-1	A16L-A□A-5-1	R: red, Y: yellow
	Incandescent lamp	12 VAC/VDC	A16L-A□M-12-1	A16L-A□A-12-1	PY: pure yellow G: green, W: white A: blue
		24 VAC/VDC	A16L-A□M-24-1	A16L-A□A-24-1	
	Non-lighted		A16-A□M-1	A16-A□A-1	B: black *2
	LED without	5 VDC	A16L-A□M-5D-2	A16L-A□A-5D-2	R: red, Y: yellow PY: pure yellow
	Voltage Reduction	12 VAC/VDC	A16L-A□M-12D-2	A16L-A□A-12D-2	G: green, A: blue W: white
DDDT	Unit	24 VAC/VDC	A16L-A□M-24D-2	A16L-A□A-24D-2	PW: pure white
DPDT		5 VAC/VDC	A16L-A□M-5-2	A16L-A□A-5-2	R: red, Y: yellow
	Incandescent lamp	12 VAC/VDC	A16L-A□M-12-2	A16L-A□A-12-2	PY: pure yellow
	p	24 VAC/VDC	A16L-A□M-24-2	A16L-A□A-24-2	G: green, W: white A: blue
	Non-lighted		A16-A□M-2	A16-A□A-2	B: black *2

^{*1.} Enter the desired color symbol for the Pushbutton in the \square . *2. Black ("B") Pushbuttons are only available for non-lighted models.



Oil-resistant IP65

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *1	
	LED without	5 VDC	A165L-A□M-5D-1	A165L-A□A-5D-1	R: red, Y: yellow PY: pure yellow	
	Voltage Reduction	12 VAC/VDC	A165L-A□M-12D-1	A165L-A□A-12D-1	G: green, A: blue	
	Unit	24 VAC/VDC	A165L-A□M-24D-1	A165L-A□A-24D-1	W: white PW: pure white	
SPDT		5 VAC/VDC	A165L-A□M-5-1	A165L-A□A-5-1	R: red, Y: yellow	
	Incandescent lamp	12 VAC/VDC	A165L-A□M-12-1	A165L-A□A-12-1	PY: pure yellow G: green, W: white A: blue	
		24 VAC/VDC	A165L-A□M-24-1	A165L-A□A-24-1		
	Non-lighted		A165-A□M-1	A165-A□A-1	B: black *2	
	LED without	5 VDC	A165L-A□M-5D-2	A165L-A□A-5D-2	R: red, Y: yellow PY: pure yellow	
	Voltage Reduction	12 VAC/VDC	A165L-A□M-12D-2	A165L-A□A-12D-2	G: green, A: blue W: white	
DDDT	Unit	24 VAC/VDC	A165L-A□M-24D-2	A165L-A□A-24D-2	PW: pure white	
DPDT		5 VAC/VDC	A165L-A□M-5-2	A165L-A□A-5-2	R: red, Y: yellow	
	Incandescent lamp	12 VAC/VDC	A165L-A□M-12-2	A165L-A□A-12-2	PY: pure yellow G: green, W: white A: blue	
	ia.i.p	24 VAC/VDC	A165L-A□M-24-2	A165L-A□A-24-2		
	Non-lighted		A165-A□M-2	A165-A□A-2	B: black *2	

^{*1.} Enter the desired color symbol for the Pushbutton in the \Box .

Individual models: Refer to pages 9 to 13.

(The Pushbutton, Lamp, Case, and Switch can be ordered separately.)

^{*2.} Black ("B") Pushbuttons are only available for non-lighted models.

[■] Ratings: Refer to page 16. ■ Characteristics: Refer to page 16.

[■] Accessories: Refer to page 15.

Ordering as a SetThe model numbers used to order sets of Units are given in the following tables. One set comprises the Pushbutton, Lamp (lighted models only), Case, and Switch.

Solder Terminals

Round Models

IP40



Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *1	
	LED without	5 VDC	A16L-T□M-5D-1	A16L-T□A-5D-1	R: red, Y: yellow PY: pure yellow	
	Voltage Reduction	12 VAC/VDC	A16L-T□M-12D-1	A16L-T□A-12D-1	G: green, A: blue W: white	
	Unit	24 VAC/VDC	A16L-T□M-24D-1	A16L-T□A-24D-1	PW: pure white	
SPDT		5 VAC/VDC	A16L-T□M-5-1	A16L-T□A-5-1	R: red, Y: yellow	
	Incandescent lamp	12 VAC/VDC	A16L-T□M-12-1	A16L-T□A-12-1	PY: pure yellow G: green, W: white	
		24 VAC/VDC	A16L-T□M-24-1	A16L-T□A-24-1	A: blue	
	Non-lighted		A16-T□M-1	A16-T□A-1	B: black *2	
	LED without	5 VDC	A16L-T□M-5D-2	A16L-T□A-5D-2	R: red, Y: yellow PY: pure yellow	
	Voltage Reduction	12 VAC/VDC	A16L-T□M-12D-2	A16L-T□A-12D-2	G: green, A: blue W: white	
DDDT	Unit	24 VAC/VDC	A16L-T□M-24D-2	A16L-T□A-24D-2	PW: pure white	
DPDT		5 VAC/VDC	A16L-T□M-5-2	A16L-T□A-5-2	R: red, Y: yellow	
	Incandescent lamp	12 VAC/VDC	A16L-T□M-12-2	A16L-T□A-12-2	PY: pure yellow	
		24 VAC/VDC	A16L-T□M-24-2	A16L-T□A-24-2	G: green, W: white A: blue	
	Non-lighted		A16-T□M-2	A16-T□A-2	B: black *2	

^{*1.} Enter the desired color symbol for the Pushbutton in the \square .

^{*2.} Black ("B") Pushbuttons are only available for non-lighted models.



Oil-resistant IP65

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *1	
	LED without	5 VDC	A165L-T□M-5D-1	A165L-T□A-5D-1	R: red, Y: yellow PY: pure yellow	
	Voltage Reduction	12 VAC/VDC	A165L-T□M-12D-1	A165L-T□A-12D-1	G: green, A: blue W: white	
	Unit	24 VAC/VDC	A165L-T□M-24D-1	A165L-T□A-24D-1	PW: pure white	
SPDT		5 VAC/VDC	A165L-T□M-5-1	A165L-T□A-5-1	R: red, Y: yellow	
	Incandescent lamp	12 VAC/VDC	A165L-T□M-12-1	A165L-T□A-12-1	PY: pure yellow	
		24 VAC/VDC	A165L-T□M-24-1	A165L-T□A-24-1	G: green, W: white A: blue	
	Non-lighted		A165-T□M-1	A165-T□A-1	B: black *2	
	LED without	5 VDC	A165L-T□M-5D-2	A165L-T□A-5D-2	R: red, Y: yellow PY: pure yellow	
	Voltage Reduction	12 VAC/VDC	A165L-T□M-12D-2	A165L-T□A-12D-2	G: green, A: blue W: white	
DDDT	Unit	24 VAC/VDC	A165L-T□M-24D-2	A165L-T□A-24D-2	PW: pure white	
DPDT		5 VAC/VDC	A165L-T□M-5-2	A165L-T□A-5-2	R: red, Y: yellow	
	Incandescent lamp	12 VAC/VDC	A165L-T□M-12-2	A165L-T□A-12-2	PY: pure yellow	
	idilip	24 VAC/VDC	A165L-T□M-24-2	A165L-T□A-24-2	G: green, W: white A: blue	
	Non-lighted		A165-T□M-2	A165-T□A-2	B: black *2	

^{*1.} Enter the desired color symbol for the Pushbutton in the \square .

Individual models: Refer to pages 9 to 13.

(The Pushbutton, Lamp, Case, and Switch can be ordered separately.)

- Ratings: Refer to page 16. Characteristics: Refer to page 16.
- Accessories: Refer to page 15.

^{*2.} Black ("B") Pushbuttons are only available for non-lighted models.

Ordering as a Set The model numbers used to order sets of Units are given in the following tables. One set comprises the Pushbutton, Lamp (lighted models only), Case, and Switch.

Models with Reduced-voltage Lighting and Solder Terminals



A16□-T1

Note: Models with voltage ratings of 200 to 220 VAC/DC (T2 models) are listed with models with screw-less clamp

IP40

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *
SPDT	LED (with built-in	100/110 VAC/VDC	A16L-∆□M-T1-1	A16L-∆□A-T1-1	R: red, Y: yellow PY: pure yellow
DPDT	reduced-voltage	100/110 VAC/VDC	A16L-∆□M-T1-2	A16L-∆□A-T1-2	G: green, W: white A: blue PW: pure white


^{*} Enter the desired shape for the Pushbutton in Δ : J (rectangular), A (square), or T (round). Enter the desired color symbol for the Pushbutton in the \Box .

Oil-resistant IP65

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *
SPDT	LED (with built-in	100/110 VAC/VDC	A165L-∆□M-T1-1	A165L-∆□A-T1-1	R: red, Y: yellow PY: pure yellow
DPDT	reduced-voltage	100/110 VAC/VDC	A165L-∆□M-T1-2	A165L-∆□A-T1-2	G: green, W: white A: blue PW: pure white

^{*} Enter the desired shape for the Pushbutton in Δ : J (rectangular), A (square), or T (round). Enter the desired color symbol for the Pushbutton in the \Box .

Screw-less Clamp Models



IP40

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Pushbutton color symbol *1	
		5 VDC	A16L-∆□M-5D-2S	A16L-∆□A-5D-2S		
	LED	LED	12 VAC/VDC	A16L-∆□M-12D-2S	A16L-∆□A-12D-2S	R: red, Y: yellow
		24 VAC/VDC	A16L-∆□M-24D-2S	A16L-∆□A-24D-2S	PY: pure yellow G: green, W: white	
DPDT	reduced-voltage	100/110 VAC/VDC	A16L-∆□M-T1-2S	A16L-∆□A-T1-2S	A: blue PW: pure white	
		200/220 VAC/VDC	A16L-∆□M-T2-2S	A16L-∆□A-T2-2S	B: black *2	
	Non-lighted		A16-∆□M-2S	A16-∆□A-2S		

^{*1.} Enter the desired shape for the Pushbutton in ∆: J (rectangular), A (square), or T (round). Enter the desired color symbol for the Pushbutton in the □. *2. Black ("B") Pushbuttons are only available for non-lighted models.

Oil-resistant IP65


Output	Lighting	Item Operating voltage	Wolfiertary operation	Alternate operation (Self-holding)	Pushbutton color symbol *1
DPDT		5 VDC	A165L-∆□M-5D-2S	A165L-∆□A-5D-2S	
	LED	12 VAC/VDC	A165L-∆□M-12D-2S	A165L-∆□A-12D-2S	R: red, Y: yellow
		24 VAC/VDC	A165L-∆□M-24D-2S	A165L-∆□A-24D-2S	PY: pure yellow G: green, W: white
	LED (with built-in reduced-voltage lighting function)	100/110 VAC/VDC	A165L-∆□M-T1-2S	A165L-∆□A-T1-2S	A: blue PW: pure white
		200/220 VAC/VDC	A165L-∆□M-T2-2S	A165L-∆□A-T2-2S	B: black *2
	Non-lighted		A165-∆□M-2S	A165-∆□A-2S	_

^{*1.} Enter the desired shape for the Pushbutton in Δ : J (rectangular), A (square), or T (round). Enter the desired color symbol for the Pushbutton in the \Box .

^{*2.} Black ("B") Pushbuttons are only available for non-lighted models.

Ordering as a SetThe model numbers used to order sets of Units are given in the following tables. One set comprises the Pushbutton, Lamp (lighted models only), Case, and Switch.

Models with PCB Terminals



IP40

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Pushbutton color symbol *1
SPDT		5 VDC	A16L-∆□M-5D-1P	
	LED	12 VAC/VDC	A16L-∆□M-12D-1P	
		24 VAC/VDC	A16L-∆□M-24D-1P	R: red
	Non-lighted		A16-∆□M-1P	Y: yellow PY: pure yellow
		5 VDC	A16L-∆□M-5D-2P	G: green A: blue W: white
DPDT	LED	12 VAC/VDC	A16L-∆□M-12D-2P	B: black *2
DPD1		24 VAC/VDC	A16L-∆□M-24D-2P	
	Non-lighted		A16-∆□M-2P	

Note: Contact your OMRON representative about Selector Switches and Key Selector Switches.

*1. Enter the desired shape for the Pushbutton in Δ : J (rectangular), A (square), or T (round). Enter the desired color symbol for the Pushbutton in the \Box . *2. Black ("B") Pushbuttons are only available for non-lighted models.

IP65

Output	Lighting	Item Operating voltage	Momentary operation (Self-resetting)	Pushbutton color symbol *1	
		5 VDC	A165L-∆□M-5D-1P		
SPDT	LED	12 VAC/VDC	A165L-∆□M-12D-1P		
		24 VAC/VDC	A165L-∆□M-24D-1P R: red Y: yellow		
	Non-lighted		A165-∆□M-1P	Y: yellow PY: pure yellow G: green	
		5 VDC	A165L-∆□M-5D-2P	A: blue W: white	
DPDT	LED	12 VAC/VDC	A165L-∆□M-12D-2P	B: black *2	
וטפט		24 VAC/VDC	A165L-∆□M-24D-2P		
	Non-lighted		A165-∆□M-2P		


Note: Contact your OMRON representative about Selector Switches and Key Selector Switches.

*1. Enter the desired shape for the Pushbutton in Δ : J (rectangular), A (square), or T (round). Enter the desired color symbol for the Pushbutton in the \square .


*2. Black ("B") Pushbuttons are only available for non-lighted models.

Illumination Only and Colored Illumination for Models with LEDs

With illumination only, the color of the lighted surface is the same when the LED is lit and when it is not lit. Example: Red Illumination



With colored illumination, the color of the lighted surface is white when the LED is not lit and the LED emits another color when it is lit. Example: Red Illumination




Ordering: For colored illumination, order the Operation Unit, Case, Lamp, and Socket Unit separately.

Color emitted when lit	Operation Unit	Case	Lamp (LED)		Socket Unit
Red		IP40 • Momentary: A16-C□M	A16-□DSR	5. 2 ADC	Refer to page 14 . Any Switch can be mounted.
Yellow		Alternate: A16-C□A IP65 Momentary: A165-C□M Alternate: A165-C□A Insert one of the following symbols into the box (□). J: Rectangular (2-way guard)	A16-□DSY		
Green			A16-□DSG		
Blue	A: Square T: Round	A: Square (2-way guard) T: Round (projected)	A16-□DA		


8


Ordering Individually Pushbuttons, Lamps, Cases, and Switches (Sockets) can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs.



Socket Units and use IP65 Operation Units with IP65 Socket Units. There is no Legend Plate built into the Operation Unit.








Socket Solder terminals Lighted/non-lighted Note: Socket Unit Sets that combine a Lamp and a Socket Unit are also available. (Refer to page 11.)

Ordering set combinations: Refer to pages 3 to 7.

- Specifications: Refer to page 16.
- Accessories, Replacement, and Tools: Refer to page 15.



Unit Sets..... Sets that combine an Operation Unit and a Case. **Operation Unit**

Appearance		Classification				
			Rectangular (2-way guard)	A16-J□M		
		,	Square (2-way guard)	A16-A□M		
	IP40	operation	Round (projected)	A16-T□M		
	1640		Rectangular (2-way guard)	A16-J□A		
		Alternate operation	Square (2-way guard)	A16-A□A		
			Round (projected)	A16-A□M A16-T□M A16-J□A		
			Rectangular (2-way guard)	A165-J□M		
		•	Square (2-way guard)	A16-J M A16-A M A16-T M A16-J A A16-A A A16-T A A16-T A A165-J M A165-A M A165-T M A165-J A A165-J A		
	Oil-resistant IP65	operation	Round (projected)	A165-T□M		
•	Oll-resistant iros	Momentary operation Square (2-way guard) Round (projected) Rectangular (2-way guard) Square (2-way guard) Square (2-way guard) Round (projected) Momentary operation Momentary operation Round (projected) Rectangular (2-way guard) Square (2-way guard) Square (2-way guard) Round (projected)	A165-J□A			
		Alternate operation	Square (2-way guard)	A165-A□A		
			Round (projected)	A165-T□A		

Insert one of the following symbols into the box (\Box) .

Symbol	Color	Remarks	
R	Red		
Υ	Yellow		
PY	Pure yellow	LED indicator, incandescent lamp, or non-lighted	
Α	Blue	lamp, or nor lighted	
W	White*		
GY	Green	LED only	
G	Green	Incandescent lamp or non-lighted	
В	Black	Non-lighted only	

^{*} Use this pushbutton color if the illumination color of the LED is white or pure white.

Unit Sets Sets that combine a Socket Unit and a Lamp.

Socket Unit Sets with Incandescent Lamps

Appearance		Model		
	Standard loads and	Solder terminals	SPDT A16L-□-1	A16L-□-1
	microloads	Soluei terriiriais	DPDT	A16L-□-1 A16L-□-2

Socket Unit Sets with LED Lamps

Appearance		Model		
		Solder terminals SPD		A16L-∆-□-1
	Standard loads and	Solder terminals	DPDT	A16L-∆-□-2
	microloads	PCB terminals	SPDT A16L-	A16L-∆-□-1P
ր. ը <mark>ն</mark> գր		POB terminals	DPDT	A16L-∆-□-2P

Socket Unit Set with Voltage-reduction Lighting (Soldered Terminals)

Appearance	Classification		Operating voltage	Model
	Standard loads and microloads	SPDT 100/110 VAC/VDC A16L- Δ -T1- 1		A16L- Δ-T1-1
	Standard loads and microloads	DPDT	100/110 VAC/VDC	A16L-∆-T1-2

Note: An LED rated 24 VAC/VDC is built-in.

Screw-less Clamp Socket Unit Sets

Appearance	Classification					Model
				Non-lig	A16-2S	
				No voltage	A16L-∆-□-2S A16L-∆-T1-2S	
	Standard loads and microloads	DPDT	Lighted	Voltage-reduc-	100/110 VAC/VDC	A16L-∆-T1-2S
				Note.	200/220 VAC/VDC	A16L-∆-T2-2S

Note: The 100-V models and 200-V models an LED rated 24 VAC/VDC is built-in.

Insert symbols in Δ and \square .

Δ

Symbol	Color
R	Red
Υ	Yellow
G	Green
W	White
Α	Blue

Symbol	Туре	Operating voltage
5		5 VAC/VDC
12	Incandescent	12 VAC/VDC
24		24 VAC/VDC
5D		5 VDC
12D	LED	12 VAC/VDC
24D		24 VAC/VDC

Note: If the Operation Unit is pure yellow (PY), use white (W) for the Socket Unit Set.

11

Ordering Individually Pushbuttons, Lamps, Cases, and Switches (Sockets) can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and

Pushbuttons LED

Degree of protection	IP40			Oil-resistant IP65			
	Rectangular	Square	Round	Rectangular	Square	Round	
Color						0	
Red	A16L-JR	A16L-AR	A16L-TR	A165L-JR	A165L-AR	A165L-TR	
Yellow	A16L-JY	A16L-AY	A16L-TY	A165L-JY	A165L-AY	A165L-TY	
Pure yellow	A16L-JPY	A16L-APY	A16L-TPY	A165L-JPY	A165L-APY	A165L-TPY	
Green	A16L-JGY	A16L-AGY	A16L-TGY	A165L-JGY	A165L-AGY	A165L-TGY	
White*	A16L-JW	A16L-AW	A16L-TW	A165L-JW	A165L-AW	A165L-TW	
Blue	A16L-JA	A16L-AA	A16L-TA	A165L-JA	A165L-AA	A165L-TA	

^{*} Use this pushbutton color if the illumination color of the LED is white or pure white.

Incandescent Lamps (With the exception of green, the Units are the same as for LEDs.)

Degree of protection	IP40				Oil-resistant IP65			
	Rectangular	Square	Round	Rectangular	Square	Round		
Color			O					
Red	A16L-JR	A16L-AR	A16L-TR	A165L-JR	A165L-AR	A165L-TR		
Yellow	A16L-JY	A16L-AY	A16L-TY	A165L-JY	A165L-AY	A165L-TY		
Pure yellow	A16L-JPY	A16L-APY	A16L-TPY	A165L-JPY	A165L-APY	A165L-TPY		
Green	A16L-JG	A16L-AG	A16L-TG	A165L-JG	A165L-AG	A165L-TG		
White	A16L-JW	A16L-AW	A16L-TW	A165L-JW	A165L-AW	A165L-TW		
Blue	A16L-JA	A16L-AA	A16L-TA	A165L-JA	A165L-AA	A165L-TA		

Non-lighted (Same as Units for incandescent lamps.)

Degree of protection		IP40			Oil-resistant IP65	
	Rectangular	Square	Round	Rectangular	Square	Round
Color						O
Red	A16L-JR	A16L-AR	A16L-TR	A165L-JR	A165L-AR	A165L-TR
Yellow	A16L-JY	A16L-AY	A16L-TY	A165L-JY	A165L-AY	A165L-TY
Pure yellow	A16L-JPY	A16L-APY	A16L-TPY	A165L-JPY	A165L-APY	A165L-TPY
Green	A16L-JG	A16L-AG	A16L-TG	A165L-JG	A165L-AG	A165L-TG
White	A16L-JW	A16L-AW	A16L-TW	A165L-JW	A165L-AW	A165L-TW
Blue	A16L-JA	A16L-AA	A16L-TA	A165L-JA	A165L-AA	A165L-TA
Black	A16L-JB	A16L-AB	A16L-TB	A165L-JB	A165L-AB	A165L-TB

Ordering set combinations: Refer to pages 3 to 7.

- Specifications: Refer to page 16.
- Accessories, Replacement, and Tools: Refer to page 15.

Ordering Individually Pushbuttons, Lamps, Cases, and Switches (Sockets) can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and

Lamps **LED**

Operating voltage	High brightness		
Light color	5 VDC	12 VAC/VDC	24 VAC/VDC
Red	A16-5DSR	A16-12DSR	A16-24DSR
Yellow	A16-5DSY	A16-12DSY	A16-24DSY
Green	A16-5DSG	A16-12DSG	A16-24DSG
White *	A16-5DSW	A16-12DSW	A16-24DSW
Blue	A16-5DA	A16-12DA	A16-24DA
Pure white	A16-5DPW	A16-12DPW	A16-24DPW

Incandescent Lamp

Appearance	Operating voltage	Model
100	5 VAC/VDC	A16-5
	12 VAC/VDC	A16-12
	24 VAC/VDC	A16-24

Cases

Appearance		Classification			
			Rectangular (2-way guard)	A16-CJM	
		Momentary operation	Square (2-way guard)	A16-CAM	
	IP40		Round (projected)	A16-CTM	
	11740		Rectangular (2-way guard)	A16-CJA	
		Alternate operation	Square (2-way guard)	A16-CAA	
			Round (projected)	A16-CTA	
		Momentary operation	Rectangular (2-way guard)	A165-CJM	
			Square (2-way guard)	A165-CAM	
	Oil-resistant IP65		Round (projected)	A165-CTM	
	Oll-resistant IP65		Rectangular (2-way guard)	A165-CJA	
		Alternate operation	Square (2-way guard)	A165-CAA	
			Round (projected)	A165-CTA	

Ordering set combinations: Refer to pages 3 to 7.

- Specifications: Refer to page 16.
- Accessories, Replacement, and Tools: Refer to page 15.

Note: 1. If an LED lamp with normal brightness is needed, select a Lamp used in the A3C.
2. For voltage-reduction lighting use the A16-24D□. Only 24 VAC/VDC LED lamps can be used.
* Use the white LED together with white or pure yellow Pushbuttons.

Switches

Appearance	Cla	ssification		Model
Solder terminal			SPDT	A16-1
			DPDT	A16-2
PCB terminal			SPDT	A16-1P
The state of the s	Lighted/non-lighted (common use)	Standard load/microload (common use)	DPDT	A16-2P
Screw-less Clamp			DPDT	A16-2S

Switches with Reduced-voltage Lighting

Appearance		Classification		Model
Solder terminal	400 V		SPDT	A16-T1-1
	100 V	Standard load/microload	DPDT	A16-T1-2
Screw-less Clamp	100 V	(common use)	DPDT	A16-T1-2S
200 V	200 V		וטפטו	A16-T2-2S

Note: For voltage-reduction use the A16-24D□. Only 24 VAC/VDC LED lamps can be used.

Accessories, Replacements, and Tools Accessories

Name	Appearance	Classification	Model	Remarks	
Switch Guards		For rectangular models		Cannot be used with the Dust Cover.	
Switch Guards	Switch Guards	For square and round models	A16ZA-5050	Carnot be used with the Bust Cover.	
		For rectangular models	A16ZJ-5060		
Dust Covers		For square models	A16ZA-5060	Cannot be used with the Switch Guard. Can be operated with the Dust Cover attached.	
		For round models	A16ZT-5060		
		For rectangular models		Used for covering the panel cutouts for future panel	
Panel Plugs		For square models	A16ZA-3003	expansion. Protective structure: IP40	
	421	For round models	A16ZT-3003	Color: Black	

Replacements

Name	Appearance		Classificati	on	Model	Remarks
		Rectangu- lar	Oil-resistant IP65	Milky	A16ZJ-5204	A single Legend Plate (Milky white) is included with a standard
Legend Plates		Square	Oil-resistant IP65	Milky	A16ZA-5204	model. • The milky Legend Plate can be
		Round	Oil-resistant IP65	Milky	A16ZT-5204	used with the IP40 and oil-resistant IP65.
			1	White	A16Z□-5001W	
	Rectangular			Red	A16Z□-5001R	Insert one of the following letters
	^	LED lamp/incandescent lamp/nonlighted		Yellow	A16Z□-5001Y	into the box (\Box) .
Color Caps (for				Pure yellow	A16Z□-5001PY	J: RectangularA: Square
IP40)				Blue	A16Z□-5001A	T: Round
		LED lamp		Green	A16Z□-5001GY	The Color Cap is usually supplied.
	Square	Incandescent lamp/non-lighted		Green	A16Z□-5001G	Replace the Cap if the color is to
		Non-lighted		Black	A16Z□-5011B	be changed.
			White	A16Z□-5101W	When using an LED indicator, be sure to use a Color Cap that	
					A16Z□-5101R	matches the luminescent color of
	Round	lamp/nonlig	ncandescent	Yellow	A16Z□-5101Y	the LED.
Color Caps (for oil-resistant IP65)	riodrid	lamp/nomig	jiileu	Pure yellow	A16Z□-5101PY	The materials used for the IP40
				Blue	A16Z□-5101A	 and oil-resistant IP65 are different so be sure to use a Color Cap that
		LED lamp	LED lamp		A16Z□-5101GY	matches the specifications of the
	6	Incandescent la	amp/non-lighted	Green	A16Z□-5101G	Switch.
		Non-lighted		Black	A16Z□-5111B	

Tools

				A	oplicable type	es		
Name	Appearance	Model	Pushbut- ton Switch	Knob-type Selector Switch	Key-type Selector Switch	Emergen- cy Stop Switch	Indicator	Remarks
Operation Unit Extractor		A3PJ-5080	•		_	_	•	Convenient for extracting Pushbutton Switches
Screw Fitting		A16Z-3004	•	•	•	•	•	Convenient for ganged installation.
Socket Unit Lamp Extractor		A16Z-5080	•	•	•	•	•	Convenient for extracting the Switch and Lamps.

OMRON 15

Specifications

Approved Standard Ratings

UL, cUL (File No. E41515)

5 A at 125 VAC, 3 A at 250 VAC (general use) 3 A at 30 VDC (resistive)

Note: Certification has been obtained for the Socket Unit. For detailed information on individual products that have received certification, consult your supplier.

TÜV (EN60947-5-1) (Low Voltage Directive)

3 A at 250 VAC 3 A at 30 VDC

CCC (GB14048.5)

5 A at 125 VAC 3 A at 250 VAC 3 A at 30 VDC

Ratings

Contacts

Rated voltage	Resistive load
125 VAC	5 A
250 VAC	3 A
30 VDC	3 A

Minimum applicable load: 1 mA at 5 VDC

Rated values are obtained from tests conducted under the following conditions.

- 1. Load: Resistive load
- 2. Mounting conditions: No vibration and no shock
- 3. Temperature: 20 ±2°C
- 4. Operating frequency: 20 operations/min

Contact Form

Name	Contact
DPDT	COM
	NO

Characteristics Socket Unit

Item	Туре	Pushbutton Switch	
Allowable operating	Mechanical	Momentary operation: 120 operations/minute max. Alternate operation: 60 operations/minute max. *1	
frequency Electrical		20 operations/minute max. *1	
Insulation r	esistance	100 MΩ min. (at 500 VDC)	
Between terminals of same polarity		1,000 VAC, 50/60 Hz for 1 minute	
Dielectric	Between terminals of different polarity	2,000 VAC, 50/60 Hz for 1 minute	
strength	Between each ter- minal and ground	2,000 VAC, 50/60 Hz for 1 minute	
	Between lamp ter- minals	1,000 VAC, 50/60 Hz for 1 minute *2	
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)	
Shock	Destruction	500 m/s ²	
resistance	Malfunction	150 m/s ² max. (malfunction within 1 ms)	
Durability	Mechanical	Momentary operation: 2,000,000 operations min. Alternate operation: 200,000 operations min. *1	
_	Electrical	100,000 operations min. *1	
Electric sho	ock protection class	Class II	
PTI (trackin	g characteristic)	175	
Degree of c	ontamination	3 (IEC947-5-1)	
Weight		Approx. 10 g (in the case of a lighted DPDT switch with solder terminals)	
Degree of p	rotection	IP40: A16, Oil-resistant IP65: A165 *3	
Ambient op	erating temperature	-10°C to 55°C (with no icing or condensation)	
Ambient op	erating humidity	35% to 85%RH	
Ambient ste	orage temperature	−25°C to 65°C (with no icing or condensation)	

- *1. Set and reset constitute one operation.
 *2. With LED and incandescent lamp not mounted.
- *3. Degree of protection from the front of the panel.

Super-bright LED

Rated voltage	Rated current	Operating voltage	Internal limiting resistor
5 VDC		5 VDC ±5%	Red, yellow, white: 300 Ω Green, blue, pure white: 160 Ω
12 VAC/VDC	8 mA	12 VAC/VDC ±5%	Red, yellow, white: 1 k Ω Green, blue, pure white: 910 Ω
24 VAC/VDC		24 VAC/VDC ±5%	2.4 kΩ

Incandescent Lamp

Rated voltage	Rated current	Operating voltage
6 VAC/VDC	60 mA	5 VAC/VDC
14 VAC/VDC	40 mA	12 VAC/VDC
28 VAC/VDC	24 mA	24 VAC/VDC

Voltage-reduction Unit (LED Lamp)

_	•	
Rated voltage	Operating voltage	Applicable lamp
110 VAC/VDC	100/110 VAC/VDC (90 to 121 V)	A16-24DS□
220 VAC/VDC	200/220 VAC/VDC (180 to 242 V)	LED Lamp

Screw-less Clamp

Item		Screw-Less Clamp			
Recommended wire size		0.5 mm² twisted wire or 0.8 mm-dia. solid wire			
	Twisted wire	0.3 mm ²	0.5 mm ²	0.75 mm ²	1.25 mm ²
Usable wires and tensile strength	Solid wire	0.5 mm dia.	0.8 mm dia.	1.0 mm dia.	_
onongai	Tensile strength	10 N	20 N	30 N	40 N
Length of exposed wire		10 ±1mm			
Compliant standards		JIS C 2811 Terminal Blocks for Industrial Use			


Operating Characteristics

4.91 N
4.91 N
nm

Alternate operation models only.

Nomenclature

Model Structure




OMRON 1


(Unit: mm)


Rectangular

A16□-J

Solder terminals (tab terminals #110)











• See page 21 for panel cutouts




Square A16□-A


Solder terminals (tab terminals #110)








• See page 21 for panel cutouts




Round A16□-T


Solder terminals (tab terminals #110)












Dimensions • The Dimension shows 2-switch outputs. • The lamp terminal is also provided with non-lighted models. • A rectangular model is listed as an example. (Unit: mm)


Rectangular A16□-J□-□P

PCB terminals









• See page 21 for panel cutouts


Rectangular

A16□-J□-T1


Voltage-reduction lighting, solder terminals (tab terminals #110)








Panel Cutouts




Rectangular A16□-J□-2S, T1-2S, T2-2S **Screw-less Clamp**






Panel Cutouts




Lamps **LED** A16-5D\(\sigma\)-12D\(\sigma\)-24D\(\sigma\)

OMRON



Incandescent Lamp A16-5/-12/-24



* The voltage display surface is the same color as the illumination color. The opposite surface is light gray. (For pure white, the entire surface is light gray.)


19

Dimensions (Unit: mm)


Accessories, Tools, and Components







Legend Plates A16ZJ-520□




A16ZA-520 12.9 -

A16ZT-520□ --12.9 dia.--0.6

Screw Fitting







Note: 1. The panel is 0.6 mm thick.
2. The panel is made of the materials listed in the following table.


Color	Degree of protection	Materials	
Millar	IP40	- Polyalylate resin	
Milky	IP65		
Transparent	IP40	Polycarbonate resin	
папъраген	IP65	Polyalylate resin	


Panel Plugs (Black Resin)

Select the Plug that fits the panel design and mount from the front of the Panel. Panel cutouts are the same as those for Switches. Protective structure: IP40

Color: Black

Rectangular	Square	Round
A16ZJ-3003 ∠	A16ZA-3003	A16ZT-3003
24	18	18 dia.












OMRON

Dimensions (Unit: mm)

Panel Cutouts

Solder Terminals and Screw-less Clamp Connectors




Note: Make sure the thickness of the mounting panel is between 0.5 and 3.2 mm. If, however, a Switch Guard or Dust Cover is used, the thickness of the mounting panel must be between 0.5 and 2 mm.

- If the panel is to be finished with coating, etc., make sure that the panel meets the specified dimensions after coating.

 • Figures in parentheses are for Screw-less Clamp Connectors.

PCB Terminals




Note: Ensure that the variation in the distance between the centers of neighboring mounting holes is less than ±0.1 mm.

- Make sure the thickness of the mounting panel is between 0.5 and 3.2 mm. If, however, a Switch Guard or Dust Cover is used, the thickness of the mounting panel must be between 0.5 and 2 mm.
- If the panel is to be finished with coating, etc., make sure that the panel meets the specified dimensions after coating.


Terminal Arrangement

Models without Reduced-voltage Lighting (Non-lighted Pushbutton Switches are also provided with lamp terminals.) **Solder Terminals**



Dimensions (Unit: mm)

PCB Terminals (Lamp terminals are also present on non-lighted models.)



Terminal Arrangement


Voltage-reduction Lighting (Lamp terminals are also present on non-lighted models.)

Solder Terminals

(Bottom view) Side with direction arrow

• The voltage-reduction circuit is built in.

Screw-Less Clamps




• Voltage-reduction lighting models with Screw-Less Clamps (A16L-□T1-2S, A16L-□T2-2S) incorporate voltage-reduction circuits.

Dimensions (Unit: mm)

Accessory Dimensions Mounted Dimensions with Switch Guard Installed

Square Rectangular A16ZA-5050 A16ZJ-5050 Torsion spring 23.5 23.5 10.5 10.5 Guard (transparent) Panel Cutout (Top View) Panel Cutout (Top View) 16^{+0.2} dia. - 24.5 min. 16^{+0.2} dia. 19.6 - 27 Note: This example is for when X is 4.5 Note: This example is for when X is 28 min. If X is not required, the Switches can be mounted with a minimum If X is not required, the Switches can be mounted with vertical installation pitch of 24 mm a minimum vertical installation pitch of 24 mm min. If PCB terminals are used, provide X must be 24 mm or larger.



Safety Precautions

Refer to Safety Precautions for All Pushbutton Switches.

⚠ WARNING

Do not apply a voltage between the incandescent lamp and the terminal that is greater than the rated voltage. If the incandescent lamp is broken, the operating part may pop out.



Always turn OFF the power and wait for 10 minutes before replacing the incandescent lamp. If the lamp is replaced immediately after the power is turned OFF, the remaining heat may cause burns.



Precautions for Correct Use

Mounting

- Always make sure that the power is turned OFF before mounting, removing, or wiring the Switch, or performing maintenance.
- Do not tighten the mounting nut more than necessary using tools such as pointed-nose pliers. Doing so will damage the mounting nut

The tightening torque is 0.29 to 0.49 N·m.

Wiring

- Solder terminals and quick-connect terminals (#110) are commonly used for terminals
- Be sure to use electrical wires that are a size appropriate for the applied voltage and carry current (conductor size is 0.5 to 0.75 mm²). Perform soldering according to the conditions provided below. If the soldering is not properly performed, the lead wires will become detached, resulting in short-circuits.
- 1. Hand soldering: 350°C, within 3 s
- Dip soldering: 350°C, within 3 s
 Wait for one minute after soldering before exerting any external force on the solder.
- Use non-corrosive resin fluid as the flux.
- Make sure that the electric cord is wired so that it does not touch the Unit. If the electric cord touches the Unit, then electric wires with a heat resistance of 100°C min. must be used.
- After wiring the Switch, maintain an appropriate clearance and creepage distance.


Operating Environment

- This Switch is intended for indoor use only. Using the Switch outdoors will cause the Switch to fail. If IP40 models are used in locations subject to dust, metallic particles, or oil, be careful that none of these penetrates the Switch.
- The IP65 model is designed with a degree of protection so that it
 will not sustain damage if it is subjected to water from any direction
 to the front of the panel.
- Do not use the Switch submersed in oil or water, or in locations continuously subject to splashes of oil or water. Doing so may result in oil of water entering the Switch.

Using the Microload

- Insert a contact protection circuit, if necessary, to prevent the reduction of life expectancy due to extreme wear on the contacts caused by loads where inrush current occurs when the contact is opened and closed.
- The A16 allows both a standard load (125 V at 5A, 250 V at 3 A) and a microload. If a standard load is applied, however, the microload area cannot be used. If the microload area is used with a standard load, the contact surface will become rough, and the opening and closing of the contact for a microload may become unreliable.
- The minimum applicable load is the N-level reference value. This
 value indicates the malfunction reference level for the reliability
 level of 60% (λ 60) (conforming to JIS C5003).

The equation, λ 60 = 0.5 × 10⁻⁴/operations indicates that the estimated malfunction rate is less than 1/2,000,000 operations with a reliability level of 60%.



LED

 The LED current-limiting resistor is built-in, so external resistance is not required.


Rated voltage	Internal limiting resistor
5 VDC	Red, yellow, white: 300 Ω Green, blue, pure white: 160 Ω
12 VAC/VDC	Red, yellow, white: 1 k Ω Green, blue, pure white: 910 Ω
24 VAC/VDC	2.4 kΩ


Others

- The oil-resistant IP65 uses NBR rubber and is resistant to general cutting oil and cooling oil. Some particular oils cannot be used with the oil-resistant IP65, however, so contact your OMRON representative for details.
- The durability of the Switch depends in the switching conditions. Always test the Switch under actual application conditions to confirm applicability and use the Switch only for the number of switching operations that will not affect performance. Continuing to use the Switch with degraded performance will eventually result insulation faults between circuits, burning of the Switch, or other failures.
- If the panel is to be finished with coating, etc., make sure that the panel meets the specified dimensions after the coating.
- Do not subject the Switch to extreme shock or vibration. Doing so will cause malfunctions and damage to the Switch.
- Do not let sharp objects come into contact with the Switches that are made of resin. Doing so will damage the Switches, causing scratches on the outside of the operating parts, and malfunction.
 When handling the Switches, do not throw or drop them.

 Rubber is used inside IP65 models. Do not allow the rubber to become scratched or foreign matter to become attached to the rubber.

Scratches and foreign matter will degrade the waterproofing, and the Switch may fail operate correctly.





Screw-less Clamp Wiring Procedure

Connecting Wires

- 1. Strip the wires for 10 mm (allowable range: 10± 1 mm).
- 2. If braided wire is used, twist the wire to straighten it out.
- Insert the wire into the insertion hole while pressing the release button at the side of the hole. (Using a precision screwdriver is recommended.)
- 4. Let go of the release button to lock the wire into place.
- After locking, pull on the wire gently to confirm that it is securely locked.


Removing Wires

Remove wires by pulling them while pressing the release button.

Note: When reusing wires that have already been locked one, cut off the end of the wire and strip the wire again before using.

Precautions

- 1. The mounting panel thickness must be 0.5 to 3.2 mm.
- 2. The mounting ring must be tightened to a torque 0.29 to 0.49 N·m.
- 3. The procedure for making the mounting hole for the screw-less clamp connector is described on page 21. A mounting dimension of at least 33 mm is required, however, because the Switch is removed with the screw-less clamp connector mounted to the panel. If Switches are mounted side-by-side separated by less than the specified distance, it may not be possible to remove the Switch.
- Be sure to mount the Case to the Switch with the correct orientation. Mount with the dimple on the Case facing in the same direction as the side of the Switch with the direction arrow or the word TOP.




- 5. Bend the end of the wire if braided wire is used with the screwless clamp connector.
- When wiring, insert the wire until it comes into contact with something. After wiring is completed, pull on the wires to confirm that they are connected securely.
- After wiring, ensure that continuous pressure is not applied to the terminals.
- 8. Refer to internal connection diagrams and confirm the terminal numbers before wiring.

Panel Mounting

After mounting the Pushbutton Unit (i.e., the Pushbutton and the Case) to the panel, snap in the Switch Unit (i.e., the Switch and the Lamp) from the back of the panel.


Mounting to the Panel

- Insert the Pushbutton Unit into the front of the panel, and fix the lock ring and mounting nut from the terminal side.
- Make sure that the lock ring is aligned with the thread of the Case and the edge of the lock ring is touching the panel.
- Tighten the mounting nuts to a torque of 0.29 to 0.49 N·m.



Mounting the Switch Unit

- Snap on the Switch Unit to the Pushbutton Unit.
- Make sure that the Switch Unit has the correct orientation when snapping it onto the Case. Align the dimple on the Case with the groove between the case guards on the NC terminal side of the Switch Unit in the way shown below, and push the Switch Unit into the Case until it clicks into place. Confirm that the Switch Unit is securely in place before using.



Removing the Switch Unit

 Grip the part between the Switch holder of the Case and the Switch Unit using the A16Z-5080 Extractor, and pull to remove the Switch Unit.



Note: Refer to page 21 for PCB terminals.


Engraving

Engraving the Legend Plate


- The characters must not be engraved deeper than 0.4 mm.
- Apply an alcohol-based paint coating, such as melamine, phthalate, or acrylic resin paint coating.

Mounting and Replacing the Pushbutton Removing and Mounting the Pushbutton

 Remove the Pushbutton as shown in the following diagram. If the Pushbutton cannot be removed by hand, use the A3PJ-5080 Extractor.




(2) When mounting the Operation Unit to the Case, press the entire surface of the Operation Unit to surface A of the Case as shown in the following diagram.



Removing the Lamp


(1) Removing from the Pushbutton End



(2) Removing from the Switch End The Lamp can be removed by hand once the Switch is removed using the A16Z-5080 Extractor.

Installing the Lamp


 When mounting the Lamp, make sure it is facing the direction shown in the following diagram. Insert the Lamp while matching the protruding part of the Lamp and the small guides on the outer surface of the Case.



 The Lamp can be mounted from the Pushbutton end by using the A16Z-5080 Extractor.

The lamp can be mounted by following the opposite procedure for removing the Lamp.


Mounting the A16Z Dust Cover



- 1. Separate the Dust Cover into 2 parts: cover A and cover B.
- 2. Insert the Case (Pushbutton Unit) into cover A.
- 3. Mount these parts together onto the panel.
- From the back of the panel, mount the lock ring and secure with the mounting nut.
- Insert cover B into cover A. Ensure that the entire perimeter of cover B is securely attached to cover A by pressing in different directions.
- 6. Mount the Switch Unit to the Case.

Note: Recommended panel thickness: 0.5 to 2 mm.

Mounting the A16Z Switch Guard



- 1. Insert the Case (Pushbutton Unit) into the Switch Guard.
- 2. Mount these parts together onto the panel.
- From the back of the panel, mount the lock ring and secure with the mounting nut.
- 4. Attach the Switch Unit to the Case.

Note: Recommended panel thickness: 0.5 to 2 mm.

Read and Understand This Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranty and Limitations of Liability

WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

Application Considerations

SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
- Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

PROGRAMMABLE PRODUCTS

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

Disclaimers

CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the products may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased products.

DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

ERRORS AND OMISSIONS

The information in this document has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.

2009.12

In the interest of product improvement, specifications are subject to change without notice.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

A16L-TRA-5-1 A16L-JRM-24D-1 A16L-JRM-24D-2 A16L-AGM-5-2 A16L-AGA-5-1 A16L-AGM-5-1 A16L-AGA-5-2 A165L-TGM-24D-1 A165L-TRM-24D-2 A165L-TRM-24D-1 A16L-JGM-5-2 A16L-JGM-5-1 A165L-TGM-24D-2 A165L-TGA-12-1 A165L-AGA-12-1 A165L-TGA-12-2 A165L-AGA-12-2 A165L-JGA-12-2 A165L-JGA-12-1 A165L-ARA-24-2 A16-JRM-1 A165L-JRA-24-2 A165L-JRA-24D-1 A165L-TRA-24-2 A165L-JRA-24-1 A165L-JGA-24D-1 A165L-ARA-24-1 A165L-JGA-24D-2 A165L-JRA-24D-2 A165L-TRA-24-1 A165L-ARM-24D-2 A165L-AGM-24D-1 A165L-AGM-24D-2 A165L-ARM-24D-1 A16L-TGA-24-1 A16L-TGA-24-2 A16L-TGA-12-1 A16L-JGA-24-2 A16L-AGA-12-2 A16L-JGA-12-1 A16L-JGA-24-1 A16L-TGA-12-2 A16L-TRM-12D-1 A16L-AGA-12-1 A16L-JGA-12-2 A16L-TRM-12D-2 A16L-TGM-12D-1 A16L-TGM-12D-2 A165-JBA-2 A165-JBA-1 A165L-AGA-5-2 A16L-JRM-5-2 A165L-AGA-5-1 A16L-JRM-5-1 A16L-ARA-12D-2 A16L-AGM-24D-2 A16L-ARA-12D-1 A16L-ARM-24D-2 A16L-AGA-12D-2 A16L-AGA-12D-1 A16L-ARM-24D-1 A16L-AGM-24D-1 A165L-ARA-12D-1 A165L-ARA-12D-2 A165L-AGA-12D-1 A165L-AGA-12D-2 A165L-JGA-12D-1 A165L-JGM-24D-1 A165L-JGM-24D-2 A165L-JRM-24D-2 A165L-JRM-24D-1 A165L-AGA-5D-2 A165L-TGA-5D-2 A165L-AGA-5D-1 A165L-TGA-5D-1 A165L-JGA-5D-1 A165L-JGA-5D-2 A165L-TGM-5-1 A165L-TGM-5-2 A16-TBM-2 A16-TBM-1 A165L-AGM-24-2 A165L-TGM-24-2 A165L-AGM-24-1 A165L-TGM-24-1 A165L-JGM-24-2 A165L-JGM-24-1 A165L-AGM-5D-1 A165L-TGM-5D-2 A165L-TGM-5D-1 A165L-JGM-5D-1 A165L-JGM-5D-2 A165L-AGM-5D-2 A16L-JRA-5-1 A16L-JRA-5-2 A16L-JRM-12D-1 A16L-JGM-12D-1 A16L-JGM-12D-2 A16L-JRM-12D-2 A165L-TGA-5-1