
PRODUCT DATASHEET CP17416_YASMEEN-70-WW-C

YASMEEN-70-WW-C

~60° wide beam. Assembly with holder C compatible with LEDiL HEKLA. Black version.

SPECIFICATION:



MATERIALS:

ComponentTypeMaterialColourFinishYASMEEN-70-WWSingle lensPMMAclearYASMEEN-70-HLD-CHolder CPCblack

ORDERING INFORMATION:

 Component
 Qty in box
 MOQ
 MPQ
 Box weight (kg)


 CP17416_YASMEEN-70-WW-C
 Single lens
 105
 105
 15
 9.8

 » Box size: 476 x 273 x 305 mm
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8
 9.8

Published: 21/10/2020




PRODUCT DATASHEET CP17416_YASMEEN-70-WW-C




See also our general installation guide: www.ledil.com/installation_guide




















PRODUCT DATASHEET CP17416_YASMEEN-70-WW-C

OPTICAL RESULTS (MEASURED):



Published: 21/10/2020


PRODUCT DATASHEET CP17416_YASMEEN-70-WW-C

OPTICAL RESULTS (MEASURED):

PHILIPS

LED Fortimo SLM L09 CoB

FWHM / FWTM 54.0° / 74.0°
Efficiency 81 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:




SAMSUNG

F17437_HEKLA-G2-H

LED LC016D / LC019D / LC026D / LC033D

FWHM / FWTM 52.0° / 77.0°
Efficiency 80 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:



SAMSUNG

F17438_HEKLA-G2-I


 LED
 LC030C/040C G2

 FWHM / FWTM
 54.0° / 75.0°

 Efficiency
 81 %

 Peak intensity
 1 cd/lm

LEDs/each optic 1 Light colour White Required components: F17438_HEKLA-G2-I




SEOUL SEMICONDUCTOR


LED MJT COB LES 14.5

FWHM / FWTM 52.0° / 77.0°
Efficiency 80 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:

F17438_HEKLA-G2-I







OPTICAL RESULTS (SIMULATED):

CITIZEN

LED CLU712/713


FWHM / FWTM 56.0° / 76.0°

Efficiency 81 %

Peak intensity 1 cd/lm

LEDs/each optic 1
Light colour White

Required components: F17438_HEKLA-G2-I



CREE - LED

LED CMU10xx


FWHM / FWTM 56.0° / 76.0°

Efficiency 81 %

Peak intensity 1 cd/lm LEDs/each optic 1

Light colour White

Required components: F17435_HEKLA-G2-C



CREE - LED

LED CXA/B 13xx

FWHM / FWTM 58.0° / 76.0°


Efficiency 82 %

Peak intensity 1 cd/lm

LEDs/each optic 1
Light colour White

Required components:

F17439_HEKLA-G2-J



CREE & LED

LED CXA/B 15xx

FWHM / FWTM 56.0° / 76.0°


Efficiency 80 %
Peak intensity 1 cd/lm

Peak intensity 1 cd/lr LEDs/each optic 1

Light colour White

Required components:

F17436_HEKLA-G2-D



OPTICAL RESULTS (SIMULATED):

CREE - LED

LED CXA/B 1830
FWHM / FWTM 54.0° / 78.0°
Efficiency 79 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White


Required components: Bender Wirth: 637b Hekla

ELUMINUS

LED CxM-14 (19x19)

Assembly NULL
FWHM / FWTM 54.0° / 78.0°
Efficiency 78 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:

equired components: F17438_HEKLA-G2-I



WNICHIA

LED NVCWJ024Z-V1MT: COB J-Type Tunable White

FWHM / FWTM 58.0° / 80.0°


Efficiency 81 %

Peak intensity 0.9 cd/lm

LEDs/each optic 1

Light colour White

Required components: C16142_HEKLA-SOCKET-K Bender Wirth: 498 Typ L8 HV




OSRAM

LED PrevaLED Core G7 LES15 CoB

Assembly NULL
FWHM / FWTM 52.0° / 78.0°
Efficiency 78 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17438_HEKLA-G2-I






OPTICAL RESULTS (SIMULATED):

SAMSUNG

LC003D / LC006D / LC009D / LC013D

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 56.0° / 76.0° Efficiency 80 % Peak intensity 1 cd/lm LEDs/each optic Light colour White


Required components: F17435_HEKLA-G2-C



TRIDONIC

LED SLE G7 LES13 FWHM / FWTM 54.0° / 77.0° Efficiency 80 % Peak intensity 1 cd/lm LEDs/each optic 1 White Light colour Required components:

F17438_HEKLA-G2-I



Published: 21/10/2020



PRODUCT DATASHEET CP17416_YASMEEN-70-WW-C

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

13/13

www.ledil.com/ where_to_buy