

# Industrial Gland Kits

## CW LSOH Brass Gland Kit LSF - CW Series



### Application

- > Indoor/outdoor type for SWA cable

### Features & Benefits


- > Brass indoor and outdoor cable gland & accessories
- > For circular, galvanized-steel single-wire-armour plastic or rubber sheathed cables
- > Outer seal grips sheath of cable
- > For use in most climatic conditions, weatherproof and waterproof
- > Three part armour lock with separate armour locking ring, ideal for checking electrical continuity
- > Kit comprises:
  - CW Gland
  - Brass earth tag
  - Brass locknut
  - LSF shroud
- > 2 per kit up to and including 25mm size

### Technical Data

- > EN 50262
- > BS6121:Pt 1:1989
- > Gland rated to IP66 with use of suitable sealing washer or thread sealant at gland interface
- > Service temperature range -20°C to +90°C
- > CuZn39Pb3 extruded brass alloy used for guaranteed strength and performance



# CW LSOH Brass Gland Kit LSF - CW Series



## Gland Details

Cable Dimensions mm				Kit Reference			Gland Dimensions mm				
Under Armour Diameter A  Max	Overall Diameter B		Armour Wire Diameter  C	Size	Design Number	Items Per Pack	Entry Thread		Approx. Length From Shoulder  F	Hexagon Size	
	Min	Max					Size	Length		Across Flats G	Across Corners H
							D	E			
8.6	8.0	13.2	0.9	20SS	LSF20SSCW	2	M20 × 1.5	10	44	23.4	26.7
11.6	8.0	15.8	0.9	20S	LSF20SCW	2	M20 × 1.5	10	46	25.7	29.2
13.9	11.7	20.8	0.9 / 1.25	20	LSF20CW	2	M20 × 1.5	10	46	30.5	34.0
19.9	17.0	27.2	1.25 / 1.6	25	LSF25CW	2	M25 × 1.5	10	51	37.6	42.2
26.2	23.5	33.5	1.6 / 2.0	32	LSF32CW	1	M32 × 1.5	10	56	47.3	53.6
32.1	29.0	39.9	1.6 / 2.0	40	LSF40CW	1	M40 × 1.5	15	59	56.4	61.5
38.1	38.0	46.2	2.0 / 2.5	50S	LSF50SCW	1	M50 × 1.5	15	64	65.5	72.1
44.0	39.5	52.6	2.0 / 2.5	50	LSF50CW	1	M50 × 1.5	15	64	70.1	77.2
55.9	51.3	65.3	2.5	63	LSF63CW	1	M63 × 1.5	15	67	80.0	87.4
67.9	62.5	78.0	2.5	75	LSF75CW	1	M75 × 1.5	15	76	98.8	109.2
74.0	68.0	88.0	3.15	85	LSF85CW	1	M85 × 2	20	110	115.0	126.0