

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Flux-Off

Revision date: 09.10.2019

Product code: 107

Page 2 of 8

Hazard statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H335	May cause respiratory irritation.
H319	Causes serious eye irritation.
H411	Toxic to aquatic life with long lasting effects.

Precautionary statements

P211	Do not spray on an open flame or other ignition source.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P273	Avoid release to the environment.
P271	Use only outdoors or in a well-ventilated area.
P251	Do not pierce or burn, even after use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Special labelling of certain mixtures

EUH066	Repeated exposure may cause skin dryness or cracking.
--------	---

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hazardous components

CAS No	Chemical name	Quantity
	EC No	
	Index No	
	REACH No	
	GHS Classification	
	Hydrocarbons, C9, aromatics	20-40%
	918-668-5	01-2119455851-35
	Flam. Liq. 3, STOT SE 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H226 H335 H336 H304 H411	
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol	30-35%
	200-661-7	603-117-00-0
	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336	
123-86-4	n-butyl acetate	15-20%
	204-658-1	607-025-00-1
	Flam. Liq. 3, STOT SE 3; H226 H336 EUH066	
109-87-5	Dimethoxymethane	5-10%
	203-714-2	01-2119664781-31
	Flam. Liq. 2, Eye Irrit. 2; H225 H319	
107-98-2	1-Methoxy-2-propanol	5-10 %
	203-539-1	01-2119457435-35
	Flam. Liq. 3, STOT SE 3; H226 H336	
124-38-9	Carbondioxide	5-10%
	204-696-9	
	Compressed gas; H280	

Full text of H and EUH statements: see section 16.

SECTION 4: First aid measures

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Flux-Off

Revision date: 09.10.2019

Product code: 107

Page 3 of 8

4.1. Description of first aid measures**After inhalation**

Provide fresh air. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

After contact with eyes

If product gets into the eye, keep eyelid open and rinse immediately with large quantities of water, for at least 5 minutes. Subsequently consult an ophthalmologist.

After ingestion

If swallowed, immediately drink: Water.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**

Carbon dioxide (CO₂). Foam. Extinguishing powder.

Unsuitable extinguishing media

Water with tenside additive. Water.

5.2. Special hazards arising from the substance or mixture

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Suppress gases/vapours/mists with water spray jet. Contaminated fire-fighting water must be collected separately. Do not allow to enter into surface water or drains.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition. Provide adequate ventilation. Wear a self-contained breathing apparatus and chemical protective clothing.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Explosion hazard.

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking.

7.2. Conditions for safe storage, including any incompatibilities

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Flux-Off

Revision date: 09.10.2019

Product code: 107

Page 4 of 8

Requirements for storage rooms and vessels

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition - No smoking.

Hints on joint storage

Do not store together with: Material, rich in oxygen, oxidizing.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
107-98-2	1-Methoxypropan-2-ol	100	375		TWA (8 h)	WEL
		150	560		STEL (15 min)	WEL
123-86-4	Butyl acetate	150	724		TWA (8 h)	WEL
		200	966		STEL (15 min)	WEL
124-38-9	Carbon dioxide	5000	9150		TWA (8 h)	WEL
		15000	27400		STEL (15 min)	WEL
109-87-5	Dimethoxymethane	1000	3160		TWA (8 h)	WEL
		1250	3950		STEL (15 min)	WEL
67-63-0	Propan-2-ol	400	999		TWA (8 h)	WEL
		500	1250		STEL (15 min)	WEL

8.2. Exposure controls



Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Protect skin by using skin protective cream. After work, wash hands and face. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: NBR (Nitrile rubber) For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. NBR (Nitrile rubber)

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Flux-Off

Revision date: 09.10.2019

Product code: 107

Page 5 of 8

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state:	Aerosol
Colour:	colourless
Odour:	characteristic

Changes in the physical state

Initial boiling point and boiling range:	82,4 °C
Flash point:	<0 °C
Lower explosion limits:	1,2 vol. %
Upper explosion limits:	12 vol. %
Ignition temperature:	270 °C
Vapour pressure: (at 20 °C)	40 hPa
Density (at 20 °C):	0,84 g/cm ³
Solvent content:	95%

SECTION 10: Stability and reactivity**10.1. Reactivity**

No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Irritation and corrosivity**

Irritating to eyes. Following inhalation: Lung irritation. Coughing. shortage of breath. After skin contact: irritant.

SECTION 12: Ecological information**12.1. Toxicity**

Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Advice on disposal**

Do not allow to enter into surface water or drains. Dispose of waste according to applicable legislation.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Flux-Off

Revision date: 09.10.2019

Product code: 107

Page 6 of 8

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing hazardous substances; hazardous waste

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information**Land transport (ADR/RID)**

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 625
Limited quantity: 1 L
Transport category: 2
Tunnel restriction code: D

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Flux-Off

Revision date: 09.10.2019

Product code: 107

Page 7 of 8

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)
E0**Air transport (ICAO-TI/IATA-DGR)**

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS, flammable
14.3. Transport hazard class(es): 2.1
Hazard label: 2.1



Special Provisions: A145 A167
Limited quantity Passenger: 30 kg G
IATA-packing instructions - Passenger: 203
IATA-max. quantity - Passenger: 75 kg
IATA-packing instructions - Cargo: 203
IATA-max. quantity - Cargo: 150 kg

Other applicable information (air transport)
E0
: Y203**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: yes



Danger releasing substance: Solvent Naphta Light

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

2004/42/EC (VOC): 6,45 % (54,18 g/l)

National regulatory information

Water contaminating class (D): 2 - clearly water contaminating

SECTION 16: Other information**Relevant H and EUH statements (number and full text)**

H222 Extremely flammable aerosol.
H225 Highly flammable liquid and vapour.
H226 Flammable liquid and vapour.
H229 Pressurised container: May burst if heated.
H280 Contains gas under pressure; may explode if heated.
H304 May be fatal if swallowed and enters airways.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

Flux-Off

Revision date: 09.10.2019

Product code: 107

Page 8 of 8

H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.
EUH066	Repeated exposure may cause skin dryness or cracking.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)