

## Preliminary datasheet

### EasyDUAL module with CoolSiC™ Trench MOSFET and PressFIT / NTC

#### Features

- Electrical features
  - $V_{DSS} = 1200\text{ V}$
  - $I_{DN} = 100\text{ A} / I_{DRM} = 200\text{ A}$
  - Low inductive design
  - Low switching losses
- Mechanical features
  - PressFIT contact technology
  - Integrated NTC temperature sensor
  - Rugged mounting due to integrated mounting clamps



Typical appearance


#### Potential applications

- High-frequency switching application
- DC/DC converter
- UPS systems
- DC charger for EV

#### Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

#### Description



## Table of contents

	<b>Description</b> .....	1
	<b>Features</b> .....	1
	<b>Potential applications</b> .....	1
	<b>Product validation</b> .....	1
	<b>Table of contents</b> .....	2
<b>1</b>	<b>Package</b> .....	3
<b>2</b>	<b>MOSFET</b> .....	3
<b>3</b>	<b>Body diode (MOSFET)</b> .....	5
<b>4</b>	<b>NTC-Thermistor</b> .....	6
<b>5</b>	<b>Characteristics diagrams</b> .....	7
<b>6</b>	<b>Circuit diagram</b> .....	12
<b>7</b>	<b>Package outlines</b> .....	13
<b>8</b>	<b>Module label code</b> .....	14
	<b>Revision history</b> .....	15
	<b>Disclaimer</b> .....	16

## 1 Package

**Table 1** Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	$V_{ISOL}$	RMS, $f = 50$ Hz, $t = 1$ min	3.0	kV
Internal isolation		basic insulation (class 1, IEC 61140)	$Al_2O_3$	
Comparative tracking index	$CTI$		> 200	
Relative thermal index (electrical)	$RTI$	housing	140	°C

**Table 2** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	$L_{sCE}$			9		nH
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_H = 25$ °C, per switch		2		mΩ
Storage temperature	$T_{stg}$		-40		125	°C
Mounting force per clamp	$F$		20		50	N
Weight	$G$			24		g

Note: The current under continuous operation is limited to 25 A rms per connector pin.

## 2 MOSFET

**Table 3** Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Drain-source voltage	$V_{DSS}$	$T_{vj} = 25$ °C	1200	V
Implemented drain current	$I_{DN}$		100	A
Continuous DC drain current	$I_{DDC}$	$T_{vj} = 175$ °C, $V_{GS} = 18$ V $T_H = 65$ °C	90	A
Repetitive peak drain current	$I_{DRM}$	verified by design, $t_p$ limited by $T_{vjmax}$	200	A
Gate-source voltage, max. transient voltage	$V_{GS}$	$D < 0.01$	-10/23	V
Gate-source voltage, max. static voltage	$V_{GS}$		-7/20	V

**Table 4** Recommended values

Parameter	Symbol	Note or test condition	Values	Unit
On-state gate voltage	$V_{GS(on)}$		15...18	V

(table continues...)

**Table 4 (continued) Recommended values**

Parameter	Symbol	Note or test condition	Values	Unit
Off-state gate voltage	$V_{GS(off)}$		-5...0	V

**Table 5 Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Drain-source on-resistance	$R_{DS(on)}$	$I_D = 100\text{ A}$	$V_{GS} = 18\text{ V}$ , $T_{vj} = 25\text{ °C}$		8.1		mΩ
			$V_{GS} = 18\text{ V}$ , $T_{vj} = 125\text{ °C}$		13.1		
			$V_{GS} = 18\text{ V}$ , $T_{vj} = 175\text{ °C}$		17.4		
			$V_{GS} = 15\text{ V}$ , $T_{vj} = 25\text{ °C}$		9.7		
Gate threshold voltage	$V_{GS(th)}$	$I_D = 40\text{ mA}$ , $V_{DS} = V_{GS}$ , $T_{vj} = 25\text{ °C}$ , (tested after 1ms pulse at $V_{GS} = +20\text{ V}$ )	3.45	4.3	5.15	V	
Total gate charge	$Q_G$	$V_{DD} = 800\text{ V}$ , $V_{GS} = -3/18\text{ V}$		0.297		μC	
Internal gate resistor	$R_{Gint}$	$T_{vj} = 25\text{ °C}$		2.1		Ω	
Input capacitance	$C_{ISS}$	$f = 100\text{ kHz}$ , $V_{DS} = 800\text{ V}$ , $V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		8.8	nF	
Output capacitance	$C_{OSS}$	$f = 100\text{ kHz}$ , $V_{DS} = 800\text{ V}$ , $V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		0.42	nF	
Reverse transfer capacitance	$C_{rSS}$	$f = 100\text{ kHz}$ , $V_{DS} = 800\text{ V}$ , $V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		0.028	nF	
$C_{OSS}$ stored energy	$E_{OSS}$	$V_{DS} = 800\text{ V}$ , $V_{GS} = -3/18\text{ V}$ , $T_{vj} = 25\text{ °C}$		172		μJ	
Drain-source leakage current	$I_{DSS}$	$V_{DS} = 1200\text{ V}$ , $V_{GS} = -3\text{ V}$	$T_{vj} = 25\text{ °C}$	0.06	380	μA	
Gate-source leakage current	$I_{GSS}$	$V_{DS} = 0\text{ V}$ , $T_{vj} = 25\text{ °C}$	$V_{GS} = 20\text{ V}$		400	nA	
Turn-on delay time (inductive load)	$t_{d\ on}$	$I_D = 100\text{ A}$ , $R_{Gon} = 8.2\text{ Ω}$ , $V_{DD} = 600\text{ V}$ , $V_{GS} = -3/18\text{ V}$	$T_{vj} = 25\text{ °C}$		53		ns
			$T_{vj} = 125\text{ °C}$		53		
			$T_{vj} = 175\text{ °C}$		53		
Rise time (inductive load)	$t_r$	$I_D = 100\text{ A}$ , $R_{Gon} = 8.2\text{ Ω}$ , $V_{DD} = 600\text{ V}$ , $V_{GS} = -3/18\text{ V}$	$T_{vj} = 25\text{ °C}$		70		ns
			$T_{vj} = 125\text{ °C}$		70		
			$T_{vj} = 175\text{ °C}$		70		
Turn-off delay time (inductive load)	$t_{d\ off}$	$I_D = 100\text{ A}$ , $R_{Goff} = 2.7\text{ Ω}$ , $V_{DD} = 600\text{ V}$ , $V_{GS} = -3/18\text{ V}$	$T_{vj} = 25\text{ °C}$		73		ns
			$T_{vj} = 125\text{ °C}$		79		
			$T_{vj} = 175\text{ °C}$		83		

**(table continues...)**

**Table 5 (continued) Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Fall time (inductive load)	$t_f$	$I_D = 100\text{ A}$ , $R_{Goff} = 2.7\ \Omega$ , $V_{DD} = 600\text{ V}$ , $V_{GS} = -3/18\text{ V}$	$T_{vj} = 25\text{ }^\circ\text{C}$		20	ns
			$T_{vj} = 125\text{ }^\circ\text{C}$		20	
			$T_{vj} = 175\text{ }^\circ\text{C}$		20	
Turn-on energy loss per pulse	$E_{on}$	$I_D = 100\text{ A}$ , $V_{DD} = 600\text{ V}$ , $L_\sigma = 35\text{ nH}$ , $V_{GS} = -3/18\text{ V}$ , $R_{Gon} = 8.2\ \Omega$ , $di/dt = 3.88\text{ kA}/\mu\text{s}$ ( $T_{vj} = 175\text{ }^\circ\text{C}$ )	$T_{vj} = 25\text{ }^\circ\text{C}$		2.87	mJ
			$T_{vj} = 125\text{ }^\circ\text{C}$		3.05	
			$T_{vj} = 175\text{ }^\circ\text{C}$		3.21	
Turn-off energy loss per pulse	$E_{off}$	$I_D = 100\text{ A}$ , $V_{DD} = 600\text{ V}$ , $L_\sigma = 35\text{ nH}$ , $V_{GS} = -3/18\text{ V}$ , $R_{Goff} = 2.7\ \Omega$ , $dv/dt = 24\text{ kV}/\mu\text{s}$ ( $T_{vj} = 175\text{ }^\circ\text{C}$ )	$T_{vj} = 25\text{ }^\circ\text{C}$		0.75	mJ
			$T_{vj} = 125\text{ }^\circ\text{C}$		0.81	
			$T_{vj} = 175\text{ }^\circ\text{C}$		0.83	
SC data	$I_{SC}$	$V_{GS} = -5/15\text{ V}$ , $V_{DD} = 800\text{ V}$ , $V_{DSmax} = V_{DSS} - L_{sDS} * di/dt$ , $R_G = 10\ \Omega$	$t_p = 2\ \mu\text{s}$ , $T_{vj} = 25\text{ }^\circ\text{C}$		840	A
			$t_p = 2\ \mu\text{s}$ , $T_{vj} = 150\text{ }^\circ\text{C}$		820	
Thermal resistance, junction to heat sink	$R_{thJH}$	per MOSFET, $\lambda_{grease} = 1\text{ W}/(\text{m}\cdot\text{K})$			0.553	K/W
Temperature under switching conditions	$T_{vj\ op}$		-40		175	$^\circ\text{C}$

*Note: The selection of positive and negative gate-source voltages impacts losses and the long-term behavior of the MOSFET and body diode. The design guidelines described in Application Note AN 2018-09 and AN 2021-13 must be considered to ensure sound operation of the device over the planned lifetime.*

*$T_{vj,op} > 150\text{ }^\circ\text{C}$  is allowed for operation at overload conditions for MOSFET and body diode. For detailed specifications, please refer to AN 2021-13.*

### 3 Body diode (MOSFET)

**Table 6 Maximum rated values**

Parameter	Symbol	Note or test condition	Values	Unit
DC body diode forward current	$I_{SD}$	$T_{vj} = 175\text{ }^\circ\text{C}$ , $V_{GS} = -3\text{ V}$ $T_H = 65\text{ }^\circ\text{C}$	45	A

**Table 7** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Forward voltage	$V_{SD}$	$I_{SD} = 100 \text{ A}, V_{GS} = -3 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$		4.2	5.35	V
			$T_{vj} = 125 \text{ }^\circ\text{C}$		3.9		
			$T_{vj} = 175 \text{ }^\circ\text{C}$		3.8		

## 4 NTC-Thermistor

**Table 8** Characteristic values


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	$R_{25}$	$T_{NTC} = 25 \text{ }^\circ\text{C}$		5		k $\Omega$
Deviation of $R_{100}$	$\Delta R/R$	$T_{NTC} = 100 \text{ }^\circ\text{C}, R_{100} = 493 \text{ } \Omega$	-5		5	%
Power dissipation	$P_{25}$	$T_{NTC} = 25 \text{ }^\circ\text{C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15 \text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15 \text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15 \text{ K}))]$		3433		K

Note: Specification according to the valid application note.

## 5 Characteristics diagrams


**Output characteristic (typical), MOSFET**

$I_D = f(V_{DS})$   
 $V_{GS} = 18\text{ V}$




**Output characteristic (typical), MOSFET**

$I_D = f(V_{DS})$   
 $V_{GS} = 15\text{ V}$




**Drain source on-resistance (typical), MOSFET**

$R_{DS(on)} = f(I_D)$   
 $V_{GS} = 18\text{ V}$



**Drain source on-resistance (typical), MOSFET**


$R_{DS(on)} = f(T_{vj})$   
 $I_D = 100\text{ A}$



5 Characteristics diagrams


**Output characteristic field (typical), MOSFET**

$I_D = f(V_{DS})$   
 $T_{vj} = 175\text{ °C}$




**Transfer characteristic (typical), MOSFET**

$I_D = f(V_{GS})$   
 $V_{DS} = 20\text{ V}$




**Gate-source threshold voltage (typical), MOSFET**

$V_{GS(th)} = f(T_{vj})$   
 $V_{GS} = V_{DS}$



**Gate charge characteristic (typical), MOSFET**

$V_{GS} = f(Q_G)$   
 $I_D = 100\text{ A}, T_{vj} = 25\text{ °C}$






5 Characteristics diagrams


**Capacity characteristic (typical), MOSFET**

$C = f(V_{DS})$   
 $f = 100 \text{ kHz}, T_{vj} = 25 \text{ }^\circ\text{C}, V_{GS} = 0 \text{ V}$




**Forward characteristic body diode (typical), MOSFET**

$I_{SD} = f(V_{SD})$   
 $T_{vj} = 25 \text{ }^\circ\text{C}$




**Forward voltage of body diode (typical), MOSFET**

$V_{SD} = f(T_{vj})$   
 $I_{SD} = 100 \text{ A}$



**Switching losses (typical), MOSFET**


$E = f(I_D)$   
 $R_{Goff} = 2.7 \text{ } \Omega, R_{Gon} = 8.2 \text{ } \Omega, V_{DD} = 600 \text{ V}, V_{GS} = -3/18 \text{ V}$



**Switching losses (typical), MOSFET**

$E = f(R_G)$


$V_{DD} = 600\text{ V}, I_D = 100\text{ A}, V_{GS} = -3/18\text{ V}$



**Switching times (typical), MOSFET**

$t = f(I_D)$


$R_{Goff} = 2.7\ \Omega, R_{Gon} = 8.2\ \Omega, V_{DD} = 600\text{ V}, T_{vj} = 175\text{ }^\circ\text{C}, V_{GS} = -3/18\text{ V}$



**Switching times (typical), MOSFET**

$t = f(R_G)$


$V_{DD} = 600\text{ V}, I_D = 100\text{ A}, T_{vj} = 175\text{ }^\circ\text{C}, V_{GS} = -3/18\text{ V}$



**Current slope (typical), MOSFET**

$di/dt = f(R_G)$

$V_{DD} = 600\text{ V}, I_D = 100\text{ A}, V_{GS} = -3/18\text{ V}$




5 Characteristics diagrams

**Voltage slope (typical), MOSFET**

$dv/dt = f(R_G)$


$V_{DD} = 600\text{ V}, I_D = 100\text{ A}, V_{GS} = -3/18\text{ V}$



**Reverse bias safe operating area (RBSOA), MOSFET**


$I_D = f(V_{DS})$

$R_{Goff} = 2.7\ \Omega, T_{vj} = 175\ \text{°C}, V_{GS} = -3/18\ \text{V}$




**Transient thermal impedance, MOSFET**

$Z_{th} = f(t)$



**Temperature characteristic (typical), NTC-Thermistor**

$R = f(T_{NTC})$



## 6 Circuit diagram




Figure 1

## 7 Package outlines






Figure 2

## 8 Module label code

<b>Module label code</b>			
Code format	Data Matrix	Barcode Code128	
Encoding	ASCII text	Code Set A	
Symbol size	16x16	23 digits	
Standard	IEC24720 and IEC16022	IEC8859-1	
Code content	<i>Content</i> Module serial number Module material number Production order number Date code (production year) Date code (production week)	<i>Digit</i> 1 - 5 6 - 11 12 - 19 20 - 21 22 - 23	<i>Example</i> 71549 142846 55054991 15 30
Example	 		<p>71549142846550549911530</p> <p>71549142846550549911530</p>

**Figure 3**

## Revision history

Document revision	Date of release	Description of changes
0.10	2022-10-19	Initial version
0.20	2023-01-24	Preliminary datasheet
0.30	2023-02-07	Preliminary datasheet

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2023-02-07**

**Published by**

**Infineon Technologies AG**

**81726 Munich, Germany**

**© 2023 Infineon Technologies AG**

**All Rights Reserved.**

**Do you have a question about any aspect of this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

**IFX-ABF645-003**

## Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffungsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

## Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[FF8MR12W1M1HB11BPSA1](#)