



Click [here](#) for the 3D model.

Dimensions

Chip Size	1210
L	3.2mm +0.3/-0.25mm (0.126 in +0.012/-0.01 in)
W	2.49mm +0.3/-0.25mm (0.098 in +0.012/-0.01 in)
T	2.79mm MAX (0.11 in MAX)
B	0.51mm +/-0.36mm (0.02 in +/-0.014 in)

Packaging Specifications

Packaging	Waffle
Packaging Quantity	80

General Information

Series	SMD MIL X7R PRF32535
Style	SMD Chip
Description	SMD, Military, Low ESR, MIL-PRF-32535
RoHS	No
Prop 65	⚠ WARNING: Cancer and reproductive harm - http://www.p65warnings.ca.gov
SCIP Number	d66873f5-e54d-410c-a0cf-ebf6fc635b5
Termination	Solder Plated
Failure Rate	N/A
Qualifications	MIL-PRF-32535
AEC-Q200	No
Component Weight	108 mg

Specifications

Capacitance	3.3 uF
Capacitance Tolerance	10%
Voltage DC	10 VDC
Dielectric Withstanding Voltage	25 VDC
Temperature Range	-55/+125°C
Temperature Coefficient	X7R
Dissipation Factor	5% 1 kHz 25C
Aging Rate	3% Loss/Decade Hour
Insulation Resistance	150 MOhms