8-pin SOIC Single-Channel **Phototransistor Output Optocoupler**

MOC205M, MOC206M, MOC207M, MOC211M, MOC212M, MOC213M, **MOC216M, MOC217M**

Description

These devices consist of a gallium arsenide infrared emitting diode optically coupled to a monolithic silicon phototransistor detector, in a surface mountable, small outline, plastic package. They are ideally suited for high-density applications, and eliminate the need for through-the-board mounting.

Features

- Closely Matched Current Transfer Ratios Minimum BV_{CEO} of 70 V Guaranteed
 - MOC205M, MOC206M, MOC207M
- Minimum BV_{CEO} of 30 V Guaranteed
- MOC211M, MOC212M, MOC213M, MOC216M, MOC217M
- Low LED Input Current Required for Easier Logic Interfacing MOC216M, MOC217M
- Convenient Plastic SOIC-8 Surface Mountable Package Style, with 0.050" Lead Spacing
- Safety and Regulatory Approvals:
 - ◆ UL1577, 2,500 VAC_{RMS} for 1 Minute
 - DIN-EN/IEC60747-5-5, 565 V Peak Working Insulation Voltage
- These are Pb–Free Devices

Applications

- Feedback Control Circuits
- Interfacing and Coupling Systems of Different Potentials and Impedances
- General Purpose Switching Circuits
- Monitor and Detection Circuits



ON Semiconductor®

www.onsemi.com



SOIC8 CASE 751DZ


MARKING DIAGRAM



- XXX = Specific Device Code
 - = DIN EN/IEC60747-5-5 Option (only appears on component ordered with this option)
 - = Year Code

V

- Х YY = Work Week
- = Assembly Package Code S



ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet.

SAFETY AND INSULATION RATINGS (As per DIN EN/IEC 60747–5–5, this optocoupler is suitable for "safe electrical insulation" only within the safety limit data. Compliance with the safety ratings shall be ensured by means of protective circuits.)

Parameter	Characteristics		
Installation Classifications per DIN VDE 0110/1.89 Table 1, For Rated Mains	<150 V _{RMS}	I–IV	
Voltage	<300 V _{RMS}	_	
Climatic Classification	55/100/21		
Pollution Degree (DIN VDE 0110/1.89)	2		
Comparative Tracking Index		175	

Symbol	Parameter	Value	Unit
V_{PR}	Input-to-Output Test Voltage, Method A, $V_{IORM} x 1.6 = V_{PR}$, Type and Sample Test with $t_m = 10$ s, Partial Discharge < 5 pC	904	V _{peak}
	Input–to–Output Test Voltage, Method B, V _{IORM} x 1.875 = V _{PR} , 100% Production Test with t_m = 1 s, Partial Discharge < 5 pC	1060	V _{peak}
VIORM	Maximum Working Insulation Voltage	565	V _{peak}
VIOTM	Highest Allowable Over-Voltage	4000	V _{peak}
	External Creepage	≥4	mm
	External Clearance	≥4	mm
DTI	Distance Through Insulation (Insulation Thickness)	≥0.4	mm
Τ _S	Case Temperature (Note 1)	150	°C
I _{S,INPUT}	Input Current (Note 1)	200	mA
P _{S,OUTPUT}	Output Power (Note 1)	300	mW
R _{IO}	Insulation Resistance at T _S , V _{IO} = 500 V (Note 1)	>10 ⁹	Ω

1. Safety limit values - maximum values allowed in the event of a failure.

ABSOLUTE MAXIMUM RATINGS (T_A = 25° C unless otherwise noted)

Symbol	Rating	Value	Unit				
TOTAL DEVICE							
T _{STG}	Storage Temperature	-40 to +125	°C				
T _A	Ambient Operating Temperature	-40 to +100	°C				
TJ	Junction Temperature	-40 to +125	°C				
T _{SOL}	Lead Solder Temperature	260 for 10 seconds	°C				
PD	Total Device Power Dissipation @ $T_A = 25^{\circ}C$	240	mW				
	Derate above 25°C	2.94	mW/°C				
EMITTER							
١ _F	Continuous Forward Current	60	mA				
I _F (pk)	Forward Current – Peak (PW = 100 μs, 120 pps)	1.0	А				
V _R	Reverse Voltage	6.0	V				
PD	LED Power Dissipation @ $T_A = 25^{\circ}C$	90	mW				
	Derate above 25°C	0.8	mW/°C				
DETECTO	R						
Ι _C	Continuous Collector Current	150	mA				
V _{CEO}	Collector-Emitter Voltage	30	V				
V _{ECO}	Emitter-Collector Voltage	7	V				
PD	Detector Power Dissipation @ $T_A = 25^{\circ}C$	150	mW				
	Derate above 25°C	1.76	mW/°C				

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

Symbol	Para	meter	Test Condition	Min	Тур	Max	Unit
EMITTER							
	Input Forward Voltage	MOC216M, MOC217M	I _F = 1 mA	-	1.07	1.3	V
V _F		MOC205M, MOC206M, MOC207M MOC211M, MOC212M, MOC213M	I _F = 10 mA	-	1.15	1.5	V
I _R	Reverse Leakage Current	L	V _R = 6 V	-	0.001	100	μΑ
C _{IN}	Input Capacitance			-	18	-	pF
DETECTOR	1						
I _{CEO1}	Collector-Emitter Dark Cur	rent	V_{CE} = 10 V, T_A = 25°C	-	1.0	50	nA
I _{CEO2}			$V_{CE} = 10 \text{ V}, \text{ T}_{A} = 100^{\circ}\text{C}$	-	1.0	-	μA
BV _{CEO}	Collector-Emitter Breakdown Voltage	MOC205M, MOC206M, MOC207M	I _C = 100 μA	70	100	-	V
		MOC211M, MOC212M, MOC213M, MOC216M, MOC217M	I _C = 100 μA	30	100	_	V
BV _{CBO}	Collector-Base Breakdown	Voltage	I _C = 10 μA	70	120	-	V
BV _{ECO}	Emitter-Collector Breakdov	vn Voltage	I _E = 100 μA	7	10	-	V
C _{CE}	Collector-Emitter Capacitance		f = 1.0 MHz, V _{CE} = 0 V	-	7	-	pF
COUPLED							
CTR	Collector-Output Current	MOC205M	I _F = 10 mA, V _{CE} = 10 V	40	-	80	%
		MOC206M	I _F = 10 mA, V _{CE} = 10 V	63	-	125	%
		MOC207M	I _F = 10 mA, V _{CE} = 10 V	100	-	200	%
		MOC211M	I _F = 10 mA, V _{CE} = 10 V	20	-	_	%
		MOC212M	I _F = 10 mA, V _{CE} = 10 V	50	-	_	%
		MOC213M	I _F = 10 mA, V _{CE} = 10 V	100	-	_	%
		MOC216M	I _F = 1 mA, V _{CE} = 5 V	50	-	_	%
		MOC217M	I _F = 1 mA, V _{CE} = 5 V	100	-	_	%
V _{CE(SAT)}	Collector-Emitter Saturation Voltage	MOC205M, MOC206M, MOC207M MOC211M, MOC212M, MOC213M	I _C = 2 mA, I _F = 10 mA	-	-	0.4	V
		MOC216M, MOC217M	$I_{C} = 100 \ \mu A, I_{F} = 1 \ mA$	-	-	0.4	V
t _{on}	Turn-On Time		$\label{eq:lc} \begin{array}{l} I_C = 2 \text{ mA}, \ V_{CC} = 10 \text{ V}, \\ R_L = 100 \ \Omega \ (\text{Figure 12}) \end{array}$	-	7.5	-	μs
t _{off}	Turn-Off Time		I_{C} = 2 mA, V _{CC} = 10 V, R _L = 100 Ω (Figure 12)	-	5.7	-	μs
t _r	Rise Time		$\begin{array}{l} \text{I}_{\text{C}} = 2 \text{ mA}, \text{ V}_{\text{CC}} = 10 \text{ V}, \\ \text{R}_{\text{L}} = 100 \ \Omega \ (\text{Figure 12}) \end{array}$	-	3.2	-	μs
t _f	Fall Time		$\label{eq:lc} \begin{array}{l} \text{I}_{\text{C}} = 2 \text{ mA}, \text{ V}_{\text{CC}} = 10 \text{ V}, \\ \text{R}_{\text{L}} = 100 \ \Omega \ (\text{Figure 12}) \end{array}$	-	4.7	-	μs


ELECTRICAL CHARACTERISTICS (T_A = 25° C unless otherwise noted)

ISOLATION CHARACTERISTICS

V _{ISO}	Input-Output Isolation Voltage	t = 1 Minute	2500	-	-	VAC _{RMS}
C _{ISO}	Isolation Capacitance	$V_{I-O} = 0 V$, f = 1 MHz	-	0.2	1	pF
R _{ISO}	Isolation Resistance	$V_{I-O} = \pm 500 \text{ VDC},$ $T_A = 25^{\circ}\text{C}$	10 ¹¹	-	-	Ω

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.












Figure 3. Output Current vs. Ambient Temperature

1.6






Figure 4. Output Current vs. Collector-Emitter Voltage








Figure 6. CTR vs. RBE (Unsaturated)

TYPICAL PERFORMANCE CURVES (continued)




Figure 7. CTR vs. R_{BE} (Saturated)

Figure 8. Normalized t_{on} vs. R_{BE}





Figure 9. Normalized tooff vs. RBE








Figure 11. Reflow Profile

Table 1.


Profile Freature	Pb-Free Assembly Profile
Temperature Minimum (Tsmin)	150°C
Temperature Maximum (Tsmax)	200°C
Time (t _S) from (Tsmin to Tsmax)	60 - 120 seconds
Ramp-up Rate (t _L to t _P)	3°C/second maximum
Liquidous Temperature (T _L)	217°C
Time (t _L) Maintained Above (T _L)	60 - 150 seconds
Peak Body Package Temperature	260°C +0°C / -5°C
Time (t _P) within 5°C of 260°C	30 seconds
Ramp-down Rate (T _P to T _L)	6°C/second maximum
Time 25°C to Peak Temperature	8 minutes maximum

ORDERING INFORMATION (Note 2)

Part Number	Package	Shipping [†]
MOC205M	Small Outline 8-Pin	100 Units / Tube
MOC205R2M Small Outline 8-Pin		2500 / Tape & Reel
MOC205VM Small Outline 8–Pin, DIN EN/IEC60747–5–5 Option		100 Units / Tube
MOC205R2VM Small Outline 8-Pin, DIN EN/IEC60747-5-5 Optio		2500 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

2. The product orderable part number system listed in this table also applies to the MOC20XM and MOC21XM products.



DOCUMENT NUMBER:	98AON13733G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION: SOIC8 PAGE 1		PAGE 1 OF 1			
ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.					

© Semiconductor Components Industries, LLC, 2019

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

MOC213R2VM MOC217R2M MOC207M MOC212VM MOC211R2VM MOC205R2VM MOC207R2M MOC205VM MOC211R2M MOC212R2VM MOC206R2VM MOC206R2M MOC207R2VM MOC205R2M MOC213VM MOC205M MOC206M MOC213M MOC211M MOC212M MOC207VM MOC212R2M MOC206VM MOC211VM MOC213R2M MOC216M MOC216VM MOC217M MOC217R2VM MOC217VM MOC216R2M MOC216R2VM