



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	02	P	LTR	DESCRIPTION	DATE	DWN	APVD
		H1		REV PER ECR 07-017037	20JUL07	JR	TM

AMP WIRE RANGE	AMP INSULATION RANGE
22-16 AWG 0.3-1.5 mm ²	.140 MAX DIA 3.5 MAX DIA



- △1 ASTERISK * FOR PHOS BRONZE VERSION ONLY
- △2 OBSOLETE W/O REPLACEMENT



△2	OBSOLETE	2-165563-6	GOLD	PHOS BRONZE	165563-6
△2	OBSOLETE	2-165563-5	GOLD	BRASS	165563-5
△2	OBSOLETE	2-165563-4	SILVER	PHOS BRONZE	165563-4
△2	OBSOLETE	2-165563-3	SILVER	BRASS	165563-3
△2	OBSOLETE	2-165563-2	TIN	PHOS BRONZE	165563-2
		2-165563-1	TIN	BRASS	165563-1
		PN ON TAPE	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 15APR05	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: mm		CHK T MICHIELUTTI 15APR05	NAME RECEPTACLE, FASTON, PIDG, .110 SERIES		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHIELUTTI 15APR05	PRODUCT SPEC		
0 PLC ± -		APPLICATION SPEC			
1 PLC ± 0.2		SIZE		CAGE CODE	DRAWING NO
2 PLC ± -		A3		00779	C-165563
3 PLC ± -		WEIGHT		RESTRICTED TO	
4 PLC ± -		-		-	
ANGLES ± 5'		CUSTOMER DRAWING			
MATERIAL		SCALE		SHEET	REV
-		1:1		1 OF 1	H1