

668A.10 | 668A - Cobalt steel bimetal saw blades



Description:

- Characteristics: 668A.8: for thick semi-hard steels thickness recommended: 6 25 mm. 668A.10: for special or alloy steels thickness recommended: 3 6 mm. 668A.12: for stainless steel, copper thickness recommended: 1 3 mm.
- Blade in cobalt steel: higher heat resistance, reduced teeth wear.
- Equal performance throughout blade lifecycle.
- Enhanced flexibility and neater cut.
- Suited to all materials.
- Blade length 300 mm.
- Minimum order: 10 blades.

=	668A.10
CONTENT SET []	10
Length L [mm]	300.0
Teeth [cm]	10.0
Weight [Kg]	0.018
Contents []	Plastic box