


PC MOUNTING



▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
2-3	OPEN	2-1





NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: GOLD
5. RATING: 0.4VOLT-AMPS MAX. @20V MAX. AC OR DC
6. ELECTRIC LIFE: 30,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. PACKAGE: TRAY/270 PIECES PER.
12. 2011/65/EU (ROHS) COMPLIANT

OBSOLETE
 March 2018
 PCR 23242



E-SWITCH MARKING and RATINGS



B	23147	drawing update	12/21/17	MW
A	17058	RELEASED FOR PRODUCTION	3/6/07	TN
REV	PCR NO	DESCRIPTION	DATE	BY

E-SWITCH®				
TITLE 200AWMSP3T2A1M6RE- NO FRONT BRACKET				
SCALE	DATE	DR	DWG	REV
3:1	3/6/2007	TN	T201243	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED