



2-wire level transmitter

5343A

- Potentiometer or Ohmic input
- Programmable sensor error value
- High measurement accuracy
- Unique process calibration function
- Programmable via standard PC



Application

- Conversion of resistance variation to standard analog current signals, e.g. from Ohmic level sensors or valve positions.
- User-defined linearization function can be activated.


Technical characteristics

- Within a few seconds the user can program PR5343A to measure within the defined Ohmic values.
- Continuous check of vital stored data for safety reasons.
- The transmitter is protected against polarity reversal.
- PR5343A is configured to the current task by way of a PC, the PReset software and the communications interface Loop Link.
- The PRelevel configuration tool included in the PReset software has been developed specifically for the configuration of level applications. Among other things, it contains a function for "on line" measurement of input span as well as a linearization function for volume linear output from horizontal cylindrical tanks.

Mounting / installation

- For DIN form B sensor head or DIN rail mounting with a special fitting.

Connections



Order:

| |
|-------|
| Type |
| 5343A |

Environmental Conditions

| | |
|---|----------------------|
| Specifications range..... | -40°C to +85°C |
| Calibration temperature..... | 20...28°C |
| Relative humidity..... | < 95% RH (non-cond.) |
| Protection degree (encl./terminal)..... | IP68 / IP00 |

Mechanical specifications

| | |
|-----------------------------|---------------------------------------|
| Dimensions..... | Ø 44 x 20.2 mm |
| Weight approx..... | 50 g |
| Wire size..... | 1 x 1.5 mm ² stranded wire |
| Screw terminal torque..... | 0.4 Nm |
| Vibration..... | IEC 60068-2-6 : 2007 |
| Vibration: 2...25 Hz..... | ±1.6 mm |
| Vibration: 25...100 Hz..... | ±4 g |

Common specifications**Supply**

| | |
|---------------------|--------------|
| Supply voltage..... | 8.0...35 VDC |
|---------------------|--------------|

Response time

| | |
|--------------------------------------|------------------------------------|
| Response time (programmable)..... | 0.33...60 s |
| Internal consumption..... | 25 mW...0.8 W |
| Voltage drop..... | 8.0 VDC |
| Warm-up time..... | 5 min. |
| Programming..... | Loop Link |
| Signal / noise ratio..... | Min. 60 dB |
| Accuracy..... | Better than 0.1% of selected range |
| Signal dynamics, input..... | 19 bit |
| Signal dynamics, output..... | 16 bit |
| Effect of supply voltage change..... | < 0.005% of span / VDC |
| EMC immunity influence..... | < ±0.5% of span |

Input specifications**Common input specifications**

| | |
|------------------|----------------------------|
| Max. offset..... | 50% of selected max. value |
|------------------|----------------------------|

Linear resistance input

| | |
|---|-------------------|
| Measurement range / min. range (span)..... | 0...100 kΩ / 1 kΩ |
| Cable resistance per wire (max.)..... | 100 Ω |
| Sensor current..... | > 25 μA, < 120 μA |
| Effect of sensor cable resistance (3-wire)..... | < 0.002 Ω / Ω |
| Sensor error detection, lin. R..... | Yes |
| Min. measurement range..... | 1 kΩ |

Output specifications**Current output**

| | |
|------------------------------------|-----------------------------|
| Signal range..... | 4...20 mA |
| Min. signal range..... | 16 mA |
| Load (@ current output)..... | ≤ (Vsupply - 8) / 0.023 [Ω] |
| Load stability..... | ≤ 0.01% of span / 100 Ω |
| Sensor error indication..... | Programmable 3.5...23 mA |
| NAMUR NE 43 Upscale/Downscale..... | 23 mA / 3.5 mA |

Common output specifications

| | |
|--------------------|-----------------------------------|
| Updating time..... | 135 ms |
| *of span..... | = of the presently selected range |

Observed authority requirements

| | |
|----------|------------|
| EMC..... | 2014/30/EU |
|----------|------------|

Approvals

| | |
|----------------------|-----------------------------|
| ATEX 2014/34/EU..... | KEMA 10ATEX0004 X |
| IECEX..... | DEK 13.0036X |
| INMETRO..... | DEKRA 13.0002 X |
| EAC..... | TR-CU 020/2011 |
| DNV-GL Marine..... | Stand. f. Certific. No. 2.4 |
| GL..... | V1-7-2 |