


## HVZOE105NF

Aliases (USCHVZOE105N00)

HVZ, Supercapacitors, Radial, 1F, 30%, 2.7 VDC, Wire Leads, Lead Spacing = 3.5mm



Click [here](#) for the 3D model.

Dimensions	
D	8mm +/-0.5mm
L	12mm +/-2mm
S	3.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.6mm NOM

Packaging Specifications	
Lead	Wire Leads
Packaging	Bulk, Box
Packaging Quantity	4000

### General Information

Series	HVZ
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
AEC-Q200	No
Component Weight	1g

### Specifications

Capacitance	1F
Capacitance Tolerance	30%
Voltage DC	2.7 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
Resistance	300 mOhms (1kHz)
Discharge Current	0.8 mAmps (30 Minutes After Charging)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.