


MS3V-T1R

Tuning Fork Crystal 30 kHz – 200 kHz



DIMENSIONS



All dimensions in mm typical

APPLICATIONS

IoT
Metering
Wearables
Health Care
Mobile Phones
Consumer Electronics

DESCRIPTION

The MS3V-T1R is a low frequency surface mount technology Quartz Crystal Unit that incorporates a tuning fork Quartz Crystal Resonator. It operates under vacuum in a hermetically sealed square-bodied metal can package.

MS3V-T1R is compatible with other suppliers' same footprint crystals.

FEATURES

High stability is guaranteed by hermetic sealing.
High shock and vibration resistant.
Small, proven surface mount technology package for reflow soldering.
Excellent lead coplanarity for surface mounting.
RoHS-compliant.

ELECTRICAL CHARACTERISTICS AT 25°C

Standard Frequency	¹⁾	F_L	32.768	kHz
Load capacitance	²⁾	C_L	6.0 / 7.0 / 9.0 / 12.5	pF
Frequency tolerance	³⁾	$\Delta F/F$	±20	ppm
		$\Delta F/F$	±100	ppm
Series resistance typ./max.		R_S	50 / 65	kΩ
Motional capacitance typ.		C_1	2.25	fF
Static capacitance typ.		C_0	0.9	pF
Drive level max.		P	1.0	μW
Insulation resistance min.		R_i	500	MΩ
Aging first year max.		$\Delta F/F$	±3	ppm
Turnover temperature		T_0	25 ±5	°C
Frequency vs. temperature		$\Delta F/F_0$	$-0.035 \text{ ppm}/^\circ\text{C} \cdot (T - T_0)^2 \pm 10\%$	ppm

1) Other frequencies on request.

2) Other load capacitances on request.

3) Tighter and wider frequency tolerances on request.

STANDARD FREQUENCIES

Frequencies		
32.768 kHz	60.000 kHz	76.800 kHz
Other frequencies on request		

ENVIRONMENTAL CHARACTERISTICS

		Conditions	Max. Dev.
Storage temperature range		-55 to +85°C	
TA Operating temperature range		-40 to +85°C	
Shock resistance	ΔF/F	5000 g, 0.3 ms, ½ sine	±5 ppm
Vibration resistance	ΔF/F	20 g / 10–2000 Hz	±5 ppm

TERMINATIONS AND PROCESSING

Type	Termination	Processing
MS3V-T1R	Can: Au flashed ¹⁾ Leads: Formed leads Au flashed	For surface mounting IPC/JEDEC J-STD-020C 260°C / 20 - 40 s
MS3V-T1N	Can: Au flashed ¹⁾ Leads: Straight leads Au flashed	For through-hole mounting IPC/JEDEC J-STD-020C 260°C / 20 - 40 s

1) Pd plated can on request.

ORDERING INFORMATION

M S 3 V - T 1 R 32.768 kHz 12.5 pF ±20 ppm TA QC Au		
Square metal package MS3V = 1.4 x 1.4 x 5.2 mm	Frequency F_L	
SMT Package	Load capacitance C_L	
Au flashed leads	6.0 pF	
Package lead form	7.0 pF	
R = SMD spacing 1.0 mm	9.0 pF	
N = Straight leads	12.5 pF	
	Other C_L on request	
	Frequency tolerance	
	±20 ppm	
	±100 ppm	
	Tighter and wider freq. tolerances on request	
	Temperature range	
	TA = -40 to +85°C	
	Qualification	
	QC = Commercial Grade	
	Au flashed can	

A unique part number will be generated for each product specification, i.e:		
20xxx-ML02	2'000 pcs (in 16 mm tape on 7" reel)	MS3V-T1R
20xxx-PL09	9'000 pcs (in 16 mm tape on 13" reel)	MS3V-T1R
20xxx-BA01	1'000 pcs (in plastic bag)	MS3V-T1N

All specifications subject to change without notice.



Micro Crystal AG
Muehlestrasse 14
CH-2540 Grenchen
Switzerland

Phone +41 32 655 82 82
Fax +41 32 655 82 83
sales@microcrystal.com
www.microcrystal.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Crystal:

[MS3V-T1R-32.768kHz-12.5pF-20PPM-TA-QC-Au](#) [MS3V-T1R-32.768kHz-9pF-20PPM-TA-QC-Au](#) [MS3V-T1R-32.768kHz-7pF-20PPM-TA-QC-Au](#)