

## Ultra-Grip Domed Head

Carbon Steel  
Mandrel: Carbon Steel



			DESCRIPTION							BULK PACK		
										ARTICLE	BOX QTY	
mm	mm	mm		mm	mm	mm	mm	N	N			kg
<b>4.8</b>	10.1	1.6 - 7.0	<b>SD670UG</b>	4.9 - 5.1	9.2 - 9.8	2.1	3.0	6,500	5,330	62323	2,000	
	14.1	5.5 - 11.1	<b>SD6110UG</b>							62324	2,000	
	14.1	1.6 - 11.1	<b>SD6110UGX</b>							62325	2,000	
<b>6.4</b>	13.8	2.0 - 9.5	<b>SD895UG</b>	6.6 - 7.0	12.7 - 13.3	2.8	4.0	11,800	10,000	62338	1,000	
	20.3	9.0 - 16.0	<b>SD8160UG</b>							62339	1,000	
	20.3	2.0 - 16.0	<b>SD8160UGX</b>							62340	1,000	

## Ultra-Grip 100° Countersunk

Carbon Steel  
Mandrel: Carbon Steel



			DESCRIPTION							BULK PACK		
										ARTICLE	BOX QTY	
mm	mm	mm		mm	mm	mm	mm	N	N			kg
<b>4.8</b>	11.9	3.2 - 8.5	<b>SK685UG</b>	4.9 - 5.1	8.1 - 8.7	1.7	3.0	6,500	5,330	62326	2,000	
	16.2	7.5 - 12.5	<b>SK6125UG</b>							62327	2,000	
<b>6.4</b>	16.6	4.0 - 12.0	<b>SK8120UG</b>	6.6 - 7.0	9.7 - 10.3	2.0	4.0	11,800	10,000	62341	1,000	
	23.1	10.5 - 18.5	<b>SK8185UG</b>							62342	1,000	

$d$ =Nominal Diameter;  $l$ =Body Length (+/- 0.5mm);  $g$ =Grip Range (Min - Max);  $d_h$ =Hole Size (Min - Max);  $d_k$ =Flange Diameter (Min - Max);  
 $k$ =Flange Thickness (Max);  $d_m$ =Nominal Mandrel Diameter;  $S$ =Nominal Shear Strength;  $T$ =Nominal Tensile Strength

The POP® Riveting Systems catalogue contains details of our core range only. Other rivet configurations are available. Items marked "on request" are subject to minimum order quantities or values and made to order lead times. Please enquire to Emhart Customer Service. For the latest catalogue digital version please visit [www.emhart.eu](http://www.emhart.eu)