

## Amphenol ICC

# 1.00mm Pitch FFC/FPC – F52L/F52M Series

### VERTICAL NON ZIF FLEX CONNECTORS

F52L/F52M series are 1.00mm pitch vertical Non-ZIF flex connectors with surface mount termination and no locking mechanism. F52L and F52M are vertical A-Type and B-Type respectively. These connectors feature a height of 5.04mm and comes in 4 to 30 contacts. This series features a cable thickness of 0.30mm and provides enhanced durability of 30 mating cycles. The connectors come with a robust design and prevent solder and flux wicking. These are ideal for automotive, data, industrial, communication, consumer and medical applications.

- Single action low-force FFC/FPC insertion and removal
- Ensures high solderability and durability
- Wide operating temperature range of -40°C to +105°C



#### **FEATURES**

- Non-ZIF (Zero Insertion Force) mechanism requires some force for insertion
- No locking mechanism
- Design against solder and flux wicking
- High-temperature thermoplastic housing
- 4 to 30 positions available
- Lead and halogen-free

#### **BENEFITS**

- Single action low-force FFC/FPC insertion and removal
- Ensures high solderability
- Wide operating temperature range of -40°C to +105°C
- Comprehensive range to satisfy different customer requirements
- Meets environmental, health and safety requirements

### **TECHNICAL INFORMATION**

#### **MATERIAL**

- Housing: LCP, natural color (UL94V-0)
- Contact: Phosphor bronze, T=0.20mm
- Mylar: T=0.10mm, thermostable, yellow color

#### **MECHANICAL PERFORMANCE**

- FFC/FPC Retention Force: 40gf/pin min.
- FFC/FPC Insertion Force: 3,000gf max.
- Terminal Retention Force: 200gf/terminal min.
- Durability: 30 mating cycles

#### **ELECTRICAL PERFORMANCE**

- Voltage Rating: 50V AC/DC
- Current Rating: 0.5A
- Contact Resistance: 30MΩ max.
- Insulation Resistance: 500MΩ min.
- Dielectric Withstanding Voltage: No short or breakdown after 500V AC, 2mA, 1min.

#### PACKAGING

Tape & Reel

#### APPROVALS AND CERTIFICATIONS

- UL file number E41797
- RoHS compliant

#### **SPECIFICATION**

Aorora Product Specification: IS.EQC.050

#### **ENVIRONMENTAL**

Operating Temperature Range: -40°C to +105°C

#### **TARGET MARKETS/APPLICATIONS**



Car Multimedia **Car Navigation** Dashboard PND



Power Switches



Notebook **Tablets** Wearables Gaming DSC

LCD & PDP TV

Router Server ODD




Sensing element Monitoring camera Human Machine Interface Industrial PC Robotics



Ultrasonic Patient Monitor MRI CT Infusion Pump

### PART NUMBER SELECTOR



### www.amphenol-icc.com

#### Disclaimer

Please note that the above information is subject to change without notice.