

242272



242276



Tape is wound on a low-sloughing plastic core.

RoHS 2, REACH, and Conflict Minerals Statement

None of the RoHS 2 restricted materials, or REACH substances of very high concern as of 2015/12/17, or Conflict Minerals are intentionally added in manufacturing this product. Ref: European Union Directive 2011/65/EU and Regulation (EC) No. 1907/2006/CE. See details of Limited Warranty online at Vermason.co.uk.

Replace regular adhesive tapes with Antistatic tapes complying with EN 61340-5

- "All generators of electrostatic charges, such as untreated plastic films, foams, synthetic fibres, adhesive tapes, etc., must be prohibited and should be kept away from the EPA [ESD protected area]." (EN 61340-5-2 section 6)
- "EPA should never have any electrostatic generative adhesive tapes or labels, as these can cause very high potentials when applied or stripped off." (EN 61340-5-1 section 7.4)

Wescorp Tape Storage and Limited Warranty:

The user must determine the suitability for use of an antistatic tape for his particular application. For best results, tape inventory should be continually replenished. It is recommended that rolls of tape be stored flat and rotated (flipped over to the other side) periodically. Tapes should be stored in a dry, well ventilated room with a reasonably consistent temperature of 68°F (20°C) and be protected from exposure to direct sunlight. Tape should not be stored in ultraviolet sunlight, moisture, or heat. Tape over one year old should be evaluated by the user to determine acceptability for the user's application. Vermason recommends those tracking useful life of product to use shipping/invoice date as Vermason expressly warrants that for a period of one (1) year from the date of purchase, our Wescorp Brand ESD Tape will be free of defects in material (parts) and workmanship (labor). See details of Limited Warranty online at Vermason.co.uk

*Wescorp is a Desco Industries brand.

Note: Tape rolls may vary slightly in color

Antistatic Cellulose Tape with Symbols

For general purpose applications

- 2.4 mil (0.06 mm) total thickness
- Cellulose film resistance 1×10^{10} to $< 1 \times 10^{12}$ ohms per IEC 61340-2-3
- Rubber based adhesive absorbs moisture
- Adhesive surface resistance 1×10^{10} to $< 1 \times 10^{12}$ ohms per IEC 61340-2-3
- Temperature Range -10°C - 71°C (14°F - 160°F); meets MIL-B-81705 of 100°C for 10 min max
- Available in clear, clear with ESD symbols, and clear with ESD symbols with yellow stripe. Marking is approved symbols of Mil STD-1285* and CLC / TR 61340-5-2:2008.
- Symbols printed in between film and adhesive; will not rub off.

Width - See Metric Note


Tape	12mm	18mm	24mm	48mm	Core	Length
Antistatic Clear Cellulose with Symbols	242270	242271	242272	242273	76.22mm	65.8 m
Antistatic Clear Cellulose w/Symbols & Yellow Stripe	242274	242275	242276		76.22mm	65.8 m

Tape widths are nominal metric ± 0.8 mm

6 mm nominal or 0.236" ± 0.031
 12 mm nominal or 0.472" ± 0.031
 18 mm nominal or 0.709" ± 0.031
 24 mm nominal or 0.945" ± 0.031
 48 mm nominal or 1.890" ± 0.031

No sulfur, surfactants or silicone based material (adhesive, film backing, release material) is used in the manufacture of our cellulose tape.

*Military organizations sometimes use MIL-STD-1285 for hardware marking and that document once required the use of the "three arrows in a circle" symbol. That symbol has been changed for consistency with industry marking to the "hand in triangle" ESD Susceptibility symbol. (Ref: TR20.20 section 5.3.14.1)



Antistatic Tape

Imprint on Clear Cellulose with Symbols



Antistatic Tape

Imprint on Clear Cellulose w/ Symbols w/Yellow Stripe



Specifications and procedures subject to change without notice.

Vermason

WESCORP* ESD Cellulose Tape with Symbols, Plastic Core

VERMASON
 UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,
 HERTS, SG6 2TD UK
 PHONE: +44 (0) 1462-672005 FAX: +44 (0) 1462-670440
 E-MAIL: Service@Vermason.co.uk INTERNET: Vermason.co.uk

DRAWING NUMBER:
242270

DATE:
February
2016