

HE2G Grip Switch







New compact, light-weight grip switch provides a comfortable hold


An HE2B enabling switch, compliant with IEC/EN60947-5-8, is installed inside the HE2G grip switch.



Equipped with different control units for various use.







Internal connector and solder terminals available

AS6M-2KT2PA

Choice of wire-saving internal connectors or solder terminal connections.

Internal Connector



Solder Terminal



Design

Compact design fits comfortably in the hand

The curved grip and small-size makes operation comfortable. The light-weight (approx. 140g, HE2G-21SH) and compact size is suitable for operators with small hands and for use in tight working environments.



Light operating force ensures worry-free operation

The operating force required to shift from position 1 (contact OFF) to position 2 (contact ON) is reduced by 50% compared with IDEC's HE1G grip switch. Less operating force ensures worry-free operation.


3-position switch with distinctive tactile feedback


Tactile clicking feedback allows easy recognition of switch operation when shifting from position 1 (contact OFF) to position 2 (contact ON).

Safety

Dual enabling contacts ensure a high level of safety

Dual enabling contacts with a separate actuator for each contact is IDEC's original design. This ensures a higher safety level. Disparity detection of category 4 (ISO 13849-1) can be achieved by using this switch with a safety relay module or a safety controller.







Types

Contact Configuration								
3-Position Switch	Monitor Switch	Additional Control Units (*1)				Rubber Boot Material /	Wiring Style	Type No.
		Emergency Stop Switch	Control Unit (A)	Control Unit (B)	Pilot Switch (green) (C)	Color	Willing Otyle	(Ordering Type No.)
2 contacts	With (1NC)	Without				Silicon Rubber / (Yellow) (*2)	Solder Terminal	HE2G-21SH
							Internal Connector	HE2G-21SC
						NBR/PVC Polyblend / (Gray) (*3)	Solder Terminal	HE2G-21SH-1N
							Internal Connector	HE2G-21SC-1N
			Without		Without		Solder Terminal	HE2G-21SHE
					With		Solder Terminal	HE2G-21SHE-P-0
		Without	Momentary Pushbutton (DPDT)	Momentary Pushbutton (DPDT)	Without	Silicon Rubber / (Yellow) (*2)	Solder Terminal	HE2G-21SH-L-L
		With (2NC)					Solder Terminal	HE2G-21SHE-L-L
							Internal Connector	HE2G-21SCE-L-L
				Key Selector Switch (DPDT)			Solder Terminal	HE2G-21SHE-L-K
							Internal Connector	HE2G-21SCE-L-K

- *1) Additional control units installed on the HE2G are as follows: Emergency Stop Switch: XA1E-BV3U02R Momentary Pushbutton: AB6M-M2PLW Key Selector Switch: AS6M-2KT2PA Pilot Light: UP9P-2498G
- *2) Silicon rubber: Can be used in general factories. Remains flexible in cold temperatures. Suitable in applications with a wide operating temperature
- *3) NBR/PVC polyblend: Oil-proof. Suitable for environments subjected to machine oil and painting robots where silicon rubber cannot be used.

Specifications

Degree of F (IEC 60529		IP67 / 66 (without additional control units) IP65 (with additional control units)		
Conditional	Short-circuit Current	50A (250V) (Note)		
Direct Oper	ning Force	60N (monitor switch)		
Free Fall		1.0m 1 fall (IEC60068-2-32 compliant)		
Applicable Wire Size	Internal Connector	0.05 to 0.86 mm ² (AWG18 to 30) (AWG22 between switch and connector		
Wile Gize	Solder Terminal	0.5 mm² maximum		
Applicable (Cable	Multicore cable diameter ø4.5 to 10 mm		

Note) Use a 250V/10A fast-blow fuse as a short-circuit protector

Contact Ratings


Rated Insulation Vo	250V (momentary pushbutton and key selector: 125V) / 30V (with pilot light)				
Rated Thermal Cur	3A (emergency stop switch: 5A)*				
Rated Voltage (Ue)			30V	125V	250V
	AC	Resistive Load (AC-12)	_	1A	0.5A
Rated Current (le) 3-position switch		Inductive Load (AC-15)	_	0.7A	0.5A
(Terminal No. NO1-C1, NO2-C2)	DC	Resistive Load (DC-12)	1A	0.2A	_
		Inductive Load (DC-13)	0.7A	0.1A	_

Note) Minimum applicable load (reference value): 3V AC/DC, 5 mA (Applicable operation area depends on the operating conditions.)

- *However, operating temperature for internal connectors:

- -25°C min., 40°C max. 2.5A (12 to 19 poles), 2A (20 to 22 poles) 40°C min., 50°C max. 2.5A (8 to12 poles), 2A (13 to 22 poles) 50°C min., 60°C max. 2.5A (6, 7 poles), 2A (8 to13 poles), 1.5A (14 to 22 poles)


Operation Characteristics



- : contact OFF (open) : contact ON (closed)
- Terminals NO1-C1/A1-B1, NO2-C2/A3-B3 are outputs of the 3-position enabling
- The above operation characteristics show when the center of the grip switch button is pressed. Because two contacts are designed to operate independently, pressing the edge of the button turns on one contact earlier than the other contact,


Specifications and other descriptions in this catalog are subject to change without notice.

Additional Control Unit Layout



Contact Arrangement (Internal Connector)

•Internal Connector Pin No.



3-position switch /control unit side connector: Tyco Electronics D-1200D Series Tab housing: 1-1903130-2 (4-pin connector) 1-1903130-3 (6-pin connector)

6-Pin Connector Allotment Table

Tab contact: 19303116-2

· Emergency stop · 3-position switch

- - Momentary pushbutton Key selector switch

•Terminal Arrangement (TOP VIEW)



switch




 Emergency stop
 Momentary pushbutton Key selector switch

Internal Connector Pin No.	Momentary pushbutton Key selector switch		
A1	C2		
A2	NO2		
A3	NC2		
B1	C1		
B2	NO1		
B3	NC1		

- For signal of the 3-position switch, see "Operation Characteristics".
- · For solder terminal type terminal arrangement of each control unit, see each catalog.

Dimensions

•HE2G-21SH/HE2G-21SC



Internal Connector

Tyco Electronics D-1200D Series

- Receptacle: 1-1827864-□
- · Receptacle contact
 - 1827586-2: AWG28 to 30
 - (Hand tool: 1762952-1)
 - 1827587-2: AWG22 to 28
 - (Hand tool: 1762846-1)
 - 1827588-2: AWG22 to 28
 - (Hand tool: 1762950-1) 1827589-2: AWG18 to 22
 - (Hand tool: 1762625-1)

Specify 2 or 3 in place of □.

- 2: 4-pin connector
- 3: 6-pin connector

The customer needs to purchase the connector separately.

All dimensions in mm. causing a delay in operation To avoid this, always press the center of the button.

DEC

IDEC CORPORATION

7-31, Nishi-Miyahara 1-Chome, Yodogawa-ku, Osaka 532-8550, Japan Tel: +81-6-6398-2571, Fax: +81-6-6392-9731 E-mail: marketing@idec.co.jp

IDEC CORPORATION (USA) **IDEC CANADA LIMITED** IDEC AUSTRALIA PTY. LTD **IDEC ELECTRONICS LIMITED**

IDEC ELEKTROTECHNIK GmbH IDEC (SHANGHAI) CORPORATION IDEC (BEIJING) CORPORATION IDEC (SHENZHEN) CORPORATION IDEC IZUMI (H.K.) CO., LTD. **IDEC TAIWAN CORPORATION** IDEC IZUMI ASIA PTE. LTD.

www.idec.com