

# 2.5mm Jack Socket

## 4 Pole



pro-SIGNAL




### Specifications

No. of Contacts	: 4 Contacts
Gender	: Jack
Pin Diameter	: 2.5mm
Contact Resistance	: 50mΩ Max.
Insulation Resistance	: 100MΩ Min. at 500V DC
Dielectric Strength	: 500V AC for one Minute

### Diagram



#### CIRCUIT



No.	Part Name	Material	Finish	Qty
1	Body	PA	-	1
2	Sleeve	BSR	Ni	
3	Contact A	PBS t=0.25	Ni	
4	Contact B	PBS t=0.3	Au	
5	Contact C	PBS t=0.3	Ni	
6	Contact D	PBS t=0.3	Ni	
7	CAP	PE	-	

### Part Number Table

Description	Part Number
2.5mm Jack Socket, 4 Pole	PSG08262

Dimensions : Millimetres

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands  
 Farnell.com/exclusive-brands  
 Element14.com/exclusive-brands

pro-SIGNAL