

DS14185 EIA/TIA-232 3 Driver x 5 Receiver

General Description

The DS14185 is a three driver, five receiver device which conforms to the EIA/TIA-232-E standard.


The flow-through pinout facilitates simple non-crossover board layout. The DS14185 provides a one-chip solution for the common 9-pin serial RS-232 interface between data terminal and data communications equipment.

- Flow through pinout
- Failsafe receiver outputs
- 20-pin SOIC package
- LapLink® compatible -200 kbps data rate

Features


- Replaces one 1488 and two 1489s
- Conforms to EIA/TIA-232-E
- 3 drivers and 5 receivers

Connection Diagram



Order Number DS14185WM See NS Package M20B

Functional Diagram



LapLink® is a registered trademark of Travelling Software.

Absolute Maximum Ratings (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Driver Output Voltage (Power

Off) $\pm 15V$ Receiver Input Voltage $\pm 25V$

Receiver Output Voltage

 (R_{OUT}) 0V to V_{CC}

Maximum Package Power Dissipation @ +25°C

M Package 1488 mW

Derate M Package 11.9 mW/°C above +25°C

Storage Temperature Range -65°C to $+150^{\circ}\text{C}$ Lead Temperature Range (Soldering, 4 seconds) $+260^{\circ}\text{C}$ ESD Ratings (HBM, 1.5 k Ω , 100 pF) ≥ 1.5 kV

Recommended Operating Conditions

	Min	Тур	Max	Units
Supply Voltage (V _{CC})	+4.75	+5.0	+5.25	V
Supply Voltage (V+)	+9.0	+12.0	+13.2	V
Supply Voltage (V-)	-13.2	-12.0	-9.0	V
Operating Free Air				
Temperature (T_A)	0	25	70	°C

Electrical Characteristics (Note 2)

Over recommended supply voltage and operating temperature ranges, unless otherwise specified.

Symbol	Parameter	Conditions		Min	Тур	Max	Units
DEVICE CHARACTERISTICS							
I _{cc}	V _{CC} Supply Current	No Load, All Inputs at +5V			21.0	30	mA
I ⁺	V ⁺ Supply Current	No Load, All Driver	$V^{+} = 9V, V^{-} = -9V$		8.7	15	mA
	(Note 2)	Inputs at 0.8V or +2V	V ⁺ = 13.2V, V ⁻ = -13.2V		13	22	mA
I-	V ⁻ Supply Current	All Receiver Inputs	$V^{+} = 9V, V^{-} = -9V$		-12.5	-22	mA
	(Note 2)	at 0.8V or 2.4V.	V ⁺ = 13.2V, V ⁻ = -13.2V		-16.5	-28	mA
DRIVER C	HARACTERISTICS			•			
V _{IH}	High Level Input Voltage			2.0			V
V _{IL}	Low Level Input Voltage					0.8	V
I _{IH}	High Level Input Current	$V_{IN} = 5V$				10	μΑ
	(Note 2)						
I _{IL}	Low Level Input Current	$V_{IN} = 0V$			-1.24	-1.5	mA
	(Note 2)						
V _{OH}	High Level Output Voltage	$R_L = 3 \text{ k}\Omega, V_{IN} = 0.8V,$		6	7		V
	(Note 2)	$V^{+} = 9V, V^{-} = -9V$					
		$R_L = 3 k\Omega$, $V_{IN} = 0.8V$,		8.5	9		V
		$V^{+} = +12V, V^{-} = -12V$					
		$R_L = 7 \text{ k}\Omega, V_{IN} = 0.8V,$			11.5		V
		$V^{+} = +13.2V, V^{-} = -13.2V$					
V_{OL}	Low Level Output Voltage	$R_L = 3 k\Omega$, $V_{IN} = 2V$,			-7	-6	V
	(Note 2)	$V^{+} = 9V, V^{-} = -9V$					
		$R_L = 3 \text{ k}\Omega, V_{IN} = 2V,$			-8	-7.5	V
		$V^+ = +12V, V^- = -12V$					
		$R_L = 7 \text{ k}\Omega, V_{IN} = 0.8V,$			-11	-10	V
		$V^+ = +13.2V, V^- = -13.2V$	2V				
I _{os} +	Output High Short	$V_{O} = 0V, V_{IN} = 0.8V$		-6	-13	-18	mA
	Circuit Current (Note 2)						
I _{os} -	Output Low Short	$V_{O} = 0V, V_{IN} = 2.0V$			13	18	mA
	Circuit Current (Note 2)						
	-				-		

www.national.com 2

Electrical Characteristics (Note 2) (Continued)

Over recommended supply voltage and operating temperature ranges, unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Units	
DRIVER CHARACTERISTICS							
R _o	Output Resistance	$-2V \le V_O \le +2V$,	300			Ω	
		$V^{+} = V^{-} = V_{CC} = 0V$					
		$-2V \le V_O \le +2V$,	300			Ω	
		$V^+ = V^- = V_{CC} = Open Ckt$					
RECEIVER	CHARACTERISTICS		•	•	•		
V _{TH}	Input High Threshold	$V_{O} \le 0.4V, I_{O} = 3.2 \text{ mA}$		1.85	2.4	V	
	(Recognized as a High Signal)						
V _{TL}	Input Low Threshold	$V_{O} \ge 2.5V, I_{O} = -0.5 \text{ mA}$	0.7	1.0		V	
	(Recognized as a Low Signal)						
R _{IN}	Input Resistance	$V_{IN} = \pm 3V$ to $\pm 15V$	3.0	4.1	7.0	kΩ	
I _{IN}	Input Current (Note 2)	$V_{IN} = +15V$	2.1	4.1	5.0	mA	
		$V_{IN} = +3V$	0.43	0.7	1	mA	
		$V_{IN} = -15V$	-5.0	-4.1	-2.1	mA	
		$V_{IN} = -3V$	-1	-0.65	-0.43	mA	
V _{OH}	High Level Output Voltage	$I_{OH} = -0.5 \text{ mA}, V_{IN} = -3V$	2.6	4		V	
	(Note 7)	$I_{OH} = -10 \mu A, V_{IN} = -3V$	4.0	4.9		V	
		I _{OH} = -0.5 mA, V _{IN} = Open Circuit	2.6	4		V	
		I _{OH} = -10 μA, V _{IN} = Open Circuit	4.0	4.9		V	
V _{OL}	Low Level Output Voltage	$I_{OL} = 3.2 \text{ mA}, V_{IN} = +3V$		0.2	0.4	V	
I _{OSR}	Short Circuit Current (Note 2)	$V_O = 0V$, $V_{IN} = 0V$	-4	-2.7	-1.7	mA	

Switching Characteristics (Note 2)

 $T_A = 25^{\circ}C$

Symbol	Parameter	Conditions	Min	Тур	Max	Units	
DRIVER C	DRIVER CHARACTERISTICS						
t _{PHL}	Propagation Delay High to Low	$R_L = 3 \text{ k}\Omega, C_L = 50 \text{ pF}$		60	350	ns	
t _{PLH}	Propagation Delay Low to High	(Figures 1, 2)		240	350	ns	
t _r , t _f	Output Slew Rate (Note 8)			50		ns	
RECEIVER CHARACTERISTICS							
t _{PHL}	Propagation Delay High to Low	$R_L = 1.5 \text{ k}\Omega, C_L = 15 \text{ pF}$		150	350	ns	
t _{PLH}	Propagation Delay Low to High	(includes fixture plus probe), (Figures 3, 4)		240	350	ns	
t _r	Rise Time			87	175	ns	
t _f	Fall Time			40	100	ns	

Note 1: Absolute Maximum Ratings are those values beyond which the safety of the device cannot be guaranteed. They are not meant to imply that the devices should be operated at these limits. The table of Electrical Characteristics specifies conditions of device operation.

Note 2: Current into device pins is defined as positive. Current out of device pins is defined as negative. All voltages are referenced to ground unless otherwise specified. For current, minimum and maximum values are specified as an absolute value and the sign is used to indicate direction. For voltage logic levels, the more positive value is designated as maximum. For example, if –6V is a maximum, the typical value (–6.8V) is more negative.

- Note 3: All typicals are given for: V_{CC} = +5.0V, V^+ = +12.0V, V^- = -12V, T_A = +25°C.
- Note 4: Only one driver output shorted at a time.
- Note 5: Generator characteristics for driver input: f = 64 kHz (128 kbits/sec), $t_r = t_f < 10$ ns, $V_{IH} = 3V$, $V_{IL} = 0V$, duty cycle = 50%.
- Note 6: Generator characteristics for receiver input: f = 64 kHz (128 kbits/sec), $t_r = t_f = 200 \text{ ns}$, $V_{IH} = 3V$, $V_{IL} = -3V$, duty cycle = 50%.
- Note 7: If receiver inputs are unconnected, receiver output is a logic high.

Note 8: Refer to typical curves. Driver output slew rate is measured from the +3.0V to the -3.0V level on the output waveform. Inputs not under test are connected to V_{CC} or GND. Slew rate is determined by load capacitance. To comply with a 30 V/µs maximum slew rate, a minimum load capacitance of 390 pF is recommended.

Parameter Measurement Information




FIGURE 1. Driver Propagation Delay and Transition Time Test Circuit (Note 5)




FIGURE 2. Driver Propagation Delay and Transition Time Waveforms Slew Rate (SR) = $6V/(t_r \text{ or } t_f)$




FIGURE 3. Receiver Propagation Delay and Transition Time Test Circuit (Note 6)




FIGURE 4. Receiver Propagation Delay and Transition Time Waveform

www.national.com

Pin Descriptions

Pin #	Name	Description
13, 15, 16	D _{IN}	Driver Input Pins
5, 6, 8	D _{OUT}	Driver Output Pins, RS-232 Levels
2, 3, 4, 7, 9	R _{IN}	Receiver Input Pins, RS-232 Levels
12, 14, 17, 18, 19	R _{OUT}	Receiver Output Pins
11	GND	Ground
1	V ⁺	Positive Power Supply Pin (+9.0 ≤ V ⁺ ≤ +13.2)
10	V-	Negative Power Supply Pin (–9.0 ≤ V [−] ≤ –13.2)
20	V _{CC}	Positive Power Supply Pin (+5V ±5%)

Applications Information

In a typical Data Terminal Equipment (DTE) to Data Circuit-Terminating Equipment (DCE) 9-pin de-facto interface implementation, 2 data lines and 6 control lines are required. The data lines are TXD and RXD. The control lines are RTS, DTR, DSR, DCD, CTS, and RI.

The DS14185 is a 3 x 5 Driver/Receiver and offers a single chip solutuion for this DTE interface. As shown in *Figure 5*, this interface allows for direct flow-thru interconnect. For a more conservative design, the user may wish to insert ground traces between the signal lines to minimize cross talk.

LapLink COMPATIBILITY

The DS14185 can easily provide 128 kbps data rate under maximum driver load conditions of C_L = 2500 pF and R_L = 3 k Ω , while power supplies are:

$$V_{CC} = 4.75V, V^{+} = 10.8V, V^{-} = -10.8V$$

MOUSE DRIVING

A typical mouse can be powered from the drivers. Two driver outputs connected in parallel and set to $V_{\rm OH}$ can be used to supply power to the V+ pin of the mouse. The third driver output is set to $V_{\rm OL}$ to sink the current from the V^ terminal. Refer to typical curves of $V_{\rm OUT}/I_{\rm OUT}.$ Typical mouse specifications are:

10 mA at +6V 5 mA at -6V






FIGURE 5. Typical DTE Application

5 www.national.com

Typical Performance Characteristics







The above input waveforms were used to generate all Typical AC Characteristics.

Driver Output Slew Rate between +3V and -3V vs Load Capacitance


Conditions: V_{CC} = 5V, R_L = 5 $k\Omega$, T_A = 25°C, f_{IN} = 64 kHz Square Wave




Driver Output Voltage vs Frequency and C_L Conditions: V_{CC} = 5V, R_L = 5 $k\Omega$, T_A = 25°C



Supply Current vs Frequency and Driver C_L




Supply Current vs Frequency and Driver C_L




01193817

Typical Performance Characteristics (Continued)

Supply Current vs Frequency





Driver Output Current vs Output Voltage




Physical Dimensions inches (millimeters)

unless otherwise noted







Small Outline Package Order Number DS14185WM NS Package M20B

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

BANNED SUBSTANCE COMPLIANCE

National Semiconductor certifies that the products and packing materials meet the provisions of the Customer Products Stewardship Specification (CSP-9-111C2) and the Banned Substances and Materials of Interest Specification (CSP-9-111S2) and contain no "Banned Substances" as defined in CSP-9-111S2.



National Semiconductor Americas Customer Support Center

Email: new.feedback@nsc.com Tel: 1-800-272-9959

www.national.com

National Semiconductor Europe Customer Support Center Fax: +49 (0) 180-530 85 86

Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 69 9508 6208
English Tel: +44 (0) 870 24 0 2171
Français Tel: +33 (0) 1 41 91 8790

National Semiconductor Asia Pacific Customer Support Center Email: ap.support@nsc.com National Semiconductor Japan Customer Support Center Fax: 81-3-5639-7507 Email: jpn.feedback@nsc.com Tel: 81-3-5639-7560