2-Serial Module 6.0V 2.5F



FEATURES

Electric double layer capacitor


2 cells serially connected supercapacitor

Semi-permanent, quick charge and discharge than batteries Suitable for smart meter or car driving recorder application UL and ISO/TS certificated, RoHS compliant

Radial design with lead terminal type customized in 3 ways



DIMENSIONS



		Dimens	ions in mm	2	
D +0.1 Max	W ± 1.0	L ± 1.5	$d \pm 0.1$		P ± 0.2
Ф10.5	21.0	22.5	Ф0.6	1: 5.5	O: 15.5 H: 10.5

This drawing is not to be scaled.

SPECIFICATIONS

Part Number	Rated Voltage, V _R	Rated Capacitance	AC ESR 1kHz	DCIR	Maximum Current	Leakage Current	Stored Energy	Dimension D x W x L	Weight
	(V)	(F)	$(m\Omega)$	$(m\Omega)$	(A)	(mA)	(J)	(mm)	(g)
VEC 6R0 255 QG-X	6.0	2.5	135.00	205.00	5.	0.015	45.0	10.5 x 21.0 x 22.5	4.7

^{*} X is variant type code such as I, O or H.

^{*} Leakage Current: After 72hours at $V_{\rm R}$ and 25 $^{\circ}\!\mathrm{C}$

Item	Characteristics	Remarks
Rated Voltage(V _R)	6.0V	
Capacitance Tolerance	-10 ~ +30%	
Operating Temperature (T _{min} ~ T _{max})		Δcap ≤ 30% of initial value at 25℃
	-40 ~ +65℃	ΔESR ≤ 100% of specified value at 25 ℃
(min max)		After 1,000 hours application of V_{R} at T_{max}
Storage Temperature	-40 ~ 70℃	
		Δcap ≤ 30% of initial value at 25℃
Cycle Life	500,000 cycles	ΔESR ≤ 100% of specified value at 25 °C
		Cycles from V_R to $1/2 \cdot V_R$ under constant current at 25°C
		Δcap ≤ 10% of initial value at 25℃
Shelf Life	2 years	ΔESR ≤ 50% of specified value at 25°C
		Without electrical charge under T _{max}



^{*} Maximum Current: 1 second discharge to ½· V_R