

Quartz Crystal

SEAM SEALED CERAMIC 7.0 X 5MM Surface Mount Package



SPECIFICATION

P/N: KSE-6FxxxxxMAF343ZA3

xxxxx - frequency, MHz; e.g. 08000=8MHz, 12000=12MHz

Quartz Crystal

SEAM SEALED CERAMIC 7.0 X 5MM Surface Mount Package

FEATURE

- I Ultra thin, thickness 1.0mm
- I Leadless type
- I High precision characteristic covering up to high frequency range
- I Automatic mounting
- I Embossed taping specification
- I Reflow soldering

APPLICATIONS

- I Ideally suited designed for disc drives, NB, PCs and hand-held electronic products

ELECTRICAL SPECIFICATIONS

Output Frequency Range	1MHz - 100.000 MHz
Mode	AT/Fundamental
Frequency Tolerance (at 25°C)	±30ppm
Frequency Stability Over Operating Temperature Characteristics	±30ppm, -40 °C to +85 °C
Storage Temperature Range	-40 °C to +85 °C
Operable Temperature Range	-40 °C to +85 °C
Shunt Capacitance (C ₀)	5.0 pF Max
Driver Level (Typical)	100µW
Load Capacitance(C _L)	16pF
Equivalent Series Resistance ESR (Ω)	40Ω Max
Aging @25°C 1 st year (Max)	±3ppm/year
Shock Resistance	Drop test of 3 times on 2mm stainless plate from 75cm height

REMARK: SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE. PLEASE CONFIRM WITH OUR SALES ENGINEER.

