

5

4

3

2

1


D

C

B



A

Edge mark on first conductor



- Wire _____ Tinned copper
- Gauge _____ AWG 28/7 0,089 mm²
- Voltage rating _____ 300 Vr.m.s
- Current rating _____ 1,3 A at 10°C rise above ambient
- Capacity unbalanced _____ 45,9 pF/m at 1 MHz
- Impedance unbalanced _____ 105 Ω
- Propagation delay _____ 4,9 ns/m nominal
- Insulation material _____ PVC
- Temperature rating _____ -20°C (operating)
 _____ -30°C (static) to +105°C
- Flammability rating _____ Flame retardant VW1
- Insulation resistance _____ 10 000 MΩ/km
- Approval _____ UL AWM style 2651

09 18 009 7004	100 m (328 feet)
09 18 009 7001	30,48 m (100 feet)
Part number	Length per reel

				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	SEK 18 flat cable 9 poles	Maßstab/ Scale
			Detail.	20/10/05	JMDR			10:1
			Insp.					
			Stand.					
34400	17/09/07	PK	HARTING EURL F-95972 Paris				TB 09 18 009 700X	Blatt/ Page
33246	20/10/05	JMDR	Mod.	Dot.	Name		Sub.	1 / 1