



REV	CONTENT	CHK	DATE
-----	---------	-----	------






**PCB LAYOUT**  
S=1.5:1




**NOTES:**

1. Rating:300V 10A(UL);
2. Insulation Withstands Voltage: AC2000V/MIN
3. Insulation Resistance: 500MΩ or more at DC500V
4. Using Temperature Range: -40°C--+105°C
5. Screw Torque Vlaue: 0.4N.m
6. Suitable Electric Wire: 24-14AWG
7. RoHS Compliance.
- 8."★" is the important dimension.



**SECTION:A-A**



Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	—	//
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	0	over 10	over 100	over 150
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.55	±0.70	±0.75	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5

ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTE
DWG.	SK	DATE	14.05.16	UNITS	mm
CHK.		DATE		SCALE	2 : 1
APP.		DATE			
KEEN SIDE ELECTRONICS				NAME	KSE-103-5.0-XX
				DWGNO.	