

HyFlex® 11-531 11-537 11-539

MECHANICAL PROTECTION

 CUT PROTECTION

 LIGHT

STYLE #	CONSTRUCTION	GAUGE	LINER MATERIAL	COATING MATERIAL	FINISHING	CUFF STYLE	EN SIZE	LENGTH MM	PACKAGING
11-531	Knitted	18	Seamless plaited liner with INTERCEPT™ technology yarn	Nitrile foam	Palm coated	Knitwrist	6, 7, 8, 9, 10, 11	220-270	12 pairs in a bag, 12 bags in a carton
11-537	Knitted	18	Seamless plaited liner with INTERCEPT™ technology yarn	Nitrile foam	¾ Dipped	Knitwrist	6, 7, 8, 9, 10, 11	220-270	12 pairs in a bag, 12 bags in a carton
11-539	Knitted	18	Seamless plaited liner with INTERCEPT™ technology yarn	Nitrile foam	Fully coated	Knitwrist	6, 7, 8, 9, 10, 11	220-270	12 pairs in a bag, 12 bags in a carton



Exceptional grip performance in a comfortable ultralight weight cut resistant glove

PRIMARY INDUSTRIES



IDEAL APPLICATIONS

- Assembly of small sharp parts
- Handling small sharp metal parts
- Light duty stamping
- Maintenance

DESCRIPTION

- The new INTERCEPT™ cut resistance yarn has been designed to exceed industry standards. This Ansell proprietary technology offers best-in-class cut protection and increased comfort with dexterity.
- The liner also features ZONZ™ Comfort Fit technology for enhanced fit, higher dexterity and reduced hand fatigue.
- The FORTIX formulation provide enhanced abrasion resistance and grip, which extends gloves' working life and improves comfort in abrasive applications.
- Silicone free
- Dirt masking colours for longer wear times.

FEATURED TECHNOLOGY



EN 388
4342

CATEGORY II

Print date: 14-07-2016

Ansell Healthcare Europe N.V. (European Head Office)

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

<http://www.ansell.eu> • E-mail info@ansell.eu