


Automotive-grade N-channel 60 V, 0.07 Ω typ., 4 A STripFET II Power MOSFET in a SOT-223 package

4

SOT-223



Features

Order code	V _{DS}	R _{DS(on)} max.	I _D
STN4NF06L	60 V	< 0.1 Ω	4 A

- AEC-Q101 qualified
- Exceptional dv/dt capability
- 100% avalanche tested
- · Low gate charge

Applications

· Switching applications

Description

This Power MOSFET has been developed using STMicroelectronics' unique STripFET process, which is specifically designed to minimize input capacitance and gate charge. This renders the device suitable for use as primary switch in advanced high-efficiency isolated DC-DC converters for telecom and computer applications, and applications with low gate charge driving requirements.



Product status link STN4NF06L

Product summary				
Order code	STN4NF06L			
Marking	4NF06L			
Package	SOT-223			
Packing	Tape and reel			



1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{DS}	Drain-source voltage (V _{GS} = 0 V)	60	V
V _{GS}	Gate-source voltage	±16	V
I _D ⁽¹⁾	Drain current (continuous) at T _C = 25 °C	4	А
ıD, ,	Drain current (continuous) at T _C = 100 °C	2.9	Α
I _{DM} ⁽²⁾	Drain current (pulsed)	16	А
P _{TOT}	Total power dissipation at T _C = 25 °C	3.3	W
	Derating Factor	0.026	W/°C
dv/dt ⁽³⁾	Peak diode recovery avalanche energy	10	V/ns
E _{AS} ⁽⁴⁾	Single pulse avalanche energy	200	mJ
T _{stg}	Storage temperature range	55 to 150	°C
TJ	Operating junction temperature range	-55 to 150	

- 1. Current limited by the package.
- 2. Pulse width limited by safe operating area.
- 3. $I_{SD} \le 3~A,~di/dt \le 150~A/\mu s,~V_{DD} = V_{(BR)DSS},~T_J \le T_J~max.$
- 4. Starting $T_J = 25$ °C, $I_D = 4$ A, $V_{DD} = 30$ V.

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R _{thj-pcb} (1)	Thermal resistance junction-pcb	38	°C/W
R _{thj-pcb} ⁽²⁾	memia resistance junction-pob	100	°C/W
T _J ⁽³⁾	Maximum lead temperature for soldering purpose	260	°C

- 1. When Mounted on FR-4 board with 1 inch2 pad, 2 oz. of Cu. and t <10 s.
- 2. When mounted on minimum recommended footprint.
- 3. For 10 s 1.6 mm from case.

DS5801 - Rev 3 page 2/14



2 Electrical characteristics

 T_C = 25 °C unless otherwise specified

Table 3. On-/off-states

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit	
V _{(BR)DSS}	Drain-source breakdown voltage	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$	60			V	
I _{DSS}	Zoro goto voltogo droin ourrent	V _{GS} = 0 V, V _{DS} = 60 V			1	μA	
DSS		V _{GS} = 0 V, V _{DS} = 60 V, T _C = 125 °C			10	μA	
I _{GSS}	Gate-body leakage current	V _{DS} = 0 V, V _{GS} = ±16 V			±100	nA	
V _{GS(th)}	Gate threshold voltage	V _{DS} = V _{GS} , I _D = 250 μA	1		2.8	V	
D	Static drain-source on-resistance	V _{GS} = 10 V, I _D = 1.5 A		0.07	0.10	Ω	
R _{DS(on)}	Static drain-source on-resistance	V _{GS} = 5 V, I _D = 1.5 A		0.085	0.12	12	

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
C _{iss}	Input capacitance		-	340		pF
C _{oss}	Output capacitance	V _{DS} = 25 V, f = 1 MHz, V _{GS} = 0 V	-	63		pF
C _{rss}	Reverse transfer capacitance		-	30		pF
Qg	Total gate charge	V _{DD} = 48 V, I _D = 3 A	-	7	9	nC
Q _{gs}	Gate-source charge	$R_G = 4.7 \Omega$, $V_{GS} = 5 V$	-	1.5		nC
Q _{gd}	Gate-drain charge	(see Figure 14. Test circuit for gate charge behavior)	-	2.8		nC

Table 5. Switching times

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
t _{d(on)}	Turn-on delay time	V _{DD} = 30 V, I _D = 1.5 A,	-	9	-	ns
t _r	Rise time	$R_G = 4.7 \ \Omega, \ V_{GS} = 5 \ V$ time (see Figure 13. Test circuit for resistive load switching times and	-	25	-	ns
t _{d(off)}	Turn-off delay time		-	20	-	ns
t _f	Fall time	Figure 18. Switching time waveform)	-	10	-	ns

DS5801 - Rev 3 page 3/14



Table 6. Source-drain diode


Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
I _{SD}	Source-drain current		-		4	Α
I _{SDM} ⁽¹⁾	Source-drain current (pulsed)		-		16	Α
V _{SD} ⁽²⁾	Forward on voltage	I _{SD} = 4 A, V _{GS} = 0 V	-		1.5	V
t _{rr}	Reverse recovery time	I _{SD} = 4 A, di/dt = 100 A/μs,	-	50		ns
Q _{rr}	Reverse recovery charge	V _{DD} = 25 V, T _J = 150 °C	-	88		nC
I _{RRM}	Reverse recovery current	(see Figure 15. Test circuit for inductive load switching and diode recovery times)	-	3.5		Α


- 1. Pulse width limited by safe operating area.
- 2. Pulsed: pulse duration = $300 \mu s$, duty cycle 1.5%.


DS5801 - Rev 3 page 4/14





2.1 Electrical characteristics (curves)











DS5801 - Rev 3 page 5/14



Figure 7. Capacitance variations




Figure 8. Normalized gate threshold voltage vs temperature




Figure 9. Normalized on-resistance vs temperature




Figure 10. Source-drain diode forward characteristics





Figure 11. Normalized breakdown voltage vs temperature



DS5801 - Rev 3 page 6/14 Downloaded from Arrow.com.



3 Test circuits

Figure 12. Test circuit for resistive load switching times




Figure 13. Test circuit for gate charge behavior




Figure 14. Test circuit for inductive load switching and diode recovery times




Figure 15. Unclamped inductive load test circuit




Figure 16. Unclamped inductive waveform





Figure 17. Switching time waveform



DS5801 - Rev 3 page 7/14





4 Package information


In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

4.1 SOT-223 package information

Figure 18. SOT-223 package outline







0046067_15


0046067



Table 7. SOT-223 package mechanical data

Dim.		mm	
Dilli.	Min.	Тур.	Max.
A			1.8
В	0.6	0.7	0.85
B1	2.9	3	3.15
С	0.24	0.26	0.35
D	6.3	6.5	6.7
е		2.3	
e1		4.6	
E	3.3	3.5	3.7
Н	6.7	7	7.3
V			10 deg
A1	0.02		0.1

Figure 19. SOT-223 recommended footprint (dimensions are in mm)




DS5801 - Rev 3 page 9/14




4.2 SOT-223 packing information

Figure 20. SOT-223 tape outline



*Cumulative tolerance of 10 sprocket holes is ±0.20 mm

Figure 21. SOT-223 reel outline



DS5801 - Rev 3 page 10/14



Table 8. SOT-223 tape and reel mechanical data

	Таре				Tape	
Dim		mm		Dim.	mn	1
Dim.	Min.	Тур.	Max.	5	Min.	Max.
A0	6.75	6.85	6.95	А		180
В0	7.30	7.40	7.50	N	60	
K0	1.80	1.90	2.00	W1		12.4
F	5.40	5.50	5.60	W2		18.4
Е	1.65	1.75	1.85	W3	11.9	15.4
W	11.7	12.0	12.3			·
P2	1.90	2.00	2.10	Base qua	ntity pcs	1000
P0	3.90	4.00	4.10	Bulk qua	ntity pcs	1000
P1	7.90	8.00	8.10			·
Т	0.25	0.30	0.35			
DΦ	1.50	1.55	1.60			
D1Ф	1.50	1.60	1.70			



Revision history

Table 9. Document revision history

Date	Version	Changes
22-Apr-2008	1	Initial version.
29-Apr-2011	2	Figure 5, Figure 7, Figure 11 and Figure 12 have been updated.
05-May-2020	3	Updated Section 4.1 SOT-223 package information. Minor text changes.





Contents

1	Elec	trical ratingstrical ratings	2
2	Elec	trical characteristics	3
	2.1	Electrical characteristics (curves)	5
3	Test	circuits	7
4	Pacl	kage information	8
	4.1	SOT-223 package information	8
	4.2	SOT-223 packing information	10
Rev	vision	history	12



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics - All rights reserved

DS5801 - Rev 3 page 14/14