

Vishay Spectrol

# 3/8" Square (10 mm) Single-Turn Cermet Trimmer



#### **FEATURES**





• "O" ring seal for solvent and aqueous washing

RoHS COMPLIANT


- Rigid board mounting achieved with pins secured in housing
- Multi-finger wiper for better contact resistance
- · Solid end stop
- Tests according to CECC 41000 or IEC 60393-1
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

## **DESIGN SUPPORT TOOLS**





The Model 63 cermet trimmer is available in several pin configurations for top or side adjustment and with a choice of Knob styles for finger setting. Quick adjustment is achieved with multi-finger wiper and the standard resistance range is between  $100 \Omega$  and  $2 M\Omega$  with a tolerance of  $\pm 10 \%$ .





# Vishay Spectrol

ELECTRICAL SPECIFICATIONS			
Effective travel	270° nominal		
Resistance range	100 $\Omega$ to 2 M $\Omega$		
Resistance tolerance	± 10 %		
End resistance	2 Ω or 1 % whichever is greater		
Temperature coefficient of resistance (typical)	± 100 ppm/°C		
Power rating	0.5 W at +70 °C derated linearly to 0 W at 125 °C maximum voltage not to exceed 250 V		
Circuit diagram	$ \begin{array}{cccc} \overset{a}{\circ} & & & & & & & \\ \overset{b}{\circ} & & & & & & \\ (1) & & & & & & \\ & & & & & & \\ & & & & & &$		
Dielectric withstand voltage	1000 V <sub>AC</sub> at sea level; 250 V <sub>AC</sub> at 80 000 ft (24 000 m)		
Insulation resistance (500 V <sub>DC</sub> )	1000 MΩ minimum		
Contact resistance variation	1 % or 1 Ω, whichever is greater		

MECHANICAL SPECIFICATIONS				
Mechanical travel	300° ± 50			
Starting torque	35 mNm max.			
Weight	0.03 oz. (0.85 g) max.			
Resistance element	Cermet			
2 terminal adjustability	± 0.15 % of RT			
3 terminal adjustability	± 0.05 % of applied voltage			
Terminals	Pure Sn (code e3)			

ENVIRONMENTAL SPECIFICATIONS				
Temperature range	-55 °C to +125 °C			
Climatic category	55/125/21			
Sealing	IP64			

PERFORMANCES							
TESTS	CONDITIONS	MAX. (R)	CHANGE PER CECC		PER IEC	PER MIL	
			V <sub>AB</sub> /V <sub>AC</sub>	41100	PER IEC	PER WILL	
Vibration	98 m/s <sup>2</sup> , 10 Hz to 500 Hz	1 %	2 %	(PARA 2.3.2)	Test FC (IEC 6-2-6)	Method 204	
Electrical endurance	1000 h	3 %	-	(PARA 2.5.16)	=	No equiv.	
Soldering	-	-	-	(PARA 2.3.7)	Test TB (IEC 68-2-20)	Method 208	
Resistance to heat	-	1 %	-	(PARA 2.3.7)	Test B (IEC 68-2-20A)	Method 210	
Damp heat steady state	21 days	3 %	-	(PARA 2.1)	Test C (IEC 68-2-3)	Method 103	
Mechanical life	200 cycles	3 %	-	-	Method 2	-	
Terminal strength	2.2 lbs. (1 kg)	min.	-	-	-	-	

#### Note

• Nothing stated herein shall be construed as a guarantee of quality or durability

### **MARKING**

- Vishay trademark
- Model
- Resistance value
- Tolerance
- Date code
- Terminal identification





www.vishay.com

# Vishay Spectrol

#### **PACKAGING**

- In box of 200 pieces code B40 (BO200)
- On request : In box of 100 pieces code B30 (BO100) In tube of 50 pieces code T20 (TU50)





RELATED DOCUMENTS				
APPLICATION NOTES				
Potentiometers and Trimmers	www.vishay.com/doc?51001			
Guidelines for Vishay Sfernice Resistive and Inductive Components	www.vishay.com/doc?52029			