



REACH&RoHS Compliant


REVISION RECORD MODIFICATIONS		DATE	REV.
NEW		2021/10/12	A/0



WIRING DIAGRAM



LENGTH	
1. 0m+/-20mm	2. 0m+/-40mm
3. 0m+/-60mm	4. 0m+/-90mm
5. 0m+/-110mm	7. 0m+/-140mm
10m+/-200mm	15m+/-310mm



Printing: DIGITUS CAT6A S/FTP CU ISO/IEC 11801 & ANSI/TIA-568-C.2 26AWG CE Assmann Electronic GmbH Auf dem Schüffel 3 58513 Lüdenscheid Germany MM/DD/YY C

DESCRIPTIONS:

- . CABLE:CAT 6A S-FTP STRANDED WIRES AWG26
- . WIRES:BC AWG26 (7/0.15±0.015MM) x 4 TWISTED PAIRS
- . PLUG:RJ45 8P8C 3U" GOLD-PLATED ON CONTACT AREA TRANSPARENT COLOR
- . MOLDING:PVC MOLDING COLOR :GREY
- . CABLE JACKET:LSOH, GREY OD:6.2±0.3MM
- . WIRES CONNECTION BASE ON TIA/EIA 568B
- . TEST STANDARD ACC TO ISO PATCH CORD CAT6A
- . PACKING: ACCORDING TO CUSTOMER REQUIREMENTS
- . CABLE LENGTH: xxx METERS



Assmann Electronic GmbH				
DRAW NO.	121***	PRODUCT NAME	Cat6A SFTP 8P8C/M TO 8P8C/M	
CUSTOMER		VIEW	Tolerance	
ITEM NO.	DK-1644-A-xxxCL		X. ±1.00	X.X ±0.50
APPOBY	CHECKBY	DRAWNBY	UNTT	MM
			Page	1 of 1

NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT' Y	REMARK
1				
2				
3				
4				
5				
6				
7				