

# Linear measuring technology

**Draw wire mechanics with analog sensor**

**Draw wire encoder A30**

**Measuring length max. 0.6 m  
Traverse speed max. 0.8 m/s**



The draw wire mechanics A30 with analog output stands out with its miniaturized design. It is available with potentiometer, voltage or current output.



Analog output

## Miniaturized and simple

- Measuring length up to 600 mm.
- For applications with a low traversing speed.
- Easy to install.

**Order code** **D5.350X.AXX.X.0000**  
draw wire encoder

Type **a** **b** **c**

**a** Measuring range  
A = 300 mm <sup>1)</sup>  
B = 600 mm

**b** Output circuit  
11 = analog output 4 ... 20 mA  
22 = analog output 0 ... 10 V DC  
power supply 15 ... 28 V DC  
33 = potentiometer output 10 kΩ


**c** Type of connection  
4 = radial cable, 0.5 m [1.64']

## Accessories for draw wire encoder

Dimensions in mm [inch]

Order no.

### Guide pulley



Technical data:  
- mounting bracket (anodized alum.)  
- guide pulley (plastic POM)  
- ball bearing (type 696-2R5)

Scope of delivery:  
- 2 x countersunk screws for lateral fixing  
- 2 x hexagonal screws for fixing on a flat surface

**8.0000.7000.0045**

1) Not suitable for potentiometer output.

# Linear measuring technology

<b>Draw wire mechanics with analog sensor</b>	<b>Draw wire encoder A30</b>	<b>Measuring length max. 0.6 m</b> <b>Traverse speed max. 0.8 m/s</b>
---	------------------------------	--




## Technical data

Mechanical characteristics (draw wire mechanics)							
<b>Speed max.</b>	0.8 m/s						
<b>Working temperature</b>	-10°C ... +80°C [+14°F ... +176°F]						
<b>Protection acc. to EN 60529</b>	IP50						
<b>Weight</b>	approx. 60 g [2.12 oz]						
<b>Extension force <math>F_{min}</math></b>	3 N						
<b>Repeat accuracy</b>	±0.15 mm						
<b>Linearity</b>	±0.35 %						
<b>Material</b>	<table style="width: 100%; border: none;"> <tr> <td style="padding-right: 10px;">housing</td> <td>plastic</td> </tr> <tr> <td>wire</td> <td>stainless-steel <math>\varnothing</math> 0.4 mm</td> </tr> <tr> <td></td> <td>plastic-coated</td> </tr> </table>	housing	plastic	wire	stainless-steel $\varnothing$ 0.4 mm		plastic-coated
housing	plastic						
wire	stainless-steel $\varnothing$ 0.4 mm						
	plastic-coated						

Electrical characteristics			
<b>Analog output</b>	0 ... 10 V DC	4 ... 20 mA	potentiometer 10 k $\Omega$
<b>Power supply</b>	15 ... 28 V DC	–	–
<b>Operating range</b>	–	15 ... 28 V DC	max. 48 V DC
<b>Max. load current</b>	15 mA	–	–
<b>Load</b>	–	max. 500 $\Omega$	–
<b>Temperature range</b>	-10°C ... +80°C [+14°F ... +176°F]		
<b>CE compliant acc. to</b>	EMC guideline 2014/30/EU RoHS guideline 2011/65/EU		

### Terminal assignment

Color	BN	WH	GN
0 ... 10 V DC	+ 24 V DC	0 V	$U_{out}$
4 ... 20 mA	+I	-I	n.c.
Potentiometer	Po	Pe	S



### Dimensions

Dimensions in mm [inch]

